

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562024

Luminaire Tested: **SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562024  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8944.8 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 87.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562024

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562024

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	85	82	75	73	71	63	62	60	53	52	51	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	34	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17572	17572	17572
5°	17731	17594	17503
10°	17675	17552	17459
15°	17597	17487	17394
20°	17508	17396	17266
25°	17385	17268	17068
30°	17198	17075	16830
35°	16944	16796	16556
40°	16558	16380	16083
45°	15883	15604	15283
50°	14694	14341	14058
55°	12825	12534	12270
60°	10808	10715	10505
65°	9348	9383	9311
70°	8586	8629	8629
75°	8245	8245	8306
80°	7757	7842	7757
85°	6256	6944	6944



TEST NUMBER: P562024

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.1	2.0
10°-20°	515.3	5.8
20°-30°	777.3	8.7
30°-40°	926.1	10.4
40°-50°	913.1	10.2
50°-60°	697.8	7.8
60°-70°	431.8	4.8
70°-80°	245.3	2.7
80°-90°	74.6	0.8
90°-100°	306.9	3.4
100°-110°	873.2	9.8
110°-120°	836.6	9.4
120°-130°	662.1	7.4
130°-140°	531.5	5.9
140°-150°	416.1	4.7
150°-160°	304.4	3.4
160°-170°	188.6	2.1
170°-180°	64.0	0.7
0°-30°	1472.7	16.5
0°-40°	2398.8	26.8
0°-60°	4009.7	44.8
0°-90°	4761.4	53.2
90°-120°	2016.7	22.5
90°-150°	3626.3	40.5
90°-180°	4183.0	46.8
0°-180°	8944.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1905	1905	1905	1905	1905	
5°	1914	1894	1900	1893	1890	182
15°	1842	1823	1831	1824	1821	520
25°	1708	1687	1696	1678	1677	786
35°	1504	1487	1491	1472	1470	939
45°	1217	1201	1196	1174	1171	933
55°	797	784	779	766	763	714
65°	428	425	430	426	426	434
75°	231	231	231	233	233	244
85°	59	62	66	66	66	69
90°	0	0	0	0	0	4
95°	33	132	594	206	127	38
105°	136	206	890	1572	1494	144
115°	252	305	675	1429	1678	248
125°	356	395	644	1069	1278	319
135°	435	472	636	903	1020	336
145°	513	540	642	781	851	321
155°	586	600	657	706	735	271
165°	648	650	664	679	689	182
175°	679	675	672	668	663	64
180°	674	674	674	674	674	



TEST NUMBER: P562024

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1904.6	1904.6	1904.6	1904.6	1904.6
2.5°	1916.5	1899.8	1904.6	1900.5	1891.5
5°	1914.5	1893.6	1899.7	1893.1	1889.9
7.5°	1899.7	1879.2	1885.3	1878.7	1876.8
10°	1886.6	1867.4	1873.5	1866.8	1863.6
12.5°	1872.2	1851.6	1859.0	1851.1	1847.9
15°	1842.3	1823.1	1830.8	1824.2	1821.0
17.5°	1809.5	1789.0	1796.7	1789.1	1784.9
20°	1783.2	1764.0	1771.8	1760.2	1758.6
22.5°	1754.4	1735.1	1742.9	1727.5	1727.1
25°	1707.8	1686.9	1696.3	1678.2	1676.6
27.5°	1652.3	1633.1	1640.9	1622.4	1620.5
30°	1614.3	1595.0	1602.8	1583.0	1579.8
32.5°	1571.0	1553.0	1559.5	1539.8	1537.8
35°	1504.4	1486.7	1491.2	1471.5	1469.9
37.5°	1428.6	1412.5	1415.1	1393.4	1391.8
40°	1374.8	1358.7	1360.0	1337.0	1335.4
42.5°	1315.7	1299.7	1298.3	1275.3	1273.7
45°	1217.3	1201.2	1195.9	1174.5	1171.3
47.5°	1105.1	1089.0	1079.1	1061.7	1059.4
50°	1023.7	1007.6	999.1	984.2	979.4
52.5°	935.8	919.7	912.5	898.9	894.1
55°	797.3	784.5	779.2	766.1	762.8
57.5°	665.7	657.1	655.6	642.7	641.4
60°	585.7	580.9	580.7	569.3	569.3
62.5°	517.4	513.9	516.4	508.9	507.6
65°	428.2	425.0	429.8	426.5	426.5
67.5°	357.6	357.6	360.6	359.3	359.3
70°	318.3	318.3	319.9	319.9	319.9
72.5°	282.8	281.5	285.8	285.7	284.5
75°	231.3	231.3	231.3	233.0	233.0
77.5°	180.1	180.5	181.8	181.4	180.1
80°	146.0	147.6	147.6	146.0	146.0
82.5°	111.9	113.5	113.5	113.2	111.9
85°	59.1	62.3	65.6	65.6	65.6
87.5°	17.1	22.2	26.2	26.2	24.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.2	54.3	126.0	36.7	27.7
95°	33.3	132.2	594.1	205.6	126.8
97.5°	61.2	154.8	914.9	654.7	448.6
100°	80.7	168.3	984.6	997.3	768.2
102.5°	102.2	182.8	969.2	1276.6	1076.5
105°	135.7	205.8	889.8	1571.8	1494.2
107.5°	169.8	232.6	797.1	1655.0	1724.1
110°	193.3	252.2	743.9	1623.2	1778.4



TEST NUMBER: P562024

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	215.9	271.7	708.0	1547.9	1769.2
115°	252.2	304.8	674.7	1429.4	1678.5
117.5°	284.2	333.6	655.0	1299.9	1563.8
120°	309.8	351.2	653.0	1225.9	1478.8
122.5°	330.3	371.6	647.9	1161.0	1395.8
125°	355.9	394.7	644.0	1068.7	1277.8
127.5°	383.8	420.2	642.0	1013.6	1185.9
130°	398.2	434.5	638.9	975.2	1125.4
132.5°	413.6	448.9	638.9	945.2	1083.4
135°	435.3	471.6	636.3	902.8	1020.4
137.5°	455.8	491.1	636.1	866.8	968.5
140°	471.2	507.5	635.1	837.0	934.7
142.5°	488.6	518.9	638.1	813.2	900.9
145°	513.4	539.7	641.5	781.3	851.4
147.5°	534.7	560.2	647.1	749.1	809.7
150°	553.1	570.6	649.1	738.5	781.0
152.5°	567.5	586.0	651.2	724.0	763.6
155°	586.4	600.2	656.8	706.1	734.9
157.5°	610.0	618.2	658.1	698.0	718.5
160°	622.3	628.5	663.2	691.8	709.3
162.5°	629.4	636.7	664.2	686.6	700.1
165°	647.9	650.4	664.5	678.8	688.8
167.5°	660.4	658.2	670.4	676.9	680.9
170°	664.5	663.3	668.3	669.7	674.7
172.5°	673.7	669.5	671.4	667.7	671.7
175°	678.6	674.8	672.2	668.2	663.2
177.5°	680.6	674.6	671.4	667.3	668.3
180°	673.5	673.5	673.5	673.5	673.5

(END OF REPORT)