

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562128

Luminaire Tested: **SQ4-PR1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562128
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11093.5 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562128
CATALOG NUMBER: SQ4-PR1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562128

CATALOG NUMBER: SQ4-PR1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	89	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	23	20
6	62	50	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17572	17572	17572
5°	17731	17594	17503
10°	17675	17552	17459
15°	17597	17487	17394
20°	17508	17396	17266
25°	17385	17268	17068
30°	17198	17075	16830
35°	16944	16796	16556
40°	16558	16380	16083
45°	15883	15604	15283
50°	14694	14341	14058
55°	12825	12534	12270
60°	10808	10715	10505
65°	9348	9383	9311
70°	8586	8629	8629
75°	8245	8245	8306
80°	7757	7842	7757
85°	6256	6944	6944



TEST NUMBER: P562128

CATALOG NUMBER: SQ4-PR1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.1	1.6
10°-20°	515.3	4.6
20°-30°	777.3	7.0
30°-40°	926.1	8.3
40°-50°	913.1	8.2
50°-60°	697.8	6.3
60°-70°	431.8	3.9
70°-80°	245.3	2.2
80°-90°	74.6	0.7
90°-100°	464.5	4.2
100°-110°	1321.7	11.9
110°-120°	1266.3	11.4
120°-130°	1002.2	9.0
130°-140°	804.5	7.3
140°-150°	629.8	5.7
150°-160°	460.8	4.2
160°-170°	285.4	2.6
170°-180°	96.9	0.9
0°-30°	1472.7	13.3
0°-40°	2398.8	21.6
0°-60°	4009.7	36.1
0°-90°	4761.4	42.9
90°-120°	3052.5	27.5
90°-150°	5489.0	49.5
90°-180°	6332.0	57.1
0°-180°	11093.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1905	1905	1905	1905	1905	
5°	1914	1894	1900	1893	1890	182
15°	1842	1823	1831	1824	1821	520
25°	1708	1687	1696	1678	1677	786
35°	1504	1487	1491	1472	1470	939
45°	1217	1201	1196	1174	1171	933
55°	797	784	779	766	763	714
65°	428	425	430	426	426	434
75°	231	231	231	233	233	244
85°	59	62	66	66	66	69
90°	0	0	0	0	0	4
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	



TEST NUMBER: P562128

CATALOG NUMBER: SQ4-PR1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1904.6	1904.6	1904.6	1904.6	1904.6
2.5°	1916.5	1899.8	1904.6	1900.5	1891.5
5°	1914.5	1893.6	1899.7	1893.1	1889.9
7.5°	1899.7	1879.2	1885.3	1878.7	1876.8
10°	1886.6	1867.4	1873.5	1866.8	1863.6
12.5°	1872.2	1851.6	1859.0	1851.1	1847.9
15°	1842.3	1823.1	1830.8	1824.2	1821.0
17.5°	1809.5	1789.0	1796.7	1789.1	1784.9
20°	1783.2	1764.0	1771.8	1760.2	1758.6
22.5°	1754.4	1735.1	1742.9	1727.5	1727.1
25°	1707.8	1686.9	1696.3	1678.2	1676.6
27.5°	1652.3	1633.1	1640.9	1622.4	1620.5
30°	1614.3	1595.0	1602.8	1583.0	1579.8
32.5°	1571.0	1553.0	1559.5	1539.8	1537.8
35°	1504.4	1486.7	1491.2	1471.5	1469.9
37.5°	1428.6	1412.5	1415.1	1393.4	1391.8
40°	1374.8	1358.7	1360.0	1337.0	1335.4
42.5°	1315.7	1299.7	1298.3	1275.3	1273.7
45°	1217.3	1201.2	1195.9	1174.5	1171.3
47.5°	1105.1	1089.0	1079.1	1061.7	1059.4
50°	1023.7	1007.6	999.1	984.2	979.4
52.5°	935.8	919.7	912.5	898.9	894.1
55°	797.3	784.5	779.2	766.1	762.8
57.5°	665.7	657.1	655.6	642.7	641.4
60°	585.7	580.9	580.7	569.3	569.3
62.5°	517.4	513.9	516.4	508.9	507.6
65°	428.2	425.0	429.8	426.5	426.5
67.5°	357.6	357.6	360.6	359.3	359.3
70°	318.3	318.3	319.9	319.9	319.9
72.5°	282.8	281.5	285.8	285.7	284.5
75°	231.3	231.3	231.3	233.0	233.0
77.5°	180.1	180.5	181.8	181.4	180.1
80°	146.0	147.6	147.6	146.0	146.0
82.5°	111.9	113.5	113.5	113.2	111.9
85°	59.1	62.3	65.6	65.6	65.6
87.5°	17.1	22.2	26.2	26.2	24.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9



TEST NUMBER: P562128

CATALOG NUMBER: SQ4-PR1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)