

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562154

Luminaire Tested: **SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562154
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4699.4 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562154
CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562154

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61		
1	100	96	92	89	94	90	86	83	79	76	74	68	66	65	58	57	56	51		
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	52	49	47	43		
3	83	74	66	61	78	69	63	57	61	56	52	53	49	46	46	43	40	37		
4	76	65	57	51	71	62	54	49	54	48	44	47	43	39	41	38	35	31		
5	70	58	50	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27		
6	65	52	44	38	60	49	42	37	44	38	33	38	34	30	33	30	27	24		
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	21		
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19		
9	52	39	32	27	48	37	30	26	33	28	23	30	25	21	26	22	19	17		
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10322	10322	10322
5°	10389	10306	10261
10°	10305	10223	10167
15°	10196	10084	10045
20°	10075	9919	9901
25°	9934	9753	9723
30°	9725	9577	9514
35°	9447	9315	9259
40°	9153	9010	8975
45°	8797	8681	8643
50°	8433	8361	8305
55°	8038	8038	7912
60°	7549	7693	7422
65°	6907	7252	6735
70°	6088	6674	5929
75°	5201	5974	5058
80°	4033	5026	4086
85°	2604	3864	3440



TEST NUMBER: P562154

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.3	2.2
10°-20°	297.4	6.3
20°-30°	441.2	9.4
30°-40°	516.2	11.0
40°-50°	513.9	10.9
50°-60°	443.8	9.4
60°-70°	319.4	6.8
70°-80°	167.5	3.6
80°-90°	41.5	0.9
90°-100°	135.9	2.9
100°-110°	386.8	8.2
110°-120°	370.6	7.9
120°-130°	293.3	6.2
130°-140°	235.4	5.0
140°-150°	184.3	3.9
150°-160°	134.8	2.9
160°-170°	83.5	1.8
170°-180°	28.3	0.6
0°-30°	844.0	18.0
0°-40°	1360.2	28.9
0°-60°	2317.9	49.3
0°-90°	2846.4	60.6
90°-120°	893.2	19.0
90°-150°	1606.2	34.2
90°-180°	1853.0	39.4
0°-180°	4699.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1119	1119	1119	1119	1119	
5°	1122	1109	1113	1110	1108	106
15°	1068	1054	1056	1054	1052	301
25°	976	960	958	952	955	449
35°	839	827	827	819	822	524
45°	674	668	665	663	662	520
55°	500	499	500	493	492	446
65°	316	326	332	319	308	314
75°	146	159	168	156	142	156
85°	25	32	36	34	32	32
90°	0	0	0	0	0	1
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	

TEST NUMBER: P562154

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1118.8	1118.8	1118.8	1118.8	1118.8
2.5°	1125.1	1115.8	1118.8	1116.3	1110.9
5°	1121.7	1109.2	1112.8	1109.8	1107.9
7.5°	1110.3	1098.7	1101.4	1098.2	1097.1
10°	1100.0	1088.5	1091.2	1087.2	1085.2
12.5°	1088.2	1075.9	1078.5	1074.6	1073.4
15°	1067.5	1054.0	1055.7	1053.7	1051.7
17.5°	1043.5	1029.8	1030.0	1026.9	1026.5
20°	1026.1	1011.6	1010.3	1006.4	1008.4
22.5°	1007.2	992.0	990.6	985.2	987.9
25°	975.8	959.5	958.1	952.2	955.1
27.5°	939.6	923.4	923.4	915.2	918.3
30°	912.8	897.3	899.0	889.2	893.0
32.5°	884.4	870.5	871.4	861.6	865.4
35°	838.8	827.3	827.0	819.2	822.1
37.5°	792.3	782.1	780.5	776.0	776.7
40°	760.0	751.3	748.1	745.2	745.2
42.5°	726.1	718.2	715.0	712.8	712.1
45°	674.2	668.4	665.3	663.3	662.4
47.5°	623.0	617.6	614.9	613.5	612.5
50°	587.5	583.6	582.5	579.6	578.6
52.5°	552.0	549.7	548.6	544.9	543.9
55°	499.7	498.8	499.7	492.8	491.9
57.5°	445.3	446.9	450.1	440.7	438.4
60°	409.1	412.9	416.9	406.0	402.2
62.5°	372.0	378.2	383.8	371.3	365.9
65°	316.4	326.0	332.2	319.1	308.5
67.5°	262.8	274.7	282.1	268.0	256.1
70°	225.7	239.2	247.4	233.3	219.8
72.5°	193.4	208.4	215.1	201.8	188.3
75°	145.9	159.4	167.6	156.4	141.9
77.5°	103.5	116.2	123.0	113.3	101.3
80°	75.9	89.4	94.6	86.5	76.9
82.5°	53.8	65.0	68.6	63.7	57.2
85°	24.6	32.4	36.5	34.5	32.5
87.5°	6.3	11.7	15.0	15.0	15.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7

TEST NUMBER: P562154

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)