

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562042

Luminaire Tested: **SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562042
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7834.2 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562042

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562042

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27		
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23		
2	85	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19		
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17		
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14		
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	12		
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11		
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10		
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9		
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8		
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7709	7709	7709
5°	7779	7718	7679
10°	7753	7700	7660
15°	7720	7672	7631
20°	7681	7632	7575
25°	7627	7576	7487
30°	7545	7490	7384
35°	7434	7368	7262
40°	7264	7185	7055
45°	6968	6846	6705
50°	6446	6291	6168
55°	5627	5500	5384
60°	4740	4702	4608
65°	4100	4117	4085
70°	3766	3785	3785
75°	3618	3618	3643
80°	3406	3443	3406
85°	2742	3049	3049



TEST NUMBER: P562042

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.0	1.0
10°-20°	226.1	2.9
20°-30°	341.0	4.4
30°-40°	406.3	5.2
40°-50°	400.6	5.1
50°-60°	306.1	3.9
60°-70°	189.4	2.4
70°-80°	107.6	1.4
80°-90°	32.7	0.4
90°-100°	421.5	5.4
100°-110°	1199.2	15.3
110°-120°	1149.0	14.7
120°-130°	909.4	11.6
130°-140°	729.9	9.3
140°-150°	571.4	7.3
150°-160°	418.1	5.3
160°-170°	259.0	3.3
170°-180°	87.9	1.1
0°-30°	646.1	8.2
0°-40°	1052.3	13.4
0°-60°	1759.0	22.5
0°-90°	2088.8	26.7
90°-120°	2769.7	35.4
90°-150°	4980.4	63.6
90°-180°	5745.0	73.3
0°-180°	7834.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	840	831	833	830	829	80
15°	808	800	803	800	799	228
25°	749	740	744	736	736	345
35°	660	652	654	646	645	412
45°	534	527	525	515	514	409
55°	350	344	342	336	335	313
65°	188	186	189	187	187	190
75°	102	102	102	102	102	107
85°	26	27	29	29	29	30
90°	0	0	0	0	0	3
95°	46	182	816	282	174	52
105°	186	283	1222	2159	2052	197
115°	346	419	927	1963	2305	341
125°	489	542	884	1468	1755	438
135°	598	648	874	1240	1402	461
145°	705	741	881	1073	1169	440
155°	805	824	902	970	1009	372
165°	890	893	913	932	946	250
175°	932	927	923	918	911	88
180°	925	925	925	925	925	



TEST NUMBER: P562042

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	835.6	835.6	835.6	835.6	835.6
2.5°	840.7	833.4	835.6	833.7	829.8
5°	839.9	830.7	833.4	830.5	829.1
7.5°	833.4	824.4	827.1	824.2	823.3
10°	827.6	819.2	821.9	819.0	817.6
12.5°	821.3	812.3	815.6	812.1	810.7
15°	808.2	799.8	803.2	800.3	798.9
17.5°	793.8	784.8	788.2	784.8	783.0
20°	782.3	773.9	777.3	772.2	771.5
22.5°	769.6	761.2	764.6	757.8	757.7
25°	749.2	740.0	744.2	736.2	735.5
27.5°	724.9	716.4	719.8	711.8	710.9
30°	708.2	699.7	703.1	694.5	693.1
32.5°	689.2	681.3	684.1	675.5	674.6
35°	660.0	652.2	654.2	645.5	644.8
37.5°	626.7	619.7	620.8	611.3	610.6
40°	603.1	596.1	596.6	586.5	585.8
42.5°	577.2	570.2	569.6	559.5	558.8
45°	534.0	527.0	524.7	515.3	513.9
47.5°	484.8	477.7	473.4	465.8	464.8
50°	449.1	442.0	438.3	431.8	429.7
52.5°	410.5	403.5	400.3	394.3	392.2
55°	349.8	344.1	341.9	336.1	334.7
57.5°	292.0	288.2	287.6	282.0	281.4
60°	256.9	254.8	254.8	249.7	249.7
62.5°	227.0	225.4	226.6	223.2	222.7
65°	187.8	186.4	188.6	187.1	187.1
67.5°	156.9	156.9	158.2	157.6	157.6
70°	139.6	139.6	140.3	140.3	140.3
72.5°	124.1	123.5	125.4	125.4	124.8
75°	101.5	101.5	101.5	102.2	102.2
77.5°	79.0	79.2	79.7	79.6	79.0
80°	64.1	64.8	64.8	64.1	64.1
82.5°	49.1	49.8	49.8	49.6	49.1
85°	25.9	27.3	28.8	28.8	28.8
87.5°	7.5	9.7	11.5	11.5	10.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.1	74.6	173.0	50.4	38.0
95°	45.7	181.5	815.9	282.4	174.1
97.5°	84.1	212.7	1256.6	899.2	616.2
100°	110.8	231.1	1352.2	1369.7	1055.1
102.5°	140.3	251.0	1331.1	1753.2	1478.5
105°	186.4	282.7	1222.1	2158.7	2052.1
107.5°	233.2	319.5	1094.8	2273.0	2367.9
110°	265.5	346.3	1021.6	2229.2	2442.4

TEST NUMBER: P562042

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	296.5	373.2	972.4	2125.8	2429.8
115°	346.4	418.6	926.7	1963.1	2305.3
117.5°	390.4	458.1	899.6	1785.3	2147.7
120°	425.5	482.3	896.8	1683.7	2031.0
122.5°	453.7	510.4	889.8	1594.5	1917.0
125°	488.8	542.1	884.5	1467.8	1754.9
127.5°	527.2	577.0	881.7	1392.1	1628.7
130°	546.9	596.7	877.5	1339.3	1545.7
132.5°	568.0	616.5	877.5	1298.2	1488.0
135°	597.9	647.7	873.9	1239.8	1401.5
137.5°	626.0	674.5	873.6	1190.5	1330.1
140°	647.1	697.0	872.2	1149.5	1283.6
142.5°	671.0	712.6	876.4	1116.9	1237.2
145°	705.1	741.2	881.0	1073.1	1169.4
147.5°	734.3	769.4	888.7	1028.8	1112.0
150°	759.6	783.7	891.5	1014.2	1072.6
152.5°	779.3	804.8	894.3	994.4	1048.7
155°	805.4	824.3	902.1	969.8	1009.3
157.5°	837.7	849.1	903.8	958.6	986.8
160°	854.6	863.2	910.9	950.1	974.2
162.5°	864.4	874.4	912.3	942.9	961.5
165°	889.8	893.2	912.6	932.3	946.0
167.5°	907.0	903.9	920.7	929.6	935.1
170°	912.6	910.9	917.9	919.8	926.7
172.5°	925.3	919.4	922.1	917.0	922.5
175°	932.0	926.8	923.2	917.7	910.9
177.5°	934.8	926.5	922.1	916.5	917.9
180°	924.9	924.9	924.9	924.9	924.9

(END OF REPORT)