

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562160

Luminaire Tested: **SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562160  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (5700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5211.9 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 45.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562160  
CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562160

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	89	94	90	86	83	79	76	74	68	66	65	58	57	56	51
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	52	49	47	43
3	83	74	66	61	78	69	63	57	61	56	52	53	49	46	46	43	40	37
4	76	65	57	51	71	62	54	49	54	48	44	47	43	39	41	38	35	31
5	70	58	50	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	37	44	38	33	38	34	30	33	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	28	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11448	11448	11448
5°	11521	11430	11380
10°	11430	11338	11276
15°	11308	11183	11141
20°	11173	11001	10980
25°	11018	10817	10784
30°	10785	10622	10551
35°	10478	10331	10269
40°	10151	9993	9953
45°	9756	9628	9585
50°	9351	9274	9211
55°	8915	8915	8775
60°	8372	8532	8230
65°	7661	8043	7471
70°	6752	7402	6577
75°	5768	6623	5611
80°	4474	5574	4532
85°	2890	4277	3822



TEST NUMBER: P562160

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.8	2.2
10°-20°	329.9	6.3
20°-30°	489.3	9.4
30°-40°	572.5	11.0
40°-50°	570.0	10.9
50°-60°	492.2	9.4
60°-70°	354.3	6.8
70°-80°	185.8	3.6
80°-90°	46.1	0.9
90°-100°	150.8	2.9
100°-110°	428.9	8.2
110°-120°	411.0	7.9
120°-130°	325.3	6.2
130°-140°	261.1	5.0
140°-150°	204.4	3.9
150°-160°	149.6	2.9
160°-170°	92.6	1.8
170°-180°	31.4	0.6
0°-30°	936.0	18.0
0°-40°	1508.5	28.9
0°-60°	2570.7	49.3
0°-90°	3156.8	60.6
90°-120°	990.7	19.0
90°-150°	1781.4	34.2
90°-180°	2055.0	39.4
0°-180°	5211.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1241	1241	1241	1241	1241	
5°	1244	1230	1234	1231	1229	118
15°	1184	1169	1171	1169	1166	334
25°	1082	1064	1063	1056	1059	498
35°	930	918	917	908	912	582
45°	748	741	738	736	735	577
55°	554	553	554	547	546	495
65°	351	362	368	354	342	348
75°	162	177	186	174	157	173
85°	27	36	40	38	36	36
90°	0	0	0	0	0	2
95°	16	65	292	101	62	19
105°	67	101	437	772	734	71
115°	124	150	332	702	825	122
125°	175	194	316	525	628	157
135°	214	232	313	444	501	165
145°	252	265	315	384	418	158
155°	288	295	323	347	361	133
165°	318	320	326	334	338	90
175°	333	332	330	328	326	32
180°	331	331	331	331	331	

TEST NUMBER: P562160

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1247.8	1237.5	1240.8	1238.0	1232.0
5°	1244.0	1230.1	1234.2	1230.9	1228.7
7.5°	1231.4	1218.5	1221.5	1218.0	1216.7
10°	1220.0	1207.2	1210.2	1205.7	1203.6
12.5°	1206.9	1193.2	1196.2	1191.8	1190.5
15°	1183.9	1169.0	1170.8	1168.6	1166.4
17.5°	1157.2	1142.1	1142.4	1138.9	1138.4
20°	1138.0	1122.0	1120.5	1116.2	1118.3
22.5°	1117.0	1100.1	1098.6	1092.6	1095.6
25°	1082.3	1064.1	1062.6	1056.1	1059.3
27.5°	1042.0	1024.1	1024.1	1015.0	1018.4
30°	1012.3	995.2	997.0	986.1	990.4
32.5°	980.8	965.4	966.4	955.5	959.8
35°	930.3	917.5	917.2	908.5	911.7
37.5°	878.7	867.4	865.6	860.6	861.4
40°	842.8	833.2	829.7	826.4	826.4
42.5°	805.2	796.5	793.0	790.6	789.7
45°	747.7	741.3	737.9	735.7	734.6
47.5°	690.9	684.9	681.9	680.4	679.3
50°	651.5	647.3	646.1	642.8	641.7
52.5°	612.2	609.6	608.5	604.3	603.2
55°	554.2	553.2	554.2	546.6	545.5
57.5°	493.9	495.6	499.1	488.8	486.2
60°	453.7	457.9	462.4	450.3	446.0
62.5°	412.6	419.4	425.7	411.8	405.8
65°	350.9	361.6	368.4	353.9	342.2
67.5°	291.4	304.7	312.9	297.3	284.0
70°	250.3	265.3	274.4	258.7	243.8
72.5°	214.5	231.2	238.5	223.8	208.8
75°	161.8	176.8	185.8	173.5	157.4
77.5°	114.8	128.9	136.4	125.6	112.4
80°	84.2	99.1	104.9	96.0	85.3
82.5°	59.7	72.1	76.1	70.7	63.4
85°	27.3	35.9	40.4	38.2	36.1
87.5°	7.0	13.0	16.6	16.6	17.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.0	26.7	61.9	18.0	13.6
95°	16.4	64.9	291.8	101.0	62.3
97.5°	30.1	76.1	449.5	321.6	220.4
100°	39.6	82.7	483.7	489.9	377.4
102.5°	50.2	89.8	476.1	627.1	528.8
105°	66.7	101.1	437.1	772.1	734.0
107.5°	83.4	114.3	391.6	813.0	847.0
110°	95.0	123.9	365.4	797.4	873.6

TEST NUMBER: P562160

CATALOG NUMBER: SQ4-PW1-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	106.0	133.5	347.8	760.4	869.1
115°	123.9	149.7	331.5	702.2	824.6
117.5°	139.6	163.9	321.8	638.6	768.2
120°	152.2	172.5	320.8	602.2	726.4
122.5°	162.3	182.6	318.3	570.3	685.7
125°	174.8	193.9	316.4	525.0	627.7
127.5°	188.6	206.4	315.4	497.9	582.5
130°	195.6	213.4	313.8	479.1	552.9
132.5°	203.2	220.5	313.8	464.3	532.2
135°	213.8	231.7	312.6	443.5	501.3
137.5°	223.9	241.3	312.5	425.8	475.7
140°	231.5	249.3	312.0	411.2	459.1
142.5°	240.0	254.9	313.5	399.5	442.5
145°	252.2	265.1	315.1	383.8	418.3
147.5°	262.7	275.2	317.9	368.0	397.8
150°	271.7	280.3	318.9	362.8	383.7
152.5°	278.8	287.9	319.9	355.7	375.1
155°	288.1	294.8	322.7	346.9	361.0
157.5°	299.6	303.7	323.3	342.9	353.0
160°	305.7	308.7	325.8	339.8	348.4
162.5°	309.2	312.8	326.3	337.3	343.9
165°	318.3	319.5	326.4	333.5	338.4
167.5°	324.4	323.3	329.3	332.5	334.5
170°	326.4	325.8	328.3	329.0	331.5
172.5°	331.0	328.9	329.8	328.0	329.9
175°	333.3	331.5	330.2	328.3	325.8
177.5°	334.4	331.4	329.8	327.8	328.3
180°	330.8	330.8	330.8	330.8	330.8

(END OF REPORT)