

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562044

Luminaire Tested: **SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562044
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8021.2 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562044
CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562044

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	85	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	12
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7893	7893	7893
5°	7964	7903	7862
10°	7939	7884	7842
15°	7904	7854	7812
20°	7864	7813	7755
25°	7809	7756	7667
30°	7725	7669	7560
35°	7610	7544	7436
40°	7437	7358	7224
45°	7135	7009	6864
50°	6600	6440	6314
55°	5760	5630	5511
60°	4855	4812	4718
65°	4198	4216	4183
70°	3858	3876	3876
75°	3704	3704	3729
80°	3485	3523	3485
85°	2805	3123	3123



TEST NUMBER: P562044

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	1.0
10°-20°	231.5	2.9
20°-30°	349.1	4.4
30°-40°	416.0	5.2
40°-50°	410.1	5.1
50°-60°	313.4	3.9
60°-70°	194.0	2.4
70°-80°	110.2	1.4
80°-90°	33.5	0.4
90°-100°	431.5	5.4
100°-110°	1227.8	15.3
110°-120°	1176.4	14.7
120°-130°	931.1	11.6
130°-140°	747.3	9.3
140°-150°	585.1	7.3
150°-160°	428.1	5.3
160°-170°	265.2	3.3
170°-180°	90.0	1.1
0°-30°	661.5	8.2
0°-40°	1077.5	13.4
0°-60°	1801.0	22.5
0°-90°	2138.7	26.7
90°-120°	2835.8	35.4
90°-150°	5099.2	63.6
90°-180°	5882.0	73.3
0°-180°	8021.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	860	850	853	850	849	82
15°	828	819	822	819	818	234
25°	767	758	762	754	753	353
35°	676	668	670	661	660	422
45°	547	540	537	528	526	419
55°	358	352	350	344	343	321
65°	192	191	193	192	192	195
75°	104	104	104	105	105	110
85°	26	28	30	30	30	31
90°	0	0	0	0	0	3
95°	47	186	835	289	178	54
105°	191	289	1251	2210	2101	202
115°	355	429	949	2010	2360	349
125°	500	555	906	1503	1797	448
135°	612	663	895	1269	1435	472
145°	722	759	902	1099	1197	451
155°	825	844	924	993	1033	381
165°	911	914	934	954	969	256
175°	954	949	945	940	933	90
180°	947	947	947	947	947	

TEST NUMBER: P562044

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	855.5	855.5	855.5	855.5	855.5
2.5°	860.8	853.3	855.5	853.6	849.6
5°	859.9	850.5	853.3	850.3	848.9
7.5°	853.3	844.1	846.8	843.8	843.0
10°	847.4	838.7	841.5	838.5	837.1
12.5°	840.9	831.7	835.0	831.4	830.0
15°	827.5	818.8	822.3	819.4	817.9
17.5°	812.8	803.5	807.0	803.6	801.7
20°	801.0	792.3	795.8	790.6	789.9
22.5°	788.0	779.4	782.8	775.9	775.8
25°	767.1	757.7	761.9	753.8	753.1
27.5°	742.2	733.5	737.0	728.7	727.9
30°	725.1	716.4	719.9	711.0	709.6
32.5°	705.6	697.5	700.5	691.6	690.7
35°	675.7	667.8	669.8	660.9	660.2
37.5°	641.7	634.5	635.6	625.9	625.2
40°	617.5	610.3	610.9	600.5	599.8
42.5°	591.0	583.8	583.2	572.8	572.1
45°	546.8	539.5	537.2	527.6	526.1
47.5°	496.3	489.1	484.7	476.9	475.9
50°	459.8	452.6	448.7	442.1	439.9
52.5°	420.3	413.1	409.8	403.8	401.6
55°	358.1	352.4	350.0	344.1	342.6
57.5°	299.0	295.1	294.4	288.7	288.1
60°	263.1	260.9	260.8	255.7	255.7
62.5°	232.4	230.8	232.0	228.6	228.0
65°	192.3	190.9	193.1	191.6	191.6
67.5°	160.6	160.6	162.0	161.4	161.4
70°	143.0	143.0	143.7	143.7	143.7
72.5°	127.0	126.5	128.4	128.3	127.8
75°	103.9	103.9	103.9	104.6	104.6
77.5°	80.9	81.1	81.6	81.5	80.9
80°	65.6	66.3	66.3	65.6	65.6
82.5°	50.3	51.0	51.0	50.8	50.3
85°	26.5	28.0	29.5	29.5	29.5
87.5°	7.7	10.0	11.8	11.8	11.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.4	76.4	177.2	51.6	38.9
95°	46.8	185.9	835.4	289.1	178.2
97.5°	86.1	217.7	1286.6	920.6	630.9
100°	113.4	236.6	1384.5	1402.4	1080.2
102.5°	143.7	257.0	1362.9	1795.1	1513.8
105°	190.8	289.4	1251.3	2210.2	2101.0
107.5°	238.7	327.1	1120.9	2327.2	2424.4
110°	271.9	354.6	1046.0	2282.4	2500.7

TEST NUMBER: P562044

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	303.5	382.1	995.6	2176.5	2487.8
115°	354.7	428.6	948.8	2010.0	2360.3
117.5°	399.7	469.0	921.1	1827.9	2199.0
120°	435.7	493.8	918.2	1723.8	2079.4
122.5°	464.5	522.6	911.0	1632.5	1962.8
125°	500.5	555.1	905.6	1502.8	1796.8
127.5°	539.8	590.8	902.7	1425.3	1667.5
130°	559.9	611.0	898.4	1371.3	1582.5
132.5°	581.5	631.2	898.4	1329.1	1523.5
135°	612.1	663.2	894.8	1269.4	1434.9
137.5°	640.9	690.6	894.4	1218.9	1361.8
140°	662.5	713.6	893.0	1177.0	1314.3
142.5°	687.0	729.6	897.3	1143.5	1266.7
145°	722.0	758.9	902.0	1098.7	1197.3
147.5°	751.8	787.8	909.9	1053.4	1138.6
150°	777.8	802.4	912.8	1038.4	1098.2
152.5°	797.9	824.0	915.7	1018.1	1073.7
155°	824.6	843.9	923.6	992.9	1033.4
157.5°	857.7	869.3	925.4	981.5	1010.4
160°	875.0	883.8	932.6	972.8	997.4
162.5°	885.1	895.3	934.0	965.4	984.4
165°	911.0	914.5	934.4	954.5	968.6
167.5°	928.6	925.5	942.7	951.8	957.4
170°	934.4	932.6	939.8	941.8	948.8
172.5°	947.4	941.4	944.1	938.8	944.5
175°	954.2	948.9	945.2	939.6	932.6
177.5°	957.1	948.6	944.1	938.4	939.8
180°	947.0	947.0	947.0	947.0	947.0

(END OF REPORT)