

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562055

Luminaire Tested: **SQ4-PR1-125U-075D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562055
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-075D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8873.7 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562055
CATALOG NUMBER: SQ4-PR1-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562055

CATALOG NUMBER: SQ4-PR1-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35				
1	95	91	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30				
2	86	79	73	68	78	72	67	63	58	55	52	45	43	41	34	32	31	26				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	26	22				
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19				
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17				
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15				
7	56	44	37	31	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12				
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13	10				
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11546	11546	11546
5°	11649	11559	11500
10°	11612	11532	11471
15°	11561	11490	11428
20°	11503	11430	11344
25°	11422	11346	11213
30°	11299	11218	11057
35°	11132	11034	10877
40°	10878	10761	10567
45°	10434	10252	10042
50°	9654	9422	9236
55°	8426	8236	8062
60°	7100	7041	6901
65°	6141	6165	6117
70°	5641	5670	5670
75°	5418	5418	5458
80°	5095	5154	5095
85°	4107	4563	4563



TEST NUMBER: P562055

CATALOG NUMBER: SQ4-PR1-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.3	1.3
10°-20°	338.6	3.8
20°-30°	510.7	5.8
30°-40°	608.5	6.9
40°-50°	599.9	6.8
50°-60°	458.5	5.2
60°-70°	283.7	3.2
70°-80°	161.2	1.8
80°-90°	49.0	0.6
90°-100°	421.5	4.7
100°-110°	1199.2	13.5
110°-120°	1149.0	12.9
120°-130°	909.4	10.2
130°-140°	729.9	8.2
140°-150°	571.4	6.4
150°-160°	418.1	4.7
160°-170°	259.0	2.9
170°-180°	87.9	1.0
0°-30°	967.6	10.9
0°-40°	1576.0	17.8
0°-60°	2634.4	29.7
0°-90°	3128.3	35.3
90°-120°	2769.7	31.2
90°-150°	4980.4	56.1
90°-180°	5745.0	64.7
0°-180°	8873.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1258	1244	1248	1244	1242	119
15°	1210	1198	1203	1198	1196	342
25°	1122	1108	1114	1103	1102	516
35°	988	977	980	967	966	617
45°	800	789	786	772	770	613
55°	524	515	512	503	501	469
65°	281	279	282	280	280	285
75°	152	152	152	153	153	160
85°	39	41	43	43	43	45
90°	0	0	0	0	0	3
95°	46	182	816	282	174	52
105°	186	283	1222	2159	2052	197
115°	346	419	927	1963	2305	341
125°	489	542	884	1468	1755	438
135°	598	648	874	1240	1402	461
145°	705	741	881	1073	1169	440
155°	805	824	902	970	1009	372
165°	890	893	913	932	946	250
175°	932	927	923	918	911	88
180°	925	925	925	925	925	



TEST NUMBER: P562055

CATALOG NUMBER: SQ4-PR1-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1251.4	1251.4	1251.4	1251.4	1251.4
2.5°	1259.1	1248.2	1251.4	1248.6	1242.7
5°	1257.8	1244.1	1248.1	1243.8	1241.7
7.5°	1248.1	1234.6	1238.6	1234.3	1233.0
10°	1239.5	1226.9	1230.9	1226.5	1224.4
12.5°	1230.0	1216.5	1221.4	1216.2	1214.1
15°	1210.4	1197.8	1202.9	1198.5	1196.4
17.5°	1188.8	1175.4	1180.4	1175.4	1172.7
20°	1171.6	1159.0	1164.1	1156.5	1155.4
22.5°	1152.6	1140.0	1145.1	1134.9	1134.7
25°	1122.0	1108.3	1114.5	1102.6	1101.5
27.5°	1085.6	1072.9	1078.0	1065.9	1064.7
30°	1060.6	1047.9	1053.0	1040.1	1037.9
32.5°	1032.1	1020.3	1024.6	1011.6	1010.4
35°	988.4	976.8	979.7	966.8	965.7
37.5°	938.6	928.0	929.7	915.5	914.4
40°	903.2	892.7	893.5	878.4	877.4
42.5°	864.4	853.9	853.0	837.9	836.8
45°	799.7	789.2	785.7	771.7	769.6
47.5°	726.0	715.5	709.0	697.5	696.1
50°	672.6	662.0	656.4	646.6	643.5
52.5°	614.8	604.3	599.5	590.6	587.4
55°	523.8	515.4	512.0	503.3	501.2
57.5°	437.4	431.7	430.7	422.3	421.4
60°	384.8	381.6	381.6	374.0	374.0
62.5°	339.9	337.6	339.3	334.3	333.5
65°	281.3	279.2	282.4	280.2	280.2
67.5°	235.0	235.0	236.9	236.0	236.0
70°	209.1	209.1	210.2	210.2	210.2
72.5°	185.8	185.0	187.8	187.7	186.9
75°	152.0	152.0	152.0	153.1	153.1
77.5°	118.3	118.6	119.4	119.2	118.3
80°	95.9	97.0	97.0	95.9	95.9
82.5°	73.5	74.6	74.6	74.4	73.5
85°	38.8	40.9	43.1	43.1	43.1
87.5°	11.2	14.6	17.2	17.2	16.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.1	74.6	173.0	50.4	38.0
95°	45.7	181.5	815.9	282.4	174.1
97.5°	84.1	212.7	1256.6	899.2	616.2
100°	110.8	231.1	1352.2	1369.7	1055.1
102.5°	140.3	251.0	1331.1	1753.2	1478.5
105°	186.4	282.7	1222.1	2158.7	2052.1
107.5°	233.2	319.5	1094.8	2273.0	2367.9
110°	265.5	346.3	1021.6	2229.2	2442.4



TEST NUMBER: P562055

CATALOG NUMBER: SQ4-PR1-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	296.5	373.2	972.4	2125.8	2429.8
115°	346.4	418.6	926.7	1963.1	2305.3
117.5°	390.4	458.1	899.6	1785.3	2147.7
120°	425.5	482.3	896.8	1683.7	2031.0
122.5°	453.7	510.4	889.8	1594.5	1917.0
125°	488.8	542.1	884.5	1467.8	1754.9
127.5°	527.2	577.0	881.7	1392.1	1628.7
130°	546.9	596.7	877.5	1339.3	1545.7
132.5°	568.0	616.5	877.5	1298.2	1488.0
135°	597.9	647.7	873.9	1239.8	1401.5
137.5°	626.0	674.5	873.6	1190.5	1330.1
140°	647.1	697.0	872.2	1149.5	1283.6
142.5°	671.0	712.6	876.4	1116.9	1237.2
145°	705.1	741.2	881.0	1073.1	1169.4
147.5°	734.3	769.4	888.7	1028.8	1112.0
150°	759.6	783.7	891.5	1014.2	1072.6
152.5°	779.3	804.8	894.3	994.4	1048.7
155°	805.4	824.3	902.1	969.8	1009.3
157.5°	837.7	849.1	903.8	958.6	986.8
160°	854.6	863.2	910.9	950.1	974.2
162.5°	864.4	874.4	912.3	942.9	961.5
165°	889.8	893.2	912.6	932.3	946.0
167.5°	907.0	903.9	920.7	929.6	935.1
170°	912.6	910.9	917.9	919.8	926.7
172.5°	925.3	919.4	922.1	917.0	922.5
175°	932.0	926.8	923.2	917.7	910.9
177.5°	934.8	926.5	922.1	916.5	917.9
180°	924.9	924.9	924.9	924.9	924.9

(END OF REPORT)