

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562065

Luminaire Tested: **SQ4-PR1-125U-100D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562065
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-100D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9422.6 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 83.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562065
CATALOG NUMBER: SQ4-PR1-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562065

CATALOG NUMBER: SQ4-PR1-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	56	46	39	34	39	33	30	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	49	38	31	27	32	27	23	26	22	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14507	14507	14507
5°	14638	14525	14450
10°	14591	14490	14413
15°	14527	14437	14359
20°	14455	14361	14255
25°	14353	14256	14090
30°	14198	14097	13894
35°	13988	13866	13668
40°	13669	13523	13277
45°	13112	12882	12617
50°	12130	11839	11605
55°	10587	10348	10131
60°	8922	8846	8673
65°	7717	7746	7687
70°	7086	7124	7124
75°	6809	6809	6855
80°	6402	6477	6402
85°	5166	5738	5738



TEST NUMBER: P562065

CATALOG NUMBER: SQ4-PR1-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	1.6
10°-20°	425.4	4.5
20°-30°	641.7	6.8
30°-40°	764.6	8.1
40°-50°	753.8	8.0
50°-60°	576.1	6.1
60°-70°	356.5	3.8
70°-80°	202.5	2.1
80°-90°	61.6	0.7
90°-100°	402.9	4.3
100°-110°	1146.3	12.2
110°-120°	1098.3	11.7
120°-130°	869.3	9.2
130°-140°	697.7	7.4
140°-150°	546.2	5.8
150°-160°	399.7	4.2
160°-170°	247.6	2.6
170°-180°	84.0	0.9
0°-30°	1215.8	12.9
0°-40°	1980.4	21.0
0°-60°	3310.2	35.1
0°-90°	3930.8	41.7
90°-120°	2647.5	28.1
90°-150°	4760.6	50.5
90°-180°	5492.0	58.3
0°-180°	9422.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1580	1563	1568	1563	1560	150
15°	1521	1505	1512	1506	1503	429
25°	1410	1393	1400	1386	1384	649
35°	1242	1227	1231	1215	1214	775
45°	1005	992	987	970	967	770
55°	658	648	643	632	630	590
65°	354	351	355	352	352	358
75°	191	191	191	192	192	202
85°	49	51	54	54	54	57
90°	0	0	0	0	0	4
95°	44	174	780	270	166	50
105°	178	270	1168	2063	1962	188
115°	331	400	886	1876	2204	326
125°	467	518	846	1403	1678	418
135°	572	619	835	1185	1340	441
145°	674	708	842	1026	1118	421
155°	770	788	862	927	965	356
165°	850	854	872	891	904	239
175°	891	886	882	877	871	84
180°	884	884	884	884	884	

TEST NUMBER: P562065

CATALOG NUMBER: SQ4-PR1-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1572.4	1572.4	1572.4	1572.4	1572.4
2.5°	1582.2	1568.4	1572.4	1569.0	1561.6
5°	1580.5	1563.3	1568.3	1562.9	1560.2
7.5°	1568.3	1551.4	1556.4	1551.0	1549.4
10°	1557.5	1541.6	1546.7	1541.2	1538.5
12.5°	1545.6	1528.6	1534.7	1528.2	1525.5
15°	1520.9	1505.0	1511.5	1506.0	1503.3
17.5°	1493.8	1476.9	1483.3	1477.0	1473.5
20°	1472.2	1456.3	1462.7	1453.2	1451.9
22.5°	1448.3	1432.5	1438.9	1426.1	1425.9
25°	1409.9	1392.7	1400.4	1385.5	1384.1
27.5°	1364.1	1348.2	1354.6	1339.4	1337.8
30°	1332.7	1316.8	1323.2	1306.9	1304.2
32.5°	1296.9	1282.1	1287.4	1271.2	1269.6
35°	1241.9	1227.4	1231.1	1214.8	1213.5
37.5°	1179.4	1166.1	1168.3	1150.4	1149.0
40°	1134.9	1121.7	1122.8	1103.8	1102.4
42.5°	1086.2	1072.9	1071.8	1052.8	1051.5
45°	1004.9	991.7	987.3	969.7	967.0
47.5°	912.3	899.0	890.9	876.5	874.6
50°	845.1	831.9	824.8	812.5	808.5
52.5°	772.5	759.3	753.3	742.1	738.1
55°	658.2	647.6	643.3	632.4	629.8
57.5°	549.6	542.4	541.2	530.6	529.6
60°	483.5	479.5	479.4	470.0	470.0
62.5°	427.2	424.2	426.3	420.1	419.0
65°	353.5	350.8	354.8	352.1	352.1
67.5°	295.2	295.2	297.7	296.6	296.6
70°	262.7	262.7	264.1	264.1	264.1
72.5°	233.5	232.4	235.9	235.9	234.8
75°	191.0	191.0	191.0	192.3	192.3
77.5°	148.7	149.0	150.1	149.8	148.7
80°	120.5	121.9	121.9	120.5	120.5
82.5°	92.4	93.7	93.7	93.4	92.4
85°	48.8	51.4	54.2	54.2	54.2
87.5°	14.1	18.3	21.7	21.6	20.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.4	71.3	165.4	48.1	36.3
95°	43.7	173.5	779.9	269.9	166.4
97.5°	80.3	203.3	1201.1	859.5	589.0
100°	105.9	220.9	1292.6	1309.2	1008.5
102.5°	134.1	240.0	1272.4	1675.9	1413.2
105°	178.2	270.2	1168.2	2063.4	1961.5
107.5°	222.9	305.4	1046.5	2172.7	2263.4
110°	253.8	331.0	976.6	2130.9	2334.7



TEST NUMBER: P562065

CATALOG NUMBER: SQ4-PR1-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.4	356.7	929.5	2032.0	2322.6
115°	331.1	400.1	885.8	1876.5	2203.6
117.5°	373.1	437.9	859.9	1706.5	2053.0
120°	406.8	461.0	857.2	1609.4	1941.3
122.5°	433.7	487.9	850.5	1524.1	1832.4
125°	467.3	518.2	845.5	1403.0	1677.5
127.5°	503.9	551.6	842.8	1330.6	1556.8
130°	522.7	570.4	838.7	1280.2	1477.4
132.5°	542.9	589.3	838.7	1240.9	1422.3
135°	571.5	619.1	835.4	1185.1	1339.6
137.5°	598.4	644.7	835.0	1137.9	1271.4
140°	618.5	666.2	833.7	1098.8	1227.0
142.5°	641.4	681.2	837.7	1067.6	1182.6
145°	674.0	708.5	842.1	1025.7	1117.7
147.5°	701.9	735.4	849.5	983.4	1063.0
150°	726.1	749.1	852.2	969.4	1025.3
152.5°	744.9	769.3	854.9	950.5	1002.4
155°	769.8	787.9	862.3	927.0	964.8
157.5°	800.7	811.6	863.9	916.3	943.3
160°	816.9	825.1	870.7	908.2	931.2
162.5°	826.3	835.8	872.0	901.3	919.1
165°	850.5	853.8	872.3	891.1	904.3
167.5°	867.0	864.0	880.1	888.6	893.9
170°	872.3	870.7	877.4	879.2	885.8
172.5°	884.4	878.9	881.4	876.5	881.8
175°	890.8	885.9	882.4	877.2	870.7
177.5°	893.5	885.6	881.4	876.1	877.4
180°	884.1	884.1	884.1	884.1	884.1

(END OF REPORT)