

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562168

Luminaire Tested: **SQ4-PW1-025U-100D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562168  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-100D-92765-1D-UNV-STD-W-4 (3000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5710.8 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 56.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562168  
CATALOG NUMBER: SQ4-PW1-025U-100D-92765-1D-UNV-STD-W-4 (3000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562168

CATALOG NUMBER: SQ4-PW1-025U-100D-92765-1D-UNV-STD-W-4 (3000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	69	64	62	61	57
2	93	85	79	74	87	80	75	70	72	67	64	64	60	57	56	54	51	48
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	47	44	40
4	78	66	58	52	73	63	56	50	56	51	46	50	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	24
8	57	44	36	31	53	42	35	29	38	32	27	34	29	25	31	26	23	21
9	53	40	33	27	50	38	31	26	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13850	13850	13850
5°	13939	13829	13768
10°	13828	13716	13642
15°	13682	13530	13479
20°	13518	13311	13284
25°	13330	13087	13047
30°	13047	12850	12766
35°	12677	12499	12424
40°	12281	12091	12043
45°	11804	11649	11597
50°	11315	11220	11144
55°	10787	10787	10616
60°	10129	10324	9957
65°	9269	9730	9038
70°	8171	8956	7955
75°	6976	8014	6791
80°	5409	6748	5483
85°	3504	5176	4615



TEST NUMBER: P562168

CATALOG NUMBER: SQ4-PW1-025U-100D-92765-1D-UNV-STD-W-4 (3000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.4	2.5
10°-20°	399.1	7.0
20°-30°	592.0	10.4
30°-40°	692.7	12.1
40°-50°	689.6	12.1
50°-60°	595.5	10.4
60°-70°	428.6	7.5
70°-80°	224.8	3.9
80°-90°	55.7	1.0
90°-100°	138.8	2.4
100°-110°	394.8	6.9
110°-120°	378.2	6.6
120°-130°	299.4	5.2
130°-140°	240.3	4.2
140°-150°	188.1	3.3
150°-160°	137.6	2.4
160°-170°	85.3	1.5
170°-180°	28.9	0.5
0°-30°	1132.4	19.8
0°-40°	1825.1	32.0
0°-60°	3110.2	54.5
0°-90°	3819.4	66.9
90°-120°	911.8	16.0
90°-150°	1639.5	28.7
90°-180°	1891.0	33.1
0°-180°	5710.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1501	1501	1501	1501	1501	
5°	1505	1488	1493	1489	1487	143
15°	1432	1414	1416	1414	1411	404
25°	1309	1287	1286	1278	1282	602
35°	1126	1110	1110	1099	1103	704
45°	905	897	893	890	889	698
55°	671	669	671	661	660	598
65°	425	438	446	428	414	421
75°	196	214	225	210	190	210
85°	33	43	49	46	44	44
90°	0	0	0	0	0	2
95°	15	60	269	93	57	17
105°	61	93	402	711	676	65
115°	114	138	305	646	759	112
125°	161	178	291	483	578	144
135°	197	213	288	408	461	152
145°	232	244	290	353	385	145
155°	265	271	297	319	332	123
165°	293	294	300	307	311	82
175°	307	305	304	302	300	29
180°	304	304	304	304	304	

TEST NUMBER: P562168

CATALOG NUMBER: SQ4-PW1-025U-100D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1501.2	1501.2	1501.2	1501.2	1501.2
2.5°	1509.6	1497.2	1501.2	1497.8	1490.6
5°	1505.1	1488.3	1493.2	1489.2	1486.6
7.5°	1489.8	1474.3	1477.9	1473.6	1472.1
10°	1476.0	1460.5	1464.1	1458.8	1456.2
12.5°	1460.2	1443.6	1447.2	1441.9	1440.3
15°	1432.4	1414.3	1416.5	1413.8	1411.2
17.5°	1400.1	1381.8	1382.1	1377.9	1377.4
20°	1376.8	1357.4	1355.7	1350.5	1353.0
22.5°	1351.4	1331.0	1329.2	1321.9	1325.5
25°	1309.4	1287.4	1285.6	1277.7	1281.6
27.5°	1260.7	1239.0	1239.0	1228.0	1232.1
30°	1224.7	1204.1	1206.2	1193.1	1198.3
32.5°	1186.7	1168.0	1169.2	1156.1	1161.3
35°	1125.5	1110.0	1109.7	1099.2	1103.1
37.5°	1063.1	1049.4	1047.2	1041.2	1042.2
40°	1019.7	1008.1	1003.9	999.9	999.9
42.5°	974.2	963.6	959.4	956.5	955.5
45°	904.7	896.9	892.8	890.1	888.8
47.5°	835.9	828.7	825.0	823.2	821.9
50°	788.3	783.1	781.7	777.7	776.4
52.5°	740.7	737.6	736.2	731.1	729.8
55°	670.6	669.3	670.6	661.3	660.0
57.5°	597.6	599.6	603.9	591.4	588.3
60°	548.9	554.1	559.5	544.8	539.6
62.5°	499.2	507.4	515.0	498.2	491.0
65°	424.6	437.5	445.7	428.2	414.0
67.5°	352.6	368.6	378.5	359.7	343.6
70°	302.9	321.0	332.0	313.0	294.9
72.5°	259.5	279.7	288.6	270.7	252.6
75°	195.7	213.9	224.8	209.9	190.5
77.5°	138.9	155.9	165.1	152.0	136.0
80°	101.8	119.9	127.0	116.1	103.2
82.5°	72.2	87.2	92.1	85.5	76.7
85°	33.1	43.4	48.9	46.2	43.6
87.5°	8.5	15.7	20.1	20.1	21.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.6	24.6	57.0	16.6	12.5
95°	15.1	59.8	268.6	93.0	57.3
97.5°	27.7	70.0	413.7	296.0	202.8
100°	36.5	76.1	445.1	450.9	347.3
102.5°	46.2	82.6	438.2	577.2	486.7
105°	61.4	93.1	402.3	710.6	675.5
107.5°	76.8	105.2	360.4	748.3	779.5
110°	87.4	114.0	336.3	733.9	804.0

TEST NUMBER: P562168

CATALOG NUMBER: SQ4-PW1-025U-100D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	97.6	122.8	320.1	699.8	799.9
115°	114.0	137.8	305.1	646.3	758.9
117.5°	128.5	150.8	296.1	587.7	707.0
120°	140.1	158.8	295.2	554.3	668.6
122.5°	149.3	168.0	292.9	524.9	631.1
125°	160.9	178.5	291.2	483.2	577.7
127.5°	173.5	190.0	290.2	458.3	536.1
130°	180.0	196.4	288.9	440.9	508.8
132.5°	187.0	202.9	288.9	427.3	489.8
135°	196.8	213.2	287.7	408.2	461.4
137.5°	206.1	222.0	287.6	391.9	437.9
140°	213.0	229.4	287.1	378.4	422.6
142.5°	220.9	234.6	288.5	367.7	407.3
145°	232.1	244.0	290.0	353.2	384.9
147.5°	241.7	253.3	292.6	338.7	366.1
150°	250.1	258.0	293.5	333.9	353.1
152.5°	256.6	264.9	294.4	327.3	345.2
155°	265.1	271.3	297.0	319.3	332.3
157.5°	275.8	279.5	297.5	315.6	324.9
160°	281.3	284.2	299.9	312.8	320.7
162.5°	284.6	287.9	300.3	310.4	316.5
165°	292.9	294.0	300.4	306.9	311.4
167.5°	298.6	297.6	303.1	306.0	307.8
170°	300.4	299.9	302.2	302.8	305.1
172.5°	304.6	302.7	303.6	301.9	303.7
175°	306.8	305.1	303.9	302.1	299.9
177.5°	307.7	305.0	303.6	301.7	302.2
180°	304.5	304.5	304.5	304.5	304.5

(END OF REPORT)