

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562081

Luminaire Tested: **SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562081  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10951.9 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 97.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562081  
CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562081

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39	34
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34	29
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	41	45	40	35	38	34	30	31	28	26	22
6	63	51	43	38	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19215	19215	19215
5°	19388	19239	19139
10°	19327	19192	19091
15°	19242	19122	19019
20°	19145	19022	18881
25°	19010	18883	18663
30°	18806	18671	18404
35°	18528	18366	18103
40°	18106	17911	17587
45°	17368	17063	16712
50°	16067	15681	15371
55°	14023	13706	13417
60°	11817	11717	11487
65°	10221	10261	10182
70°	9388	9436	9436
75°	9015	9015	9079
80°	8485	8575	8485
85°	6838	7601	7601



TEST NUMBER: P562081

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	196.9	1.8
10°-20°	563.5	5.1
20°-30°	849.9	7.8
30°-40°	1012.7	9.2
40°-50°	998.4	9.1
50°-60°	763.0	7.0
60°-70°	472.2	4.3
70°-80°	268.2	2.4
80°-90°	81.6	0.7
90°-100°	421.5	3.8
100°-110°	1199.2	10.9
110°-120°	1149.0	10.5
120°-130°	909.4	8.3
130°-140°	729.9	6.7
140°-150°	571.4	5.2
150°-160°	418.1	3.8
160°-170°	259.0	2.4
170°-180°	87.9	0.8
0°-30°	1610.4	14.7
0°-40°	2623.0	24.0
0°-60°	4384.5	40.0
0°-90°	5206.5	47.5
90°-120°	2769.7	25.3
90°-150°	4980.4	45.5
90°-180°	5745.0	52.5
0°-180°	10951.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2083	2083	2083	2083	2083	
5°	2093	2071	2077	2070	2066	199
15°	2014	1994	2002	1995	1991	568
25°	1867	1845	1855	1835	1833	859
35°	1645	1626	1631	1609	1607	1027
45°	1331	1314	1308	1284	1281	1020
55°	872	858	852	838	834	781
65°	468	465	470	466	466	474
75°	253	253	253	255	255	267
85°	65	68	72	72	72	75
90°	0	0	0	0	0	4
95°	46	182	816	282	174	52
105°	186	283	1222	2159	2052	197
115°	346	419	927	1963	2305	341
125°	489	542	884	1468	1755	438
135°	598	648	874	1240	1402	461
145°	705	741	881	1073	1169	440
155°	805	824	902	970	1009	372
165°	890	893	913	932	946	250
175°	932	927	923	918	911	88
180°	925	925	925	925	925	

TEST NUMBER: P562081

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2082.7	2082.7	2082.7	2082.7	2082.7
2.5°	2095.6	2077.4	2082.7	2078.2	2068.3
5°	2093.4	2070.6	2077.3	2070.0	2066.5
7.5°	2077.3	2054.9	2061.5	2054.3	2052.2
10°	2063.0	2041.9	2048.6	2041.3	2037.8
12.5°	2047.2	2024.7	2032.8	2024.1	2020.6
15°	2014.5	1993.5	2002.0	1994.7	1991.2
17.5°	1978.6	1956.2	1964.6	1956.3	1951.7
20°	1949.9	1928.9	1937.4	1924.8	1923.0
22.5°	1918.4	1897.3	1905.8	1888.9	1888.6
25°	1867.4	1844.6	1854.9	1835.1	1833.3
27.5°	1806.8	1785.7	1794.2	1774.1	1772.0
30°	1765.2	1744.1	1752.6	1731.0	1727.5
32.5°	1717.8	1698.2	1705.3	1683.7	1681.6
35°	1645.0	1625.7	1630.6	1609.1	1607.3
37.5°	1562.1	1544.6	1547.4	1523.7	1521.9
40°	1503.3	1485.7	1487.1	1462.0	1460.2
42.5°	1438.7	1421.1	1419.7	1394.5	1392.8
45°	1331.1	1313.5	1307.7	1284.3	1280.8
47.5°	1208.4	1190.8	1180.0	1160.9	1158.5
50°	1119.4	1101.8	1092.5	1076.2	1070.9
52.5°	1023.2	1005.7	997.8	982.9	977.7
55°	871.8	857.8	852.1	837.7	834.1
57.5°	728.0	718.5	716.8	702.8	701.4
60°	640.4	635.1	635.0	622.5	622.5
62.5°	565.8	561.9	564.7	556.4	555.0
65°	468.2	464.7	470.0	466.4	466.4
67.5°	391.1	391.1	394.3	392.9	392.9
70°	348.0	348.0	349.8	349.8	349.8
72.5°	309.3	307.9	312.5	312.5	311.1
75°	252.9	252.9	252.9	254.7	254.7
77.5°	197.0	197.3	198.8	198.4	197.0
80°	159.7	161.4	161.4	159.7	159.7
82.5°	122.3	124.1	124.1	123.7	122.3
85°	64.6	68.1	71.8	71.8	71.8
87.5°	18.7	24.3	28.7	28.7	27.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.1	74.6	173.0	50.4	38.0
95°	45.7	181.5	815.9	282.4	174.1
97.5°	84.1	212.7	1256.6	899.2	616.2
100°	110.8	231.1	1352.2	1369.7	1055.1
102.5°	140.3	251.0	1331.1	1753.2	1478.5
105°	186.4	282.7	1222.1	2158.7	2052.1
107.5°	233.2	319.5	1094.8	2273.0	2367.9
110°	265.5	346.3	1021.6	2229.2	2442.4

TEST NUMBER: P562081

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	296.5	373.2	972.4	2125.8	2429.8
115°	346.4	418.6	926.7	1963.1	2305.3
117.5°	390.4	458.1	899.6	1785.3	2147.7
120°	425.5	482.3	896.8	1683.7	2031.0
122.5°	453.7	510.4	889.8	1594.5	1917.0
125°	488.8	542.1	884.5	1467.8	1754.9
127.5°	527.2	577.0	881.7	1392.1	1628.7
130°	546.9	596.7	877.5	1339.3	1545.7
132.5°	568.0	616.5	877.5	1298.2	1488.0
135°	597.9	647.7	873.9	1239.8	1401.5
137.5°	626.0	674.5	873.6	1190.5	1330.1
140°	647.1	697.0	872.2	1149.5	1283.6
142.5°	671.0	712.6	876.4	1116.9	1237.2
145°	705.1	741.2	881.0	1073.1	1169.4
147.5°	734.3	769.4	888.7	1028.8	1112.0
150°	759.6	783.7	891.5	1014.2	1072.6
152.5°	779.3	804.8	894.3	994.4	1048.7
155°	805.4	824.3	902.1	969.8	1009.3
157.5°	837.7	849.1	903.8	958.6	986.8
160°	854.6	863.2	910.9	950.1	974.2
162.5°	864.4	874.4	912.3	942.9	961.5
165°	889.8	893.2	912.6	932.3	946.0
167.5°	907.0	903.9	920.7	929.6	935.1
170°	912.6	910.9	917.9	919.8	926.7
172.5°	925.3	919.4	922.1	917.0	922.5
175°	932.0	926.8	923.2	917.7	910.9
177.5°	934.8	926.5	922.1	916.5	917.9
180°	924.9	924.9	924.9	924.9	924.9

(END OF REPORT)