

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562182

Luminaire Tested: **SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562182
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6888.4 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562182
CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562182

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72
1	103	98	94	91	97	93	90	87	84	81	79	76	74	72	68	66	65	61
2	94	86	80	75	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	43
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	47	44	40	37
5	72	60	52	45	68	57	50	44	52	46	41	47	42	38	43	39	35	32
6	67	54	46	40	63	52	44	38	47	41	36	43	37	33	39	34	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	38	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17956	17956	17956
5°	18072	17929	17850
10°	17928	17783	17687
15°	17737	17542	17476
20°	17526	17257	17222
25°	17282	16967	16915
30°	16916	16660	16550
35°	16435	16203	16107
40°	15922	15675	15613
45°	15304	15102	15035
50°	14669	14546	14447
55°	13985	13985	13763
60°	13131	13384	12909
65°	12016	12616	11717
70°	10593	11610	10315
75°	9047	10391	8801
80°	7013	8745	7104
85°	4541	6711	5992



TEST NUMBER: P562182

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	2.7
10°-20°	517.4	7.5
20°-30°	767.5	11.1
30°-40°	898.0	13.0
40°-50°	894.0	13.0
50°-60°	772.0	11.2
60°-70°	555.7	8.1
70°-80°	291.4	4.2
80°-90°	72.3	1.0
90°-100°	142.1	2.1
100°-110°	404.2	5.9
110°-120°	387.3	5.6
120°-130°	306.6	4.5
130°-140°	246.0	3.6
140°-150°	192.6	2.8
150°-160°	140.9	2.0
160°-170°	87.3	1.3
170°-180°	29.6	0.4
0°-30°	1468.2	21.3
0°-40°	2366.2	34.4
0°-60°	4032.2	58.5
0°-90°	4951.6	71.9
90°-120°	933.6	13.6
90°-150°	1678.9	24.4
90°-180°	1937.0	28.1
0°-180°	6888.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1951	1930	1936	1931	1927	185
15°	1857	1834	1836	1833	1830	523
25°	1698	1669	1667	1656	1662	781
35°	1459	1439	1439	1425	1430	912
45°	1173	1163	1157	1154	1152	905
55°	869	868	869	857	856	776
65°	550	567	578	555	537	545
75°	254	277	292	272	247	272
85°	43	56	63	60	57	57
90°	0	0	0	0	0	2
95°	15	61	275	95	59	18
105°	63	95	412	728	692	66
115°	117	141	312	662	777	115
125°	165	183	298	495	592	147
135°	202	218	295	418	472	156
145°	238	250	297	362	394	148
155°	272	278	304	327	340	126
165°	300	301	308	314	319	84
175°	314	312	311	309	307	30
180°	312	312	312	312	312	

TEST NUMBER: P562182

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1946.2	1946.2	1946.2	1946.2	1946.2
2.5°	1957.2	1941.1	1946.2	1941.9	1932.5
5°	1951.3	1929.5	1935.9	1930.7	1927.3
7.5°	1931.4	1911.3	1916.0	1910.5	1908.5
10°	1913.6	1893.5	1898.2	1891.2	1887.9
12.5°	1893.0	1871.6	1876.2	1869.3	1867.3
15°	1857.0	1833.6	1836.5	1832.9	1829.6
17.5°	1815.2	1791.4	1791.9	1786.4	1785.7
20°	1785.0	1759.9	1757.6	1750.8	1754.1
22.5°	1752.1	1725.6	1723.3	1713.8	1718.5
25°	1697.6	1669.1	1666.7	1656.5	1661.6
27.5°	1634.5	1606.3	1606.3	1592.1	1597.4
30°	1587.8	1561.0	1563.8	1546.8	1553.5
32.5°	1538.4	1514.3	1515.8	1498.8	1505.5
35°	1459.2	1439.1	1438.6	1425.0	1430.1
37.5°	1378.3	1360.5	1357.7	1349.8	1351.2
40°	1322.0	1307.0	1301.5	1296.3	1296.3
42.5°	1263.1	1249.3	1243.9	1240.0	1238.7
45°	1172.9	1162.8	1157.4	1154.0	1152.3
47.5°	1083.7	1074.3	1069.6	1067.2	1065.5
50°	1022.0	1015.3	1013.4	1008.2	1006.5
52.5°	960.2	956.2	954.4	947.9	946.2
55°	869.4	867.7	869.4	857.3	855.6
57.5°	774.7	777.4	782.9	766.7	762.7
60°	711.6	718.3	725.3	706.3	699.6
62.5°	647.1	657.9	667.7	645.9	636.5
65°	550.4	567.2	577.9	555.1	536.7
67.5°	457.1	477.9	490.7	466.3	445.5
70°	392.7	416.1	430.4	405.9	382.4
72.5°	336.4	362.6	374.1	351.0	327.5
75°	253.8	277.2	291.5	272.1	246.9
77.5°	180.0	202.2	214.0	197.1	176.3
80°	132.0	155.5	164.6	150.5	133.7
82.5°	93.6	113.1	119.3	110.9	99.5
85°	42.9	56.3	63.4	59.9	56.6
87.5°	11.0	20.4	26.1	26.1	27.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	25.1	58.3	17.0	12.8
95°	15.4	61.2	275.0	95.2	58.7
97.5°	28.3	71.7	423.6	303.1	207.7
100°	37.3	77.9	455.8	461.7	355.7
102.5°	47.3	84.6	448.7	591.0	498.4
105°	62.8	95.3	412.0	727.7	691.7
107.5°	78.6	107.7	369.0	766.2	798.2
110°	89.5	116.7	344.4	751.5	823.3

TEST NUMBER: P562182

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	99.9	125.8	327.8	716.6	819.1
115°	116.8	141.1	312.4	661.8	777.1
117.5°	131.6	154.4	303.3	601.8	724.0
120°	143.4	162.6	302.3	567.6	684.6
122.5°	152.9	172.1	299.9	537.5	646.2
125°	164.8	182.8	298.2	494.8	591.6
127.5°	177.7	194.5	297.2	469.3	549.0
130°	184.3	201.2	295.8	451.5	521.0
132.5°	191.5	207.8	295.8	437.6	501.6
135°	201.5	218.3	294.6	417.9	472.4
137.5°	211.0	227.4	294.5	401.3	448.4
140°	218.1	234.9	294.0	387.5	432.7
142.5°	226.2	240.2	295.4	376.5	417.1
145°	237.7	249.9	297.0	361.7	394.2
147.5°	247.5	259.4	299.6	346.8	374.9
150°	256.1	264.2	300.5	341.9	361.6
152.5°	262.7	271.3	301.5	335.2	353.5
155°	271.5	277.9	304.1	326.9	340.2
157.5°	282.4	286.2	304.7	323.1	332.7
160°	288.1	291.0	307.0	320.3	328.4
162.5°	291.4	294.8	307.5	317.9	324.1
165°	299.9	301.1	307.6	314.3	318.9
167.5°	305.7	304.7	310.4	313.4	315.2
170°	307.6	307.1	309.4	310.1	312.4
172.5°	311.9	309.9	310.8	309.1	311.0
175°	314.2	312.4	311.2	309.4	307.0
177.5°	315.1	312.3	310.8	309.0	309.4
180°	311.8	311.8	311.8	311.8	311.8

(END OF REPORT)