

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562082

Luminaire Tested: **SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562082
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11107.9 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 97
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562082
CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562082

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39				34	
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34				29	
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	41	45	40	35	38	34	30	31	28	26				22	
6	63	51	43	38	58	48	40	35	41	35	31	34	30	27	28	25	23				20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20				17	
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	23	20	18				16	
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19489	19489	19489
5°	19665	19513	19412
10°	19602	19466	19364
15°	19516	19395	19291
20°	19418	19293	19150
25°	19281	19152	18930
30°	19073	18938	18666
35°	18791	18628	18361
40°	18363	18166	17837
45°	17615	17307	16950
50°	16295	15904	15591
55°	14223	13901	13608
60°	11985	11885	11649
65°	10368	10407	10326
70°	9522	9571	9571
75°	9144	9144	9211
80°	8602	8698	8602
85°	6934	7707	7707



TEST NUMBER: P562082

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.8	1.8
10°-20°	571.5	5.1
20°-30°	862.0	7.8
30°-40°	1027.1	9.2
40°-50°	1012.6	9.1
50°-60°	773.9	7.0
60°-70°	478.9	4.3
70°-80°	272.0	2.4
80°-90°	82.8	0.7
90°-100°	427.5	3.8
100°-110°	1216.3	10.9
110°-120°	1165.4	10.5
120°-130°	922.3	8.3
130°-140°	740.3	6.7
140°-150°	579.6	5.2
150°-160°	424.1	3.8
160°-170°	262.7	2.4
170°-180°	89.1	0.8
0°-30°	1633.3	14.7
0°-40°	2660.4	24.0
0°-60°	4447.0	40.0
0°-90°	5280.6	47.5
90°-120°	2809.1	25.3
90°-150°	5051.4	45.5
90°-180°	5827.0	52.5
0°-180°	11107.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2112	2112	2112	2112	2112	
5°	2123	2100	2107	2100	2096	201
15°	2043	2022	2030	2023	2020	577
25°	1894	1871	1881	1861	1860	872
35°	1668	1649	1654	1632	1630	1041
45°	1350	1332	1326	1303	1299	1034
55°	884	870	864	850	846	792
65°	475	471	477	473	473	481
75°	256	256	256	258	258	271
85°	66	69	73	73	73	76
90°	0	0	0	0	0	5
95°	46	184	828	286	177	53
105°	189	287	1240	2189	2081	200
115°	351	425	940	1991	2338	346
125°	496	550	897	1489	1780	444
135°	606	657	886	1258	1421	468
145°	715	752	894	1088	1186	447
155°	817	836	915	984	1024	378
165°	902	906	926	946	960	254
175°	945	940	936	931	924	90
180°	938	938	938	938	938	

TEST NUMBER: P562082

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2112.4	2112.4	2112.4	2112.4	2112.4
2.5°	2125.4	2106.9	2112.4	2107.8	2097.8
5°	2123.3	2100.1	2106.9	2099.5	2096.0
7.5°	2106.9	2084.1	2090.9	2083.6	2081.4
10°	2092.3	2071.0	2077.8	2070.4	2066.9
12.5°	2076.3	2053.6	2061.8	2053.0	2049.4
15°	2043.2	2021.9	2030.5	2023.1	2019.6
17.5°	2006.8	1984.1	1992.6	1984.2	1979.5
20°	1977.7	1956.4	1965.0	1952.2	1950.4
22.5°	1945.7	1924.3	1933.0	1915.8	1915.5
25°	1894.0	1870.9	1881.3	1861.2	1859.5
27.5°	1832.5	1811.2	1819.8	1799.4	1797.2
30°	1790.3	1769.0	1777.6	1755.7	1752.1
32.5°	1742.3	1722.4	1729.5	1707.7	1705.5
35°	1668.4	1648.8	1653.9	1632.0	1630.2
37.5°	1584.4	1566.6	1569.4	1545.4	1543.6
40°	1524.7	1506.9	1508.3	1482.8	1481.0
42.5°	1459.2	1441.4	1439.9	1414.4	1412.6
45°	1350.0	1332.2	1326.4	1302.6	1299.1
47.5°	1225.6	1207.8	1196.8	1177.5	1175.0
50°	1135.3	1117.5	1108.0	1091.5	1086.2
52.5°	1037.8	1020.0	1012.0	996.9	991.6
55°	884.2	870.0	864.2	849.6	846.0
57.5°	738.3	728.7	727.0	712.8	711.4
60°	649.5	644.2	644.1	631.3	631.3
62.5°	573.8	569.9	572.8	564.4	562.9
65°	474.9	471.3	476.7	473.0	473.0
67.5°	396.6	396.6	399.9	398.5	398.5
70°	353.0	353.0	354.8	354.8	354.8
72.5°	313.7	312.2	316.9	316.9	315.5
75°	256.5	256.5	256.5	258.4	258.4
77.5°	199.8	200.1	201.6	201.2	199.8
80°	161.9	163.7	163.7	161.9	161.9
82.5°	124.1	125.9	125.9	125.5	124.1
85°	65.5	69.1	72.8	72.8	72.8
87.5°	18.9	24.6	29.1	29.1	27.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.3	75.7	175.5	51.1	38.5
95°	46.4	184.1	827.5	286.4	176.6
97.5°	85.2	215.7	1274.5	912.0	624.9
100°	112.4	234.4	1371.5	1389.2	1070.1
102.5°	142.3	254.6	1350.1	1778.2	1499.5
105°	189.0	286.7	1239.5	2189.4	2081.3
107.5°	236.5	324.0	1110.4	2305.4	2401.6
110°	269.3	351.3	1036.2	2261.0	2477.2

TEST NUMBER: P562082

CATALOG NUMBER: SQ4-PR1-125U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	378.5	986.3	2156.1	2464.4
115°	351.3	424.6	939.9	1991.1	2338.1
117.5°	395.9	464.6	912.4	1810.7	2178.3
120°	431.6	489.1	909.6	1707.7	2059.9
122.5°	460.1	517.7	902.4	1617.2	1944.3
125°	495.8	549.9	897.1	1488.7	1779.9
127.5°	534.7	585.3	894.2	1411.9	1651.8
130°	554.7	605.2	890.0	1358.4	1567.7
132.5°	576.1	625.2	890.0	1316.7	1509.2
135°	606.4	657.0	886.4	1257.5	1421.4
137.5°	634.9	684.1	886.0	1207.4	1349.0
140°	656.3	706.9	884.6	1165.9	1301.9
142.5°	680.6	722.8	888.9	1132.8	1254.8
145°	715.2	751.8	893.5	1088.4	1186.0
147.5°	744.8	780.4	901.4	1043.5	1127.9
150°	770.5	794.9	904.2	1028.6	1087.9
152.5°	790.4	816.2	907.1	1008.6	1063.7
155°	816.8	836.0	914.9	983.6	1023.7
157.5°	849.6	861.2	916.7	972.3	1000.9
160°	866.8	875.5	923.8	963.6	988.0
162.5°	876.8	886.9	925.3	956.4	975.2
165°	902.4	905.9	925.6	945.6	959.5
167.5°	919.9	916.8	933.8	942.9	948.4
170°	925.6	923.9	931.0	932.9	939.9
172.5°	938.5	932.5	935.3	930.0	935.6
175°	945.2	940.0	936.3	930.8	923.8
177.5°	948.1	939.7	935.3	929.6	931.0
180°	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)