

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562198

Luminaire Tested: **SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562198  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4361.8 lumens  
Efficiency: N/A  
Efficacy: 119.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 36.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562198  
CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562198

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	72	64	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	63	56	50	68	59	52	46	50	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	29	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7536	7536	7536
5°	7585	7525	7492
10°	7525	7464	7424
15°	7445	7362	7335
20°	7356	7243	7228
25°	7253	7121	7100
30°	7099	6993	6946
35°	6899	6801	6760
40°	6683	6578	6553
45°	6423	6339	6310
50°	6156	6105	6064
55°	5870	5870	5776
60°	5512	5617	5418
65°	5043	5294	4919
70°	4446	4872	4330
75°	3796	4360	3693
80°	2943	3671	2981
85°	1905	2816	2509



TEST NUMBER: P562198

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.9	1.8
10°-20°	217.2	5.0
20°-30°	322.1	7.4
30°-40°	376.9	8.6
40°-50°	375.2	8.6
50°-60°	324.0	7.4
60°-70°	233.2	5.3
70°-80°	122.3	2.8
80°-90°	30.3	0.7
90°-100°	167.5	3.8
100°-110°	476.6	10.9
110°-120°	456.7	10.5
120°-130°	361.4	8.3
130°-140°	290.1	6.7
140°-150°	227.1	5.2
150°-160°	166.2	3.8
160°-170°	102.9	2.4
170°-180°	34.9	0.8
0°-30°	616.2	14.1
0°-40°	993.1	22.8
0°-60°	1692.4	38.8
0°-90°	2078.3	47.6
90°-120°	1100.8	25.2
90°-150°	1979.5	45.4
90°-180°	2283.0	52.3
0°-180°	4361.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	819	810	812	810	809	78
15°	779	770	771	769	768	220
25°	712	700	700	695	697	328
35°	612	604	604	598	600	383
45°	492	488	486	484	484	380
55°	365	364	365	360	359	326
65°	231	238	242	233	225	229
75°	106	116	122	114	104	114
85°	18	24	27	25	24	24
90°	0	0	0	0	0	1
95°	18	72	324	112	69	21
105°	74	112	486	858	816	78
115°	138	166	368	780	916	136
125°	194	216	352	583	698	174
135°	238	257	347	493	557	183
145°	280	295	350	426	465	175
155°	320	328	358	385	401	148
165°	354	355	363	370	376	99
175°	370	368	367	365	362	35
180°	368	368	368	368	368	

TEST NUMBER: P562198

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	816.8	816.8	816.8	816.8	816.8
2.5°	821.5	814.7	816.8	815.0	811.1
5°	819.0	809.9	812.5	810.3	808.9
7.5°	810.7	802.2	804.2	801.9	801.0
10°	803.2	794.7	796.7	793.8	792.4
12.5°	794.5	785.5	787.5	784.6	783.7
15°	779.4	769.6	770.8	769.3	767.9
17.5°	761.9	751.9	752.1	749.8	749.5
20°	749.2	738.6	737.7	734.8	736.2
22.5°	735.4	724.3	723.3	719.3	721.3
25°	712.5	700.5	699.5	695.3	697.4
27.5°	686.0	674.2	674.2	668.2	670.5
30°	666.4	655.2	656.4	649.2	652.0
32.5°	645.7	635.6	636.2	629.1	631.9
35°	612.5	604.0	603.8	598.1	600.2
37.5°	578.5	571.0	569.9	566.6	567.1
40°	554.9	548.5	546.2	544.1	544.1
42.5°	530.1	524.4	522.1	520.5	519.9
45°	492.3	488.0	485.8	484.3	483.6
47.5°	454.8	450.9	448.9	447.9	447.2
50°	428.9	426.1	425.3	423.2	422.5
52.5°	403.0	401.3	400.6	397.8	397.1
55°	364.9	364.2	364.9	359.8	359.1
57.5°	325.2	326.3	328.6	321.8	320.1
60°	298.7	301.5	304.4	296.4	293.6
62.5°	271.6	276.1	280.2	271.1	267.1
65°	231.0	238.1	242.5	233.0	225.3
67.5°	191.9	200.6	206.0	195.7	187.0
70°	164.8	174.7	180.6	170.3	160.5
72.5°	141.2	152.2	157.0	147.3	137.5
75°	106.5	116.4	122.3	114.2	103.6
77.5°	75.6	84.9	89.8	82.7	74.0
80°	55.4	65.3	69.1	63.2	56.1
82.5°	39.3	47.5	50.1	46.5	41.7
85°	18.0	23.6	26.6	25.2	23.7
87.5°	4.6	8.5	10.9	11.0	11.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.6	29.6	68.8	20.0	15.1
95°	18.2	72.2	324.3	112.2	69.2
97.5°	33.4	84.5	499.4	357.4	244.9
100°	44.0	91.9	537.4	544.4	419.3
102.5°	55.8	99.8	529.1	696.8	587.6
105°	74.1	112.3	485.7	858.0	815.6
107.5°	92.7	127.0	435.1	903.4	941.1
110°	105.5	137.6	406.1	886.0	970.8

TEST NUMBER: P562198

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	117.8	148.3	386.5	844.9	965.7
115°	137.7	166.4	368.3	780.3	916.2
117.5°	155.2	182.1	357.6	709.6	853.6
120°	169.1	191.7	356.4	669.2	807.2
122.5°	180.3	202.9	353.6	633.7	761.9
125°	194.3	215.5	351.5	583.4	697.5
127.5°	209.5	229.3	350.4	553.3	647.3
130°	217.4	237.2	348.7	532.3	614.3
132.5°	225.7	245.0	348.7	516.0	591.4
135°	237.6	257.4	347.3	492.8	557.0
137.5°	248.8	268.1	347.2	473.1	528.6
140°	257.2	277.0	346.6	456.9	510.2
142.5°	266.7	283.2	348.3	443.9	491.7
145°	280.3	294.6	350.1	426.5	464.8
147.5°	291.9	305.8	353.2	408.9	442.0
150°	301.9	311.5	354.3	403.1	426.3
152.5°	309.7	319.9	355.5	395.2	416.8
155°	320.1	327.6	358.5	385.4	401.2
157.5°	332.9	337.5	359.2	381.0	392.2
160°	339.7	343.1	362.0	377.6	387.2
162.5°	343.6	347.5	362.6	374.8	382.2
165°	353.6	355.0	362.7	370.5	376.0
167.5°	360.5	359.3	365.9	369.5	371.7
170°	362.7	362.0	364.8	365.6	368.3
172.5°	367.8	365.4	366.5	364.4	366.6
175°	370.4	368.4	366.9	364.8	362.0
177.5°	371.5	368.2	366.5	364.3	364.8
180°	367.6	367.6	367.6	367.6	367.6

(END OF REPORT)