

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562095

Luminaire Tested: **SQ4-PR1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562095
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9141.2 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562095
CATALOG NUMBER: SQ4-PR1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562095

CATALOG NUMBER: SQ4-PR1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23						23														
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20						20														
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	25	24	23	17						17														
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	19	14						14														
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	12						12														
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11						11														
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10						10														
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	9						9														
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10	8						8														
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	11	9	7						7														
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8	6						6														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7889	7829	7788
10°	7864	7810	7768
15°	7830	7781	7739
20°	7790	7740	7683
25°	7736	7684	7594
30°	7652	7598	7488
35°	7540	7473	7366
40°	7367	7288	7157
45°	7067	6943	6801
50°	6538	6380	6255
55°	5707	5577	5459
60°	4809	4768	4674
65°	4159	4174	4144
70°	3820	3839	3839
75°	3668	3668	3697
80°	3454	3491	3454
85°	2784	3091	3091



TEST NUMBER: P562095

CATALOG NUMBER: SQ4-PR1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.1	0.9
10°-20°	229.3	2.5
20°-30°	345.8	3.8
30°-40°	412.1	4.5
40°-50°	406.3	4.4
50°-60°	310.5	3.4
60°-70°	192.1	2.1
70°-80°	109.1	1.2
80°-90°	33.2	0.4
90°-100°	515.2	5.6
100°-110°	1465.8	16.0
110°-120°	1404.4	15.4
120°-130°	1111.5	12.2
130°-140°	892.2	9.8
140°-150°	698.5	7.6
150°-160°	511.1	5.6
160°-170°	316.6	3.5
170°-180°	107.4	1.2
0°-30°	655.3	7.2
0°-40°	1067.3	11.7
0°-60°	1784.1	19.5
0°-90°	2118.6	23.2
90°-120°	3385.4	37.0
90°-150°	6087.6	66.6
90°-180°	7023.0	76.8
0°-180°	9141.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	848	848	848	848	848	
5°	852	843	845	842	841	81
15°	820	811	815	812	810	231
25°	760	751	755	747	746	350
35°	669	662	664	655	654	418
45°	542	534	532	523	521	415
55°	355	349	347	341	339	318
65°	190	189	191	190	190	193
75°	103	103	103	104	104	109
85°	26	28	29	29	29	31
90°	0	0	0	0	0	3
95°	56	222	997	345	213	64
105°	228	346	1494	2639	2508	241
115°	423	512	1133	2400	2818	417
125°	598	663	1081	1794	2145	535
135°	731	792	1068	1516	1713	564
145°	862	906	1077	1312	1429	538
155°	984	1008	1103	1185	1234	455
165°	1088	1092	1116	1140	1156	306
175°	1139	1133	1128	1122	1113	108
180°	1131	1131	1131	1131	1131	

TEST NUMBER: P562095

CATALOG NUMBER: SQ4-PR1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	847.5	847.5	847.5	847.5	847.5
2.5°	852.7	845.3	847.5	845.6	841.6
5°	851.8	842.6	845.3	842.3	840.9
7.5°	845.3	836.1	838.8	835.9	835.1
10°	839.4	830.9	833.6	830.6	829.2
12.5°	833.0	823.9	827.2	823.6	822.2
15°	819.7	811.2	814.6	811.7	810.2
17.5°	805.1	796.0	799.4	796.0	794.2
20°	793.4	784.9	788.3	783.2	782.5
22.5°	780.6	772.0	775.5	768.6	768.5
25°	759.9	750.6	754.8	746.7	746.0
27.5°	735.2	726.6	730.1	721.9	721.0
30°	718.3	709.7	713.2	704.4	702.9
32.5°	699.0	691.0	693.9	685.1	684.2
35°	669.4	661.5	663.5	654.7	654.0
37.5°	635.6	628.5	629.6	620.0	619.3
40°	611.7	604.6	605.1	594.9	594.2
42.5°	585.4	578.3	577.7	567.4	566.7
45°	541.6	534.5	532.1	522.6	521.2
47.5°	491.7	484.5	480.2	472.4	471.4
50°	455.5	448.3	444.5	437.9	435.8
52.5°	416.4	409.2	406.0	400.0	397.8
55°	354.8	349.0	346.7	340.8	339.4
57.5°	296.2	292.4	291.7	286.0	285.4
60°	260.6	258.4	258.4	253.3	253.3
62.5°	230.2	228.7	229.8	226.4	225.8
65°	190.5	189.1	191.2	189.8	189.8
67.5°	159.1	159.1	160.4	159.9	159.9
70°	141.6	141.6	142.3	142.3	142.3
72.5°	125.8	125.3	127.2	127.1	126.6
75°	102.9	102.9	102.9	103.7	103.7
77.5°	80.1	80.3	80.9	80.7	80.1
80°	65.0	65.7	65.7	65.0	65.0
82.5°	49.8	50.5	50.5	50.4	49.8
85°	26.3	27.7	29.2	29.2	29.2
87.5°	7.6	9.9	11.7	11.7	11.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.2	91.2	211.5	61.6	46.4
95°	55.9	221.9	997.3	345.2	212.8
97.5°	102.7	259.9	1535.9	1099.1	753.1
100°	135.4	282.5	1652.8	1674.2	1289.6
102.5°	171.5	306.9	1627.1	2143.0	1807.2
105°	227.8	345.5	1493.8	2638.6	2508.3
107.5°	285.0	390.5	1338.2	2778.3	2894.3
110°	324.6	423.3	1248.8	2724.8	2985.4

TEST NUMBER: P562095

CATALOG NUMBER: SQ4-PR1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	362.4	456.1	1188.6	2598.4	2970.0
115°	423.4	511.7	1132.7	2399.6	2817.8
117.5°	477.2	560.0	1099.6	2182.2	2625.2
120°	520.1	589.5	1096.2	2058.0	2482.5
122.5°	554.5	623.9	1087.6	1949.0	2343.2
125°	597.5	662.7	1081.1	1794.1	2145.0
127.5°	644.4	705.3	1077.7	1701.5	1990.7
130°	668.4	729.4	1072.5	1637.1	1889.3
132.5°	694.2	753.5	1072.5	1586.8	1818.8
135°	730.8	791.7	1068.2	1515.5	1713.0
137.5°	765.2	824.4	1067.8	1455.1	1625.8
140°	791.0	851.9	1066.1	1405.1	1569.0
142.5°	820.2	871.0	1071.2	1365.2	1512.3
145°	861.9	906.0	1076.8	1311.6	1429.3
147.5°	897.6	940.4	1086.3	1257.5	1359.2
150°	928.5	957.9	1089.7	1239.6	1311.1
152.5°	952.6	983.7	1093.2	1215.5	1281.9
155°	984.4	1007.5	1102.6	1185.4	1233.7
157.5°	1023.9	1037.8	1104.8	1171.7	1206.2
160°	1044.6	1055.1	1113.4	1161.3	1190.7
162.5°	1056.6	1068.8	1115.1	1152.6	1175.3
165°	1087.6	1091.8	1115.5	1139.5	1156.3
167.5°	1108.6	1104.8	1125.4	1136.3	1143.0
170°	1115.5	1113.4	1122.0	1124.3	1132.7
172.5°	1131.0	1123.8	1127.1	1120.8	1127.5
175°	1139.2	1132.8	1128.4	1121.8	1113.4
177.5°	1142.6	1132.5	1127.1	1120.3	1122.0
180°	1130.6	1130.6	1130.6	1130.6	1130.6

(END OF REPORT)