

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562102

Luminaire Tested: **SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562102
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9193.0 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 82.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562102
CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562102

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	52	50	46	42	38	35	33	27	26	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	65	54	47	41	59	49	43	37	40	35	31	30	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10558	10558	10558
5°	10653	10571	10516
10°	10619	10546	10490
15°	10573	10507	10450
20°	10519	10452	10375
25°	10446	10375	10255
30°	10333	10259	10112
35°	10181	10092	9948
40°	9948	9841	9664
45°	9543	9376	9183
50°	8829	8616	8447
55°	7705	7531	7372
60°	6493	6438	6311
65°	5617	5639	5595
70°	5158	5185	5185
75°	4955	4955	4991
80°	4660	4713	4660
85°	3758	4171	4171



TEST NUMBER: P562102

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	1.2
10°-20°	309.6	3.4
20°-30°	467.0	5.1
30°-40°	556.4	6.1
40°-50°	548.6	6.0
50°-60°	419.3	4.6
60°-70°	259.5	2.8
70°-80°	147.4	1.6
80°-90°	44.8	0.5
90°-100°	464.5	5.1
100°-110°	1321.7	14.4
110°-120°	1266.3	13.8
120°-130°	1002.2	10.9
130°-140°	804.5	8.8
140°-150°	629.8	6.9
150°-160°	460.8	5.0
160°-170°	285.4	3.1
170°-180°	96.9	1.1
0°-30°	884.9	9.6
0°-40°	1441.3	15.7
0°-60°	2409.2	26.2
0°-90°	2860.8	31.1
90°-120°	3052.5	33.2
90°-150°	5489.0	59.7
90°-180°	6332.0	68.9
0°-180°	9193.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1144	1144	1144	1144	1144	
5°	1150	1138	1141	1137	1136	109
15°	1107	1095	1100	1096	1094	312
25°	1026	1014	1019	1008	1007	472
35°	904	893	896	884	883	564
45°	731	722	719	706	704	560
55°	479	471	468	460	458	429
65°	257	255	258	256	256	261
75°	139	139	139	140	140	147
85°	36	37	39	39	39	41
90°	0	0	0	0	0	4
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P562102

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1144.4	1144.4	1144.4	1144.4	1144.4
2.5°	1151.5	1141.5	1144.4	1141.9	1136.5
5°	1150.3	1137.8	1141.4	1137.4	1135.5
7.5°	1141.4	1129.1	1132.8	1128.8	1127.6
10°	1133.5	1122.0	1125.7	1121.7	1119.7
12.5°	1124.9	1112.5	1117.0	1112.2	1110.3
15°	1106.9	1095.4	1100.0	1096.0	1094.1
17.5°	1087.2	1074.9	1079.5	1074.9	1072.4
20°	1071.4	1059.9	1064.5	1057.6	1056.7
22.5°	1054.1	1042.5	1047.2	1037.9	1037.7
25°	1026.1	1013.6	1019.2	1008.3	1007.4
27.5°	992.8	981.2	985.9	974.8	973.7
30°	969.9	958.4	963.0	951.1	949.2
32.5°	943.9	933.1	937.0	925.1	924.0
35°	903.9	893.3	896.0	884.1	883.2
37.5°	858.3	848.7	850.3	837.2	836.3
40°	826.0	816.4	817.1	803.3	802.4
42.5°	790.5	780.9	780.1	766.3	765.3
45°	731.4	721.7	718.6	705.7	703.8
47.5°	664.0	654.3	648.4	637.9	636.6
50°	615.1	605.4	600.3	591.3	588.5
52.5°	562.2	552.6	548.2	540.1	537.2
55°	479.0	471.3	468.2	460.3	458.3
57.5°	400.0	394.8	393.9	386.2	385.4
60°	351.9	349.0	348.9	342.0	342.0
62.5°	310.9	308.8	310.3	305.7	305.0
65°	257.3	255.3	258.3	256.3	256.3
67.5°	214.9	214.9	216.7	215.9	215.9
70°	191.2	191.2	192.2	192.2	192.2
72.5°	169.9	169.2	171.7	171.7	170.9
75°	139.0	139.0	139.0	140.0	140.0
77.5°	108.2	108.4	109.2	109.0	108.2
80°	87.7	88.7	88.7	87.7	87.7
82.5°	67.2	68.2	68.2	68.0	67.2
85°	35.5	37.4	39.4	39.4	39.4
87.5°	10.3	13.3	15.8	15.8	15.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9

TEST NUMBER: P562102

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)