

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562104

Luminaire Tested: **SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562104
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9608.7 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 83.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562104

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562104

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	52	50	46	42	38	35	33	27	26	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	65	54	47	41	59	49	43	37	40	35	31	30	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11035	11035	11035
5°	11135	11049	10992
10°	11100	11023	10965
15°	11051	10983	10923
20°	10996	10925	10843
25°	10918	10845	10719
30°	10801	10724	10569
35°	10640	10548	10397
40°	10399	10287	10100
45°	9975	9800	9598
50°	9228	9005	8829
55°	8054	7872	7707
60°	6787	6730	6597
65°	5870	5892	5849
70°	5392	5419	5419
75°	5180	5180	5215
80°	4872	4925	4872
85°	3927	4361	4361



TEST NUMBER: P562104

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	1.2
10°-20°	323.6	3.4
20°-30°	488.1	5.1
30°-40°	581.6	6.1
40°-50°	573.4	6.0
50°-60°	438.2	4.6
60°-70°	271.2	2.8
70°-80°	154.0	1.6
80°-90°	46.9	0.5
90°-100°	485.5	5.1
100°-110°	1381.5	14.4
110°-120°	1323.6	13.8
120°-130°	1047.6	10.9
130°-140°	840.8	8.8
140°-150°	658.3	6.9
150°-160°	481.7	5.0
160°-170°	298.3	3.1
170°-180°	101.2	1.1
0°-30°	924.9	9.6
0°-40°	1506.5	15.7
0°-60°	2518.1	26.2
0°-90°	2990.2	31.1
90°-120°	3190.6	33.2
90°-150°	5737.2	59.7
90°-180°	6618.0	68.9
0°-180°	9608.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1202	1189	1193	1189	1187	114
15°	1157	1145	1150	1146	1144	326
25°	1072	1059	1065	1054	1053	494
35°	945	934	936	924	923	590
45°	764	754	751	738	736	586
55°	501	493	489	481	479	449
65°	269	267	270	268	268	272
75°	145	145	145	146	146	153
85°	37	39	41	41	41	43
90°	0	0	0	0	0	4
95°	53	209	940	325	200	60
105°	215	326	1408	2487	2364	227
115°	399	482	1068	2262	2656	393
125°	563	624	1019	1691	2022	504
135°	689	746	1007	1428	1614	531
145°	812	854	1015	1236	1347	507
155°	928	950	1039	1117	1163	429
165°	1025	1029	1051	1074	1090	288
175°	1074	1068	1064	1057	1049	102
180°	1066	1066	1066	1066	1066	

TEST NUMBER: P562104

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1203.6	1193.1	1196.1	1193.5	1187.9
5°	1202.3	1189.2	1193.0	1188.9	1186.9
7.5°	1193.0	1180.1	1184.0	1179.8	1178.6
10°	1184.8	1172.7	1176.6	1172.4	1170.4
12.5°	1175.7	1162.8	1167.5	1162.5	1160.5
15°	1157.0	1144.9	1149.8	1145.6	1143.6
17.5°	1136.4	1123.5	1128.3	1123.5	1120.9
20°	1119.9	1107.8	1112.7	1105.4	1104.4
22.5°	1101.8	1089.7	1094.5	1084.9	1084.7
25°	1072.5	1059.4	1065.3	1053.9	1052.9
27.5°	1037.7	1025.6	1030.5	1018.9	1017.7
30°	1013.8	1001.7	1006.6	994.2	992.1
32.5°	986.6	975.3	979.4	967.0	965.8
35°	944.7	933.7	936.5	924.1	923.1
37.5°	897.2	887.1	888.7	875.1	874.1
40°	863.4	853.3	854.1	839.6	838.6
42.5°	826.3	816.2	815.3	800.9	799.9
45°	764.5	754.4	751.1	737.6	735.6
47.5°	694.0	683.9	677.7	666.8	665.3
50°	642.9	632.8	627.4	618.1	615.1
52.5°	587.7	577.6	573.0	564.5	561.5
55°	500.7	492.6	489.4	481.1	479.1
57.5°	418.1	412.6	411.7	403.6	402.8
60°	367.8	364.8	364.7	357.5	357.5
62.5°	324.9	322.7	324.3	319.6	318.8
65°	268.9	266.9	269.9	267.9	267.9
67.5°	224.6	224.6	226.5	225.6	225.6
70°	199.9	199.9	200.9	200.9	200.9
72.5°	177.6	176.8	179.5	179.5	178.6
75°	145.3	145.3	145.3	146.3	146.3
77.5°	113.1	113.3	114.2	113.9	113.1
80°	91.7	92.7	92.7	91.7	91.7
82.5°	70.3	71.3	71.3	71.1	70.3
85°	37.1	39.1	41.2	41.2	41.2
87.5°	10.7	13.9	16.5	16.5	15.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.2	85.9	199.3	58.0	43.8
95°	52.7	209.1	939.9	325.3	200.5
97.5°	96.8	245.0	1447.5	1035.8	709.8
100°	127.6	266.3	1557.7	1577.8	1215.4
102.5°	161.6	289.2	1533.4	2019.7	1703.2
105°	214.7	325.6	1407.8	2486.7	2363.9
107.5°	268.6	368.0	1261.2	2618.4	2727.7
110°	305.9	399.0	1176.9	2568.0	2813.6



TEST NUMBER: P562104

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	341.5	429.9	1120.2	2448.9	2799.0
115°	399.1	482.2	1067.5	2261.5	2655.6
117.5°	449.7	527.7	1036.3	2056.6	2474.1
120°	490.2	555.6	1033.1	1939.5	2339.6
122.5°	522.6	588.0	1025.0	1836.8	2208.4
125°	563.1	624.5	1018.9	1690.8	2021.6
127.5°	607.3	664.7	1015.7	1603.6	1876.1
130°	630.0	687.4	1010.8	1542.9	1780.5
132.5°	654.3	710.1	1010.8	1495.4	1714.1
135°	688.7	746.2	1006.7	1428.3	1614.4
137.5°	721.1	777.0	1006.3	1371.4	1532.2
140°	745.4	802.9	1004.7	1324.2	1478.7
142.5°	773.0	820.9	1009.6	1286.6	1425.2
145°	812.3	853.9	1014.8	1236.1	1347.0
147.5°	845.9	886.3	1023.8	1185.2	1281.0
150°	875.1	902.8	1027.0	1168.3	1235.6
152.5°	897.8	927.1	1030.2	1145.5	1208.1
155°	927.7	949.5	1039.2	1117.2	1162.7
157.5°	965.0	978.1	1041.2	1104.3	1136.8
160°	984.5	994.4	1049.3	1094.5	1122.2
162.5°	995.8	1007.3	1050.9	1086.2	1107.6
165°	1025.0	1028.9	1051.3	1073.9	1089.8
167.5°	1044.8	1041.3	1060.6	1070.9	1077.2
170°	1051.3	1049.3	1057.4	1059.6	1067.5
172.5°	1065.9	1059.2	1062.2	1056.3	1062.6
175°	1073.6	1067.6	1063.5	1057.2	1049.3
177.5°	1076.8	1067.3	1062.2	1055.8	1057.4
180°	1065.5	1065.5	1065.5	1065.5	1065.5

(END OF REPORT)