

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562239

Luminaire Tested: **SQ4-PW1-050U-125D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562239  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-050U-125D-92765-1D-UNV-STD-W-4 (6500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7641.9 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 71.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562239

CATALOG NUMBER: SQ4-PW1-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562239

CATALOG NUMBER: SQ4-PW1-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	69
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	55	53	49
3	85	75	68	62	80	72	65	59	64	59	55	58	53	50	51	48	45	42
4	78	67	59	53	73	64	56	51	57	51	47	51	47	43	46	42	39	36
5	72	60	51	45	68	57	49	44	51	45	40	46	41	37	41	37	34	31
6	66	54	45	39	62	51	44	38	46	40	35	42	37	33	38	33	30	28
7	61	49	40	35	58	46	39	34	42	36	31	38	33	29	34	30	27	24
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19233	19233	19233
5°	19357	19205	19119
10°	19203	19048	18945
15°	18999	18789	18718
20°	18773	18484	18448
25°	18510	18174	18117
30°	18119	17846	17727
35°	17604	17356	17253
40°	17055	16789	16723
45°	16392	16177	16104
50°	15713	15581	15474
55°	14979	14979	14742
60°	14064	14336	13828
65°	12872	13513	12551
70°	11346	12436	11049
75°	9689	11129	9429
80°	7513	9367	7614
85°	4859	7198	6415



TEST NUMBER: P562239

CATALOG NUMBER: SQ4-PW1-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	196.3	2.6
10°-20°	554.2	7.3
20°-30°	822.1	10.8
30°-40°	961.9	12.6
40°-50°	957.6	12.5
50°-60°	826.9	10.8
60°-70°	595.2	7.8
70°-80°	312.2	4.1
80°-90°	77.4	1.0
90°-100°	171.5	2.2
100°-110°	488.0	6.4
110°-120°	467.6	6.1
120°-130°	370.1	4.8
130°-140°	297.0	3.9
140°-150°	232.5	3.0
150°-160°	170.1	2.2
160°-170°	105.4	1.4
170°-180°	35.8	0.5
0°-30°	1572.6	20.6
0°-40°	2534.5	33.2
0°-60°	4319.1	56.5
0°-90°	5303.9	69.4
90°-120°	1127.1	14.7
90°-150°	2026.7	26.5
90°-180°	2338.0	30.6
0°-180°	7641.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2090	2067	2074	2068	2064	198
15°	1989	1964	1967	1963	1960	561
25°	1818	1788	1785	1774	1780	836
35°	1563	1542	1541	1526	1532	977
45°	1256	1246	1240	1236	1234	969
55°	931	929	931	918	916	831
65°	590	608	619	595	575	584
75°	272	297	312	291	264	291
85°	46	60	68	64	61	61
90°	0	0	0	0	0	2
95°	19	74	332	115	71	21
105°	76	115	497	878	835	80
115°	141	170	377	799	938	139
125°	199	221	360	597	714	178
135°	243	264	356	504	570	188
145°	287	302	358	437	476	179
155°	328	335	367	395	411	151
165°	362	364	371	379	385	102
175°	379	377	376	374	371	36
180°	376	376	376	376	376	

TEST NUMBER: P562239

CATALOG NUMBER: SQ4-PW1-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2084.6	2084.6	2084.6	2084.6	2084.6
2.5°	2096.4	2079.1	2084.6	2080.0	2069.9
5°	2090.1	2066.8	2073.6	2068.0	2064.4
7.5°	2068.8	2047.3	2052.3	2046.4	2044.2
10°	2049.7	2028.2	2033.2	2025.8	2022.2
12.5°	2027.7	2004.7	2009.7	2002.3	2000.1
15°	1989.1	1964.0	1967.1	1963.3	1959.7
17.5°	1944.3	1918.8	1919.3	1913.4	1912.7
20°	1912.0	1885.0	1882.6	1875.3	1878.9
22.5°	1876.7	1848.3	1845.9	1835.7	1840.7
25°	1818.3	1787.8	1785.3	1774.4	1779.7
27.5°	1750.7	1720.6	1720.6	1705.3	1711.1
30°	1700.8	1672.0	1675.1	1656.8	1664.0
32.5°	1647.9	1622.0	1623.6	1605.4	1612.6
35°	1563.0	1541.5	1541.0	1526.4	1531.8
37.5°	1476.3	1457.3	1454.3	1445.9	1447.3
40°	1416.1	1399.9	1394.0	1388.5	1388.5
42.5°	1352.9	1338.2	1332.3	1328.3	1326.8
45°	1256.3	1245.5	1239.8	1236.0	1234.2
47.5°	1160.8	1150.7	1145.7	1143.1	1141.3
50°	1094.7	1087.5	1085.5	1079.9	1078.1
52.5°	1028.5	1024.2	1022.3	1015.3	1013.5
55°	931.2	929.4	931.2	918.3	916.5
57.5°	829.8	832.7	838.6	821.3	817.0
60°	762.2	769.4	776.9	756.5	749.4
62.5°	693.2	704.7	715.2	691.8	681.8
65°	589.6	607.5	619.0	594.6	574.9
67.5°	489.7	511.9	525.7	499.4	477.2
70°	420.6	445.7	461.0	434.7	409.6
72.5°	360.4	388.4	400.8	375.9	350.8
75°	271.8	297.0	312.2	291.4	264.5
77.5°	192.9	216.6	229.2	211.1	188.8
80°	141.4	166.6	176.3	161.2	143.3
82.5°	100.3	121.1	127.8	118.7	106.5
85°	45.9	60.3	68.0	64.2	60.6
87.5°	11.8	21.8	27.9	28.0	29.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.4	70.4	20.5	15.5
95°	18.6	73.9	332.0	114.9	70.8
97.5°	34.2	86.5	511.3	365.9	250.7
100°	45.1	94.1	550.3	557.4	429.3
102.5°	57.1	102.2	541.7	713.5	601.6
105°	75.8	115.0	497.3	878.4	835.1
107.5°	94.9	130.0	445.5	925.0	963.6
110°	108.1	140.9	415.7	907.2	993.9

TEST NUMBER: P562239

CATALOG NUMBER: SQ4-PW1-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	151.8	395.7	865.1	988.8
115°	141.0	170.4	377.1	798.9	938.1
117.5°	158.9	186.4	366.1	726.5	874.0
120°	173.2	196.3	364.9	685.1	826.5
122.5°	184.6	207.7	362.1	648.9	780.1
125°	198.9	220.6	359.9	597.3	714.1
127.5°	214.5	234.8	358.8	566.5	662.8
130°	222.5	242.8	357.1	545.0	629.0
132.5°	231.1	250.9	357.1	528.3	605.5
135°	243.3	263.6	355.6	504.5	570.3
137.5°	254.7	274.5	355.5	484.4	541.3
140°	263.3	283.6	354.9	467.8	522.4
142.5°	273.1	290.0	356.6	454.5	503.5
145°	286.9	301.6	358.5	436.7	475.8
147.5°	298.8	313.1	361.6	418.7	452.5
150°	309.1	318.9	362.8	412.7	436.5
152.5°	317.1	327.5	363.9	404.7	426.8
155°	327.7	335.4	367.1	394.6	410.7
157.5°	340.9	345.5	367.8	390.1	401.6
160°	347.8	351.3	370.7	386.6	396.4
162.5°	351.8	355.8	371.2	383.7	391.3
165°	362.1	363.5	371.4	379.4	385.0
167.5°	369.1	367.8	374.7	378.3	380.5
170°	371.4	370.7	373.5	374.3	377.1
172.5°	376.5	374.2	375.2	373.1	375.4
175°	379.2	377.1	375.7	373.5	370.7
177.5°	380.4	377.0	375.2	373.0	373.5
180°	376.4	376.4	376.4	376.4	376.4

(END OF REPORT)