

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562260

Luminaire Tested: **SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562260  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6242.5 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 55.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562260  
CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562260

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	72	64	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	63	56	50	68	59	52	46	50	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	29	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10788	10788	10788
5°	10858	10773	10725
10°	10772	10685	10627
15°	10658	10539	10500
20°	10530	10368	10349
25°	10384	10194	10163
30°	10163	10010	9944
35°	9875	9736	9677
40°	9567	9418	9381
45°	9195	9073	9033
50°	8813	8740	8681
55°	8401	8401	8270
60°	7890	8042	7756
65°	7220	7580	7041
70°	6364	6976	6196
75°	5436	6242	5290
80°	4213	5255	4272
85°	2731	4033	3599



TEST NUMBER: P562260

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	1.8
10°-20°	310.9	5.0
20°-30°	461.1	7.4
30°-40°	539.6	8.6
40°-50°	537.2	8.6
50°-60°	463.9	7.4
60°-70°	333.9	5.3
70°-80°	175.1	2.8
80°-90°	43.4	0.7
90°-100°	239.7	3.8
100°-110°	682.0	10.9
110°-120°	653.4	10.5
120°-130°	517.2	8.3
130°-140°	415.1	6.6
140°-150°	325.0	5.2
150°-160°	237.8	3.8
160°-170°	147.3	2.4
170°-180°	50.0	0.8
0°-30°	882.1	14.1
0°-40°	1421.7	22.8
0°-60°	2422.7	38.8
0°-90°	2975.1	47.7
90°-120°	1575.1	25.2
90°-150°	2832.3	45.4
90°-180°	3267.0	52.3
0°-180°	6242.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1172	1159	1163	1160	1158	111
15°	1116	1102	1103	1101	1099	314
25°	1020	1003	1001	995	998	469
35°	877	865	864	856	859	548
45°	705	699	695	693	692	544
55°	522	521	522	515	514	466
65°	331	341	347	334	322	328
75°	152	167	175	164	148	163
85°	26	34	38	36	34	34
90°	0	0	0	0	0	2
95°	26	103	464	161	99	30
105°	106	161	695	1228	1167	112
115°	197	238	527	1116	1311	194
125°	278	308	503	835	998	249
135°	340	368	497	705	797	262
145°	401	422	501	610	665	250
155°	458	469	513	552	574	212
165°	506	508	519	530	538	142
175°	530	527	525	522	518	50
180°	526	526	526	526	526	



TEST NUMBER: P562260

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1169.3	1169.3	1169.3	1169.3	1169.3
2.5°	1175.9	1166.3	1169.3	1166.7	1161.1
5°	1172.4	1159.3	1163.2	1160.0	1158.0
7.5°	1160.5	1148.4	1151.2	1147.9	1146.7
10°	1149.8	1137.7	1140.5	1136.3	1134.3
12.5°	1137.4	1124.5	1127.3	1123.2	1122.0
15°	1115.8	1101.7	1103.4	1101.3	1099.3
17.5°	1090.6	1076.3	1076.6	1073.3	1072.9
20°	1072.5	1057.4	1056.0	1051.9	1054.0
22.5°	1052.7	1036.8	1035.4	1029.7	1032.5
25°	1020.0	1002.8	1001.4	995.3	998.3
27.5°	982.0	965.1	965.2	956.6	959.8
30°	954.0	937.9	939.6	929.4	933.4
32.5°	924.4	909.8	910.8	900.5	904.6
35°	876.8	864.7	864.4	856.2	859.2
37.5°	828.1	817.4	815.8	811.0	811.8
40°	794.3	785.3	782.0	778.9	778.9
42.5°	758.9	750.6	747.4	745.1	744.3
45°	704.7	698.7	695.4	693.3	692.3
47.5°	651.1	645.5	642.7	641.2	640.2
50°	614.0	610.0	608.9	605.8	604.8
52.5°	576.9	574.5	573.4	569.5	568.5
55°	522.3	521.3	522.3	515.1	514.1
57.5°	465.5	467.1	470.4	460.7	458.3
60°	427.6	431.6	435.8	424.4	420.3
62.5°	388.8	395.3	401.2	388.1	382.4
65°	330.7	340.8	347.2	333.6	322.5
67.5°	274.7	287.2	294.9	280.2	267.7
70°	235.9	250.0	258.6	243.9	229.7
72.5°	202.1	217.9	224.8	210.9	196.8
75°	152.5	166.6	175.1	163.5	148.4
77.5°	108.2	121.5	128.6	118.4	105.9
80°	79.3	93.4	98.9	90.4	80.4
82.5°	56.3	67.9	71.7	66.6	59.8
85°	25.8	33.8	38.1	36.0	34.0
87.5°	6.6	12.2	15.7	15.7	16.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.0	42.4	98.4	28.6	21.6
95°	26.0	103.2	464.0	160.6	99.0
97.5°	47.8	120.9	714.6	511.3	350.4
100°	63.0	131.4	769.0	778.9	600.0
102.5°	79.8	142.8	757.0	997.0	840.8
105°	106.0	160.8	695.0	1227.6	1167.0
107.5°	132.6	181.7	622.6	1292.6	1346.6
110°	151.0	197.0	581.0	1267.8	1389.0



TEST NUMBER: P562260

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	168.6	212.2	553.0	1208.9	1381.8
115°	197.0	238.1	527.0	1116.4	1311.0
117.5°	222.0	260.5	511.6	1015.3	1221.4
120°	242.0	274.3	510.0	957.5	1155.0
122.5°	258.0	290.3	506.0	906.8	1090.2
125°	278.0	308.3	503.0	834.7	998.0
127.5°	299.8	328.2	501.4	791.7	926.2
130°	311.0	339.4	499.0	761.7	879.0
132.5°	323.0	350.6	499.0	738.3	846.2
135°	340.0	368.4	497.0	705.1	797.0
137.5°	356.0	383.6	496.8	677.0	756.4
140°	368.0	396.4	496.0	653.7	730.0
142.5°	381.6	405.3	498.4	635.2	703.6
145°	401.0	421.5	501.0	610.2	665.0
147.5°	417.6	437.5	505.4	585.1	632.4
150°	432.0	445.7	507.0	576.8	610.0
152.5°	443.2	457.7	508.6	565.5	596.4
155°	458.0	468.8	513.0	551.5	574.0
157.5°	476.4	482.9	514.0	545.2	561.2
160°	486.0	490.9	518.0	540.3	554.0
162.5°	491.6	497.3	518.8	536.2	546.8
165°	506.0	508.0	519.0	530.2	538.0
167.5°	515.8	514.0	523.6	528.7	531.8
170°	519.0	518.0	522.0	523.1	527.0
172.5°	526.2	522.9	524.4	521.5	524.6
175°	530.0	527.1	525.0	521.9	518.0
177.5°	531.6	526.9	524.4	521.2	522.0
180°	526.0	526.0	526.0	526.0	526.0

(END OF REPORT)