

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562262

Luminaire Tested: **SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562262
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6459.2 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 55.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562262
CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562262

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39				34	
3	81	72	64	59	74	66	60	55	56	51	47	46	43	40	37	35	33				29	
4	74	63	56	50	68	59	52	46	50	44	40	41	37	34	33	31	28				25	
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22				19	
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19				17	
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17				15	
9	50	38	30	25	46	35	29	24	30	25	21	26	21	18	21	18	16				14	
10	47	35	28	23	43	32	26	21	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11163	11163	11163
5°	11235	11147	11097
10°	11146	11056	10996
15°	11027	10905	10865
20°	10895	10728	10708
25°	10744	10549	10516
30°	10516	10357	10289
35°	10218	10074	10014
40°	9899	9745	9706
45°	9514	9389	9347
50°	9120	9043	8982
55°	8694	8694	8557
60°	8163	8320	8025
65°	7471	7844	7285
70°	6585	7219	6412
75°	5625	6459	5472
80°	4362	5435	4421
85°	2826	4171	3726



TEST NUMBER: P562262

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.9	1.8
10°-20°	321.7	5.0
20°-30°	477.2	7.4
30°-40°	558.3	8.6
40°-50°	555.8	8.6
50°-60°	480.0	7.4
60°-70°	345.5	5.3
70°-80°	181.2	2.8
80°-90°	44.9	0.7
90°-100°	248.0	3.8
100°-110°	705.7	10.9
110°-120°	676.1	10.5
120°-130°	535.1	8.3
130°-140°	429.5	6.6
140°-150°	336.2	5.2
150°-160°	246.0	3.8
160°-170°	152.4	2.4
170°-180°	51.7	0.8
0°-30°	912.8	14.1
0°-40°	1471.1	22.8
0°-60°	2506.9	38.8
0°-90°	3078.4	47.7
90°-120°	1629.8	25.2
90°-150°	2930.6	45.4
90°-180°	3381.0	52.3
0°-180°	6459.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1210	1210	1210	1210	1210	
5°	1213	1200	1204	1200	1198	115
15°	1154	1140	1142	1140	1138	325
25°	1055	1038	1036	1030	1033	485
35°	907	895	894	886	889	567
45°	729	723	720	717	716	563
55°	540	539	540	533	532	482
65°	342	353	359	345	334	339
75°	158	172	181	169	154	169
85°	27	35	39	37	35	35
90°	0	0	0	0	0	2
95°	27	107	480	166	102	31
105°	110	166	719	1270	1208	116
115°	204	246	545	1155	1356	201
125°	288	319	520	864	1033	257
135°	352	381	514	730	825	271
145°	415	436	518	631	688	259
155°	474	485	531	571	594	219
165°	524	526	537	549	557	147
175°	548	545	543	540	536	52
180°	544	544	544	544	544	



TEST NUMBER: P562262

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1209.9	1209.9	1209.9	1209.9	1209.9
2.5°	1216.8	1206.8	1209.9	1207.3	1201.4
5°	1213.1	1199.6	1203.6	1200.3	1198.2
7.5°	1200.8	1188.3	1191.2	1187.7	1186.5
10°	1189.7	1177.2	1180.1	1175.8	1173.7
12.5°	1176.9	1163.6	1166.5	1162.2	1160.9
15°	1154.5	1139.9	1141.7	1139.5	1137.5
17.5°	1128.5	1113.7	1114.0	1110.6	1110.2
20°	1109.7	1094.1	1092.7	1088.5	1090.6
22.5°	1089.3	1072.8	1071.4	1065.5	1068.4
25°	1055.4	1037.7	1036.2	1029.9	1033.0
27.5°	1016.1	998.6	998.7	989.8	993.1
30°	987.1	970.5	972.2	961.7	965.8
32.5°	956.4	941.4	942.4	931.8	936.0
35°	907.2	894.7	894.4	885.9	889.1
37.5°	856.9	845.8	844.1	839.2	840.0
40°	821.9	812.5	809.1	805.9	805.9
42.5°	785.2	776.7	773.3	770.9	770.1
45°	729.2	722.9	719.6	717.4	716.4
47.5°	673.7	667.9	665.0	663.5	662.4
50°	635.4	631.2	630.0	626.8	625.8
52.5°	597.0	594.5	593.4	589.3	588.2
55°	540.5	539.4	540.5	533.0	532.0
57.5°	481.6	483.3	486.8	476.7	474.2
60°	442.4	446.6	450.9	439.1	434.9
62.5°	402.3	409.0	415.1	401.5	395.7
65°	342.2	352.6	359.3	345.1	333.7
67.5°	284.2	297.1	305.1	289.9	277.0
70°	244.1	258.7	267.6	252.3	237.7
72.5°	209.2	225.4	232.6	218.2	203.6
75°	157.8	172.4	181.2	169.1	153.5
77.5°	111.9	125.7	133.0	122.5	109.6
80°	82.1	96.7	102.3	93.6	83.2
82.5°	58.2	70.3	74.2	68.9	61.8
85°	26.7	35.0	39.4	37.3	35.2
87.5°	6.8	12.7	16.2	16.2	17.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.3	43.9	101.8	29.6	22.3
95°	26.9	106.8	480.1	166.2	102.4
97.5°	49.5	125.1	739.4	529.1	362.6
100°	65.2	136.0	795.7	806.0	620.8
102.5°	82.6	147.7	783.3	1031.7	870.0
105°	109.7	166.3	719.1	1270.2	1207.5
107.5°	137.2	188.0	644.2	1337.5	1393.4
110°	156.2	203.8	601.2	1311.8	1437.2

TEST NUMBER: P562262

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.5	219.6	572.2	1250.9	1429.8
115°	203.8	246.3	545.3	1155.2	1356.5
117.5°	229.7	269.6	529.4	1050.5	1263.8
120°	250.4	283.8	527.7	990.7	1195.1
122.5°	267.0	300.3	523.6	938.3	1128.1
125°	287.7	319.0	520.5	863.7	1032.7
127.5°	310.2	339.5	518.8	819.1	958.4
130°	321.8	351.1	516.3	788.1	909.5
132.5°	334.2	362.7	516.3	763.9	875.6
135°	351.8	381.1	514.3	729.6	824.7
137.5°	368.4	396.9	514.0	700.5	782.7
140°	380.8	410.1	513.2	676.4	755.3
142.5°	394.8	419.3	515.7	657.2	728.0
145°	414.9	436.2	518.4	631.4	688.1
147.5°	432.1	452.7	522.9	605.4	654.4
150°	447.0	461.2	524.6	596.8	631.2
152.5°	458.6	473.6	526.3	585.1	617.1
155°	473.9	485.0	530.8	570.7	593.9
157.5°	492.9	499.6	531.8	564.1	580.7
160°	502.9	507.9	536.0	559.1	573.2
162.5°	508.7	514.5	536.8	554.9	565.8
165°	523.6	525.6	537.0	548.6	556.7
167.5°	533.7	531.9	541.8	547.0	550.3
170°	537.0	536.0	540.1	541.3	545.3
172.5°	544.5	541.0	542.6	539.6	542.8
175°	548.4	545.4	543.2	540.0	536.0
177.5°	550.1	545.2	542.6	539.3	540.1
180°	544.3	544.3	544.3	544.3	544.3

(END OF REPORT)