

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562141

Luminaire Tested: **SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562141  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3753.5 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 34.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562141

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562141

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	20	24	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6892	6892	6892
5°	6937	6882	6852
10°	6881	6826	6788
15°	6808	6733	6708
20°	6728	6623	6611
25°	6633	6512	6493
30°	6493	6394	6353
35°	6308	6219	6182
40°	6111	6016	5993
45°	5874	5797	5771
50°	5631	5583	5545
55°	5368	5368	5282
60°	5039	5137	4954
65°	4613	4842	4497
70°	4065	4456	3960
75°	3472	3989	3379
80°	2694	3358	2726
85°	1747	2583	2297



TEST NUMBER: P562141

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	1.9
10°-20°	198.6	5.3
20°-30°	294.6	7.8
30°-40°	344.7	9.2
40°-50°	343.2	9.1
50°-60°	296.3	7.9
60°-70°	213.3	5.7
70°-80°	111.9	3.0
80°-90°	27.7	0.7
90°-100°	135.9	3.6
100°-110°	386.8	10.3
110°-120°	370.6	9.9
120°-130°	293.3	7.8
130°-140°	235.4	6.3
140°-150°	184.3	4.9
150°-160°	134.8	3.6
160°-170°	83.5	2.2
170°-180°	28.3	0.8
0°-30°	563.5	15.0
0°-40°	908.2	24.2
0°-60°	1547.7	41.2
0°-90°	1900.6	50.6
90°-120°	893.2	23.8
90°-150°	1606.2	42.8
90°-180°	1853.0	49.4
0°-180°	3753.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	747	747	747	747	747	
5°	749	741	743	741	740	71
15°	713	704	705	704	702	201
25°	652	641	640	636	638	300
35°	560	552	552	547	549	350
45°	450	446	444	443	442	347
55°	334	333	334	329	328	298
65°	211	218	222	213	206	209
75°	97	106	112	104	95	104
85°	16	22	24	23	22	22
90°	0	0	0	0	0	1
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	

TEST NUMBER: P562141

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	747.0	747.0	747.0	747.0	747.0
2.5°	751.2	745.1	747.0	745.4	741.8
5°	749.0	740.6	743.1	741.1	739.8
7.5°	741.4	733.6	735.4	733.3	732.5
10°	734.5	726.8	728.6	725.9	724.6
12.5°	726.6	718.4	720.2	717.5	716.7
15°	712.8	703.8	704.9	703.6	702.3
17.5°	696.7	687.6	687.8	685.7	685.4
20°	685.2	675.5	674.6	672.0	673.3
22.5°	672.5	662.3	661.5	657.8	659.6
25°	651.6	640.6	639.7	635.8	637.8
27.5°	627.4	616.6	616.6	611.1	613.1
30°	609.5	599.2	600.2	593.7	596.3
32.5°	590.5	581.2	581.8	575.3	577.9
35°	560.1	552.4	552.2	547.0	548.9
37.5°	529.0	522.2	521.1	518.1	518.6
40°	507.4	501.7	499.5	497.6	497.6
42.5°	484.8	479.5	477.4	476.0	475.5
45°	450.2	446.3	444.3	442.9	442.3
47.5°	416.0	412.4	410.6	409.6	409.0
50°	392.3	389.7	389.0	387.0	386.3
52.5°	368.6	367.0	366.3	363.8	363.2
55°	333.7	333.0	333.7	329.1	328.4
57.5°	297.4	298.4	300.5	294.3	292.8
60°	273.1	275.7	278.4	271.1	268.5
62.5°	248.4	252.5	256.3	247.9	244.3
65°	211.3	217.7	221.8	213.1	206.0
67.5°	175.5	183.4	188.4	179.0	171.0
70°	150.7	159.7	165.2	155.8	146.8
72.5°	129.1	139.2	143.6	134.7	125.7
75°	97.4	106.4	111.9	104.4	94.8
77.5°	69.1	77.6	82.1	75.6	67.7
80°	50.7	59.7	63.2	57.8	51.3
82.5°	35.9	43.4	45.8	42.5	38.2
85°	16.5	21.6	24.4	23.0	21.7
87.5°	4.2	7.8	10.0	10.0	10.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7



TEST NUMBER: P562141

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)