

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562263

Luminaire Tested: **SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562263
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6530.7 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562263
CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562263

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	72	64	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	63	56	50	68	59	52	46	50	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	29	24	30	25	21	26	21	18	21	18	16	14
10	47	35	28	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11286	11286	11286
5°	11360	11270	11220
10°	11269	11179	11118
15°	11150	11026	10984
20°	11016	10847	10826
25°	10863	10666	10632
30°	10633	10472	10403
35°	10331	10185	10124
40°	10009	9853	9813
45°	9619	9492	9451
50°	9221	9143	9081
55°	8791	8791	8651
60°	8254	8412	8115
65°	7554	7929	7366
70°	6658	7297	6485
75°	5686	6531	5532
80°	4410	5499	4468
85°	2848	4224	3769



TEST NUMBER: P562263

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.2	1.8
10°-20°	325.2	5.0
20°-30°	482.4	7.4
30°-40°	564.5	8.6
40°-50°	562.0	8.6
50°-60°	485.3	7.4
60°-70°	349.3	5.3
70°-80°	183.2	2.8
80°-90°	45.4	0.7
90°-100°	250.8	3.8
100°-110°	713.5	10.9
110°-120°	683.6	10.5
120°-130°	541.0	8.3
130°-140°	434.3	6.6
140°-150°	340.0	5.2
150°-160°	248.8	3.8
160°-170°	154.1	2.4
170°-180°	52.3	0.8
0°-30°	922.9	14.1
0°-40°	1487.3	22.8
0°-60°	2534.6	38.8
0°-90°	3112.5	47.7
90°-120°	1647.8	25.2
90°-150°	2963.1	45.4
90°-180°	3418.0	52.3
0°-180°	6530.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1223	1223	1223	1223	1223	
5°	1227	1213	1217	1214	1212	116
15°	1167	1152	1154	1152	1150	329
25°	1067	1049	1048	1041	1044	491
35°	917	905	904	896	899	573
45°	737	731	728	725	724	569
55°	546	545	546	539	538	488
65°	346	356	363	349	337	343
75°	160	174	183	171	155	171
85°	27	35	40	38	36	36
90°	0	0	0	0	0	2
95°	27	108	485	168	104	31
105°	111	168	727	1284	1221	117
115°	206	249	551	1168	1372	203
125°	291	322	526	873	1044	260
135°	356	385	520	738	834	274
145°	420	441	524	638	696	262
155°	479	490	537	577	600	221
165°	529	531	543	555	563	149
175°	554	551	549	546	542	53
180°	550	550	550	550	550	



TEST NUMBER: P562263

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1223.3	1223.3	1223.3	1223.3	1223.3
2.5°	1230.2	1220.1	1223.3	1220.6	1214.7
5°	1226.6	1212.9	1216.9	1213.6	1211.5
7.5°	1214.1	1201.4	1204.4	1200.9	1199.6
10°	1202.9	1190.2	1193.2	1188.8	1186.7
12.5°	1189.9	1176.4	1179.4	1175.0	1173.8
15°	1167.3	1152.5	1154.4	1152.2	1150.0
17.5°	1141.0	1126.0	1126.3	1122.9	1122.5
20°	1122.0	1106.2	1104.8	1100.5	1102.6
22.5°	1101.3	1084.7	1083.2	1077.3	1080.2
25°	1067.1	1049.1	1047.7	1041.3	1044.4
27.5°	1027.4	1009.7	1009.7	1000.7	1004.1
30°	998.1	981.2	983.0	972.3	976.5
32.5°	967.0	951.9	952.8	942.1	946.3
35°	917.2	904.6	904.3	895.7	898.9
37.5°	866.4	855.2	853.4	848.5	849.3
40°	831.0	821.5	818.1	814.8	814.8
42.5°	793.9	785.3	781.9	779.5	778.6
45°	737.2	730.9	727.5	725.4	724.3
47.5°	681.2	675.3	672.4	670.8	669.8
50°	642.4	638.2	637.0	633.7	632.7
52.5°	603.6	601.1	599.9	595.8	594.7
55°	546.5	545.4	546.5	538.9	537.8
57.5°	487.0	488.6	492.1	481.9	479.4
60°	447.3	451.5	455.9	444.0	439.8
62.5°	406.8	413.5	419.7	406.0	400.1
65°	346.0	356.5	363.2	349.0	337.4
67.5°	287.3	300.4	308.5	293.1	280.0
70°	246.8	261.6	270.5	255.1	240.4
72.5°	211.5	227.9	235.2	220.6	205.9
75°	159.5	174.3	183.2	171.0	155.2
77.5°	113.2	127.1	134.5	123.9	110.8
80°	83.0	97.7	103.5	94.6	84.1
82.5°	58.8	71.1	75.0	69.7	62.5
85°	26.9	35.4	39.9	37.7	35.6
87.5°	6.9	12.8	16.4	16.4	17.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.4	44.4	102.9	30.0	22.6
95°	27.2	108.0	485.4	168.0	103.6
97.5°	50.0	126.5	747.6	535.0	366.6
100°	65.9	137.5	804.5	814.9	627.7
102.5°	83.5	149.4	792.0	1043.1	879.6
105°	110.9	168.2	727.1	1284.3	1220.9
107.5°	138.7	190.1	651.3	1352.3	1408.8
110°	158.0	206.0	607.8	1326.3	1453.1

TEST NUMBER: P562263

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	222.0	578.5	1264.7	1445.6
115°	206.1	249.1	551.3	1168.0	1371.5
117.5°	232.2	272.6	535.2	1062.2	1277.8
120°	253.2	286.9	533.5	1001.7	1208.3
122.5°	269.9	303.7	529.4	948.6	1140.5
125°	290.8	322.5	526.2	873.2	1044.1
127.5°	313.6	343.3	524.5	828.2	969.0
130°	325.4	355.0	522.0	796.8	919.6
132.5°	337.9	366.8	522.0	772.3	885.3
135°	355.7	385.4	519.9	737.6	833.8
137.5°	372.4	401.3	519.7	708.3	791.3
140°	385.0	414.7	518.9	683.9	763.7
142.5°	399.2	424.0	521.4	664.5	736.1
145°	419.5	441.0	524.1	638.4	695.7
147.5°	436.9	457.7	528.7	612.1	661.6
150°	451.9	466.3	530.4	603.4	638.2
152.5°	463.7	478.8	532.1	591.6	623.9
155°	479.1	490.4	536.7	577.0	600.5
157.5°	498.4	505.1	537.7	570.3	587.1
160°	508.4	513.6	541.9	565.3	579.6
162.5°	514.3	520.2	542.8	561.0	572.0
165°	529.4	531.4	543.0	554.7	562.8
167.5°	539.6	537.8	547.8	553.1	556.4
170°	543.0	541.9	546.1	547.2	551.3
172.5°	550.5	547.0	548.6	545.5	548.8
175°	554.5	551.4	549.2	546.0	541.9
177.5°	556.1	551.2	548.6	545.3	546.1
180°	550.3	550.3	550.3	550.3	550.3

(END OF REPORT)