

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562142

Luminaire Tested: **SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562142
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3831.4 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 34.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562142
CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562142

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	98	94	90	86	90	87	83	80	74	71	69	61	60	58	50	49	48	43				
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36				
3	82	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31				
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17	14				
10	47	35	28	23	44	33	26	22	29	23	20	24	20	17	21	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7035	7035	7035
5°	7080	7025	6993
10°	7024	6967	6930
15°	6950	6872	6847
20°	6867	6761	6748
25°	6771	6648	6627
30°	6628	6527	6485
35°	6439	6348	6311
40°	6239	6141	6117
45°	5995	5917	5891
50°	5747	5698	5661
55°	5479	5479	5392
60°	5145	5244	5058
65°	4709	4943	4591
70°	4149	4548	4041
75°	3543	4071	3447
80°	2747	3427	2784
85°	1778	2636	2350



TEST NUMBER: P562142

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	1.9
10°-20°	202.7	5.3
20°-30°	300.7	7.8
30°-40°	351.8	9.2
40°-50°	350.3	9.1
50°-60°	302.5	7.9
60°-70°	217.7	5.7
70°-80°	114.2	3.0
80°-90°	28.3	0.7
90°-100°	138.8	3.6
100°-110°	394.8	10.3
110°-120°	378.2	9.9
120°-130°	299.4	7.8
130°-140°	240.3	6.3
140°-150°	188.1	4.9
150°-160°	137.6	3.6
160°-170°	85.3	2.2
170°-180°	28.9	0.8
0°-30°	575.2	15.0
0°-40°	927.0	24.2
0°-60°	1579.8	41.2
0°-90°	1940.0	50.6
90°-120°	911.8	23.8
90°-150°	1639.5	42.8
90°-180°	1891.0	49.4
0°-180°	3831.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	762	762	762	762	762	
5°	764	756	758	756	755	72
15°	728	718	720	718	717	205
25°	665	654	653	649	651	306
35°	572	564	564	558	560	357
45°	460	456	454	452	452	355
55°	341	340	341	336	335	304
65°	216	222	226	218	210	214
75°	99	109	114	107	97	107
85°	17	22	25	24	22	22
90°	0	0	0	0	0	1
95°	15	60	269	93	57	17
105°	61	93	402	711	676	65
115°	114	138	305	646	759	112
125°	161	178	291	483	578	144
135°	197	213	288	408	461	152
145°	232	244	290	353	385	145
155°	265	271	297	319	332	123
165°	293	294	300	307	311	82
175°	307	305	304	302	300	29
180°	304	304	304	304	304	

TEST NUMBER: P562142

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	762.5	762.5	762.5	762.5	762.5
2.5°	766.8	760.5	762.5	760.8	757.1
5°	764.5	756.0	758.5	756.4	755.1
7.5°	756.7	748.8	750.7	748.5	747.7
10°	749.7	741.9	743.7	741.0	739.7
12.5°	741.7	733.3	735.1	732.4	731.6
15°	727.6	718.4	719.5	718.1	716.8
17.5°	711.2	701.8	702.0	699.9	699.6
20°	699.4	689.5	688.6	685.9	687.3
22.5°	686.5	676.1	675.2	671.4	673.3
25°	665.1	653.9	653.0	649.0	651.0
27.5°	640.4	629.3	629.3	623.8	625.9
30°	622.1	611.6	612.7	606.0	608.7
32.5°	602.7	593.3	593.9	587.2	589.8
35°	571.7	563.8	563.6	558.3	560.3
37.5°	540.0	533.0	531.9	528.9	529.4
40°	518.0	512.1	509.9	507.9	507.9
42.5°	494.9	489.5	487.3	485.8	485.3
45°	459.5	455.6	453.5	452.1	451.5
47.5°	424.6	420.9	419.1	418.1	417.5
50°	400.4	397.8	397.0	395.0	394.4
52.5°	376.2	374.6	373.9	371.4	370.7
55°	340.6	339.9	340.6	335.9	335.2
57.5°	303.5	304.6	306.7	300.4	298.8
60°	278.8	281.4	284.2	276.7	274.1
62.5°	253.5	257.7	261.6	253.1	249.4
65°	215.7	222.2	226.4	217.5	210.3
67.5°	179.1	187.2	192.3	182.7	174.5
70°	153.8	163.0	168.6	159.0	149.8
72.5°	131.8	142.1	146.6	137.5	128.3
75°	99.4	108.6	114.2	106.6	96.7
77.5°	70.5	79.2	83.8	77.2	69.1
80°	51.7	60.9	64.5	59.0	52.4
82.5°	36.7	44.3	46.8	43.4	39.0
85°	16.8	22.1	24.9	23.5	22.2
87.5°	4.3	8.0	10.2	10.2	10.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.6	24.6	57.0	16.6	12.5
95°	15.1	59.8	268.6	93.0	57.3
97.5°	27.7	70.0	413.7	296.0	202.8
100°	36.5	76.1	445.1	450.9	347.3
102.5°	46.2	82.6	438.2	577.2	486.7
105°	61.4	93.1	402.3	710.6	675.5
107.5°	76.8	105.2	360.4	748.3	779.5
110°	87.4	114.0	336.3	733.9	804.0



TEST NUMBER: P562142

CATALOG NUMBER: SQ4-PW1-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	97.6	122.8	320.1	699.8	799.9
115°	114.0	137.8	305.1	646.3	758.9
117.5°	128.5	150.8	296.1	587.7	707.0
120°	140.1	158.8	295.2	554.3	668.6
122.5°	149.3	168.0	292.9	524.9	631.1
125°	160.9	178.5	291.2	483.2	577.7
127.5°	173.5	190.0	290.2	458.3	536.1
130°	180.0	196.4	288.9	440.9	508.8
132.5°	187.0	202.9	288.9	427.3	489.8
135°	196.8	213.2	287.7	408.2	461.4
137.5°	206.1	222.0	287.6	391.9	437.9
140°	213.0	229.4	287.1	378.4	422.6
142.5°	220.9	234.6	288.5	367.7	407.3
145°	232.1	244.0	290.0	353.2	384.9
147.5°	241.7	253.3	292.6	338.7	366.1
150°	250.1	258.0	293.5	333.9	353.1
152.5°	256.6	264.9	294.4	327.3	345.2
155°	265.1	271.3	297.0	319.3	332.3
157.5°	275.8	279.5	297.5	315.6	324.9
160°	281.3	284.2	299.9	312.8	320.7
162.5°	284.6	287.9	300.3	310.4	316.5
165°	292.9	294.0	300.4	306.9	311.4
167.5°	298.6	297.6	303.1	306.0	307.8
170°	300.4	299.9	302.2	302.8	305.1
172.5°	304.6	302.7	303.6	301.9	303.7
175°	306.8	305.1	303.9	302.1	299.9
177.5°	307.7	305.0	303.6	301.7	302.2
180°	304.5	304.5	304.5	304.5	304.5

(END OF REPORT)