

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562288

Luminaire Tested: **SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562288  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (4500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8504.3 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 79.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562288  
CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (4500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562288

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (4500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	58	57	56	51
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	48	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	37	44	38	33	38	34	30	33	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18580	18580	18580
5°	18700	18552	18470
10°	18551	18401	18300
15°	18354	18150	18082
20°	18134	17856	17821
25°	17881	17556	17501
30°	17504	17238	17126
35°	17006	16766	16666
40°	16475	16220	16155
45°	15835	15626	15557
50°	15179	15051	14949
55°	14469	14469	14240
60°	13587	13849	13358
65°	12433	13053	12123
70°	10960	12012	10674
75°	9361	10751	9108
80°	7258	9048	7353
85°	4700	6944	6203



TEST NUMBER: P562288

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (4500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.6	2.2
10°-20°	535.4	6.3
20°-30°	794.1	9.3
30°-40°	929.2	10.9
40°-50°	925.1	10.9
50°-60°	798.8	9.4
60°-70°	575.0	6.8
70°-80°	301.5	3.5
80°-90°	74.8	0.9
90°-100°	248.0	2.9
100°-110°	705.7	8.3
110°-120°	676.1	8.0
120°-130°	535.1	6.3
130°-140°	429.5	5.1
140°-150°	336.2	4.0
150°-160°	246.0	2.9
160°-170°	152.4	1.8
170°-180°	51.7	0.6
0°-30°	1519.1	17.9
0°-40°	2448.3	28.8
0°-60°	4172.2	49.1
0°-90°	5123.5	60.2
90°-120°	1629.8	19.2
90°-150°	2930.6	34.5
90°-180°	3381.0	39.8
0°-180°	8504.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2014	2014	2014	2014	2014	
5°	2019	1996	2003	1998	1994	191
15°	1922	1897	1900	1897	1893	542
25°	1756	1727	1725	1714	1719	808
35°	1510	1489	1489	1474	1480	944
45°	1214	1203	1198	1194	1192	936
55°	900	898	900	887	885	803
65°	570	587	598	574	555	564
75°	263	287	302	282	256	281
85°	44	58	66	62	59	59
90°	0	0	0	0	0	3
95°	27	107	480	166	102	31
105°	110	166	719	1270	1208	116
115°	204	246	545	1155	1356	201
125°	288	319	520	864	1033	257
135°	352	381	514	730	825	271
145°	415	436	518	631	688	259
155°	474	485	531	571	594	219
165°	524	526	537	549	557	147
175°	548	545	543	540	536	52
180°	544	544	544	544	544	

TEST NUMBER: P562288

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2013.8	2013.8	2013.8	2013.8	2013.8
2.5°	2025.1	2008.5	2013.8	2009.3	1999.6
5°	2019.1	1996.5	2003.1	1997.7	1994.3
7.5°	1998.5	1977.7	1982.5	1976.8	1974.7
10°	1980.1	1959.2	1964.1	1956.9	1953.4
12.5°	1958.8	1936.6	1941.4	1934.2	1932.2
15°	1921.5	1897.2	1900.2	1896.6	1893.1
17.5°	1878.2	1853.6	1854.1	1848.4	1847.7
20°	1847.0	1821.0	1818.6	1811.6	1815.1
22.5°	1812.9	1785.5	1783.1	1773.3	1778.1
25°	1756.5	1727.0	1724.6	1714.0	1719.2
27.5°	1691.2	1662.1	1662.1	1647.3	1652.9
30°	1643.0	1615.2	1618.1	1600.5	1607.5
32.5°	1591.9	1566.9	1568.4	1550.8	1557.8
35°	1509.9	1489.1	1488.6	1474.5	1479.7
37.5°	1426.1	1407.7	1404.8	1396.7	1398.1
40°	1367.9	1352.3	1346.7	1341.3	1341.3
42.5°	1306.9	1292.7	1287.0	1283.1	1281.7
45°	1213.6	1203.2	1197.6	1194.0	1192.3
47.5°	1121.3	1111.6	1106.8	1104.3	1102.5
50°	1057.5	1050.5	1048.6	1043.2	1041.5
52.5°	993.6	989.4	987.5	980.8	979.0
55°	899.5	897.8	899.5	887.1	885.3
57.5°	801.6	804.4	810.1	793.3	789.2
60°	736.3	743.3	750.5	730.8	723.9
62.5°	669.6	680.7	690.9	668.3	658.6
65°	569.5	586.9	597.9	574.4	555.3
67.5°	473.0	494.5	507.8	482.5	460.9
70°	406.3	430.6	445.3	419.9	395.7
72.5°	348.1	375.2	387.1	363.2	338.9
75°	262.6	286.9	301.6	281.5	255.5
77.5°	186.3	209.2	221.4	203.9	182.4
80°	136.6	160.9	170.3	155.7	138.4
82.5°	96.9	117.0	123.5	114.7	102.9
85°	44.4	58.2	65.6	62.0	58.6
87.5°	11.4	21.1	27.0	27.0	28.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.3	43.9	101.8	29.6	22.3
95°	26.9	106.8	480.1	166.2	102.4
97.5°	49.5	125.1	739.4	529.1	362.6
100°	65.2	136.0	795.7	806.0	620.8
102.5°	82.6	147.7	783.3	1031.7	870.0
105°	109.7	166.3	719.1	1270.2	1207.5
107.5°	137.2	188.0	644.2	1337.5	1393.4
110°	156.2	203.8	601.2	1311.8	1437.2

TEST NUMBER: P562288

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	174.5	219.6	572.2	1250.9	1429.8
115°	203.8	246.3	545.3	1155.2	1356.5
117.5°	229.7	269.6	529.4	1050.5	1263.8
120°	250.4	283.8	527.7	990.7	1195.1
122.5°	267.0	300.3	523.6	938.3	1128.1
125°	287.7	319.0	520.5	863.7	1032.7
127.5°	310.2	339.5	518.8	819.1	958.4
130°	321.8	351.1	516.3	788.1	909.5
132.5°	334.2	362.7	516.3	763.9	875.6
135°	351.8	381.1	514.3	729.6	824.7
137.5°	368.4	396.9	514.0	700.5	782.7
140°	380.8	410.1	513.2	676.4	755.3
142.5°	394.8	419.3	515.7	657.2	728.0
145°	414.9	436.2	518.4	631.4	688.1
147.5°	432.1	452.7	522.9	605.4	654.4
150°	447.0	461.2	524.6	596.8	631.2
152.5°	458.6	473.6	526.3	585.1	617.1
155°	473.9	485.0	530.8	570.7	593.9
157.5°	492.9	499.6	531.8	564.1	580.7
160°	502.9	507.9	536.0	559.1	573.2
162.5°	508.7	514.5	536.8	554.9	565.8
165°	523.6	525.6	537.0	548.6	556.7
167.5°	533.7	531.9	541.8	547.0	550.3
170°	537.0	536.0	540.1	541.3	545.3
172.5°	544.5	541.0	542.6	539.6	542.8
175°	548.4	545.4	543.2	540.0	536.0
177.5°	550.1	545.2	542.6	539.3	540.1
180°	544.3	544.3	544.3	544.3	544.3

(END OF REPORT)