

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562289

Luminaire Tested: **SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562289
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8598.5 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 79.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562289
CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562289

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	58	57	56	51
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	48	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	37	44	38	33	38	34	30	33	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18785	18785	18785
5°	18906	18757	18674
10°	18756	18604	18504
15°	18557	18351	18283
20°	18335	18053	18018
25°	18079	17750	17696
30°	17697	17429	17315
35°	17194	16952	16851
40°	16658	16399	16334
45°	16010	15800	15729
50°	15347	15217	15114
55°	14630	14630	14398
60°	13738	14002	13505
65°	12570	13197	12258
70°	11082	12147	10790
75°	9464	10872	9208
80°	7337	9149	7433
85°	4742	7029	6267



TEST NUMBER: P562289

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.7	2.2
10°-20°	541.3	6.3
20°-30°	802.9	9.3
30°-40°	939.5	10.9
40°-50°	935.3	10.9
50°-60°	807.7	9.4
60°-70°	581.4	6.8
70°-80°	304.9	3.5
80°-90°	75.6	0.9
90°-100°	250.8	2.9
100°-110°	713.5	8.3
110°-120°	683.6	8.0
120°-130°	541.0	6.3
130°-140°	434.3	5.1
140°-150°	340.0	4.0
150°-160°	248.8	2.9
160°-170°	154.1	1.8
170°-180°	52.3	0.6
0°-30°	1535.9	17.9
0°-40°	2475.4	28.8
0°-60°	4218.4	49.1
0°-90°	5180.3	60.2
90°-120°	1647.8	19.2
90°-150°	2963.1	34.5
90°-180°	3418.0	39.8
0°-180°	8598.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2036	2036	2036	2036	2036	
5°	2041	2019	2025	2020	2016	193
15°	1943	1918	1921	1918	1914	548
25°	1776	1746	1744	1733	1738	817
35°	1527	1506	1505	1491	1496	954
45°	1227	1216	1211	1207	1206	947
55°	910	908	910	897	895	811
65°	576	593	604	581	562	571
75°	266	290	305	285	258	285
85°	45	59	66	63	59	59
90°	0	0	0	0	0	3
95°	27	108	485	168	104	31
105°	111	168	727	1284	1221	117
115°	206	249	551	1168	1372	203
125°	291	322	526	873	1044	260
135°	356	385	520	738	834	274
145°	420	441	524	638	696	262
155°	479	490	537	577	600	221
165°	529	531	543	555	563	149
175°	554	551	549	546	542	53
180°	550	550	550	550	550	



TEST NUMBER: P562289

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2036.0	2036.0	2036.0	2036.0	2036.0
2.5°	2047.5	2030.7	2036.0	2031.5	2021.7
5°	2041.4	2018.6	2025.3	2019.8	2016.3
7.5°	2020.6	1999.6	2004.5	1998.7	1996.6
10°	2002.0	1980.9	1985.8	1978.6	1975.1
12.5°	1980.4	1958.0	1962.9	1955.6	1953.5
15°	1942.8	1918.2	1921.2	1917.6	1914.1
17.5°	1899.0	1874.1	1874.6	1868.8	1868.1
20°	1867.4	1841.1	1838.7	1831.6	1835.1
22.5°	1833.0	1805.3	1802.8	1792.9	1797.8
25°	1775.9	1746.1	1743.6	1733.0	1738.3
27.5°	1709.9	1680.5	1680.5	1665.6	1671.2
30°	1661.1	1633.1	1636.0	1618.2	1625.3
32.5°	1609.5	1584.2	1585.8	1568.0	1575.0
35°	1526.6	1505.5	1505.1	1490.8	1496.1
37.5°	1441.9	1423.3	1420.4	1412.2	1413.6
40°	1383.1	1367.3	1361.6	1356.2	1356.2
42.5°	1321.4	1307.0	1301.3	1297.3	1295.9
45°	1227.0	1216.5	1210.9	1207.2	1205.5
47.5°	1133.7	1123.9	1119.0	1116.5	1114.7
50°	1069.2	1062.1	1060.2	1054.8	1053.0
52.5°	1004.6	1000.4	998.5	991.6	989.9
55°	909.5	907.7	909.5	896.9	895.1
57.5°	810.5	813.3	819.1	802.1	797.9
60°	744.5	751.5	758.8	738.9	731.9
62.5°	677.0	688.2	698.5	675.7	665.9
65°	575.8	593.4	604.5	580.8	561.5
67.5°	478.2	500.0	513.4	487.8	466.0
70°	410.8	435.4	450.3	424.6	400.0
72.5°	352.0	379.3	391.4	367.2	342.6
75°	265.5	290.0	305.0	284.6	258.3
77.5°	188.4	211.5	223.9	206.2	184.4
80°	138.1	162.7	172.2	157.5	139.9
82.5°	97.9	118.3	124.9	116.0	104.0
85°	44.8	58.9	66.4	62.7	59.2
87.5°	11.5	21.3	27.3	27.3	28.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.4	44.4	102.9	30.0	22.6
95°	27.2	108.0	485.4	168.0	103.6
97.5°	50.0	126.5	747.6	535.0	366.6
100°	65.9	137.5	804.5	814.9	627.7
102.5°	83.5	149.4	792.0	1043.1	879.6
105°	110.9	168.2	727.1	1284.3	1220.9
107.5°	138.7	190.1	651.3	1352.3	1408.8
110°	158.0	206.0	607.8	1326.3	1453.1

TEST NUMBER: P562289

CATALOG NUMBER: SQ4-PW1-075U-125D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	222.0	578.5	1264.7	1445.6
115°	206.1	249.1	551.3	1168.0	1371.5
117.5°	232.2	272.6	535.2	1062.2	1277.8
120°	253.2	286.9	533.5	1001.7	1208.3
122.5°	269.9	303.7	529.4	948.6	1140.5
125°	290.8	322.5	526.2	873.2	1044.1
127.5°	313.6	343.3	524.5	828.2	969.0
130°	325.4	355.0	522.0	796.8	919.6
132.5°	337.9	366.8	522.0	772.3	885.3
135°	355.7	385.4	519.9	737.6	833.8
137.5°	372.4	401.3	519.7	708.3	791.3
140°	385.0	414.7	518.9	683.9	763.7
142.5°	399.2	424.0	521.4	664.5	736.1
145°	419.5	441.0	524.1	638.4	695.7
147.5°	436.9	457.7	528.7	612.1	661.6
150°	451.9	466.3	530.4	603.4	638.2
152.5°	463.7	478.8	532.1	591.6	623.9
155°	479.1	490.4	536.7	577.0	600.5
157.5°	498.4	505.1	537.7	570.3	587.1
160°	508.4	513.6	541.9	565.3	579.6
162.5°	514.3	520.2	542.8	561.0	572.0
165°	529.4	531.4	543.0	554.7	562.8
167.5°	539.6	537.8	547.8	553.1	556.4
170°	543.0	541.9	546.1	547.2	551.3
172.5°	550.5	547.0	548.6	545.5	548.8
175°	554.5	551.4	549.2	546.0	541.9
177.5°	556.1	551.2	548.6	545.3	546.1
180°	550.3	550.3	550.3	550.3	550.3

(END OF REPORT)