

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562180

Luminaire Tested: **SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562180
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6590.3 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562180
CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562180

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	72	
1	103	98	94	91	97	93	90	87	84	81	79	76	74	72	68	66	65	65	65	65	61	
2	94	86	80	75	89	82	76	71	74	69	66	67	63	60	60	57	55	55	55	55	51	
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	47	47	43	
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	47	44	40	47	44	40	37	
5	72	60	52	45	68	57	50	44	52	46	41	47	42	38	43	39	35	43	39	35	32	
6	67	54	46	40	63	52	44	38	47	41	36	43	38	33	39	34	31	39	34	31	29	
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	35	31	28	35	31	28	25	
8	57	45	37	31	54	43	35	30	39	33	28	36	30	27	33	28	25	33	28	25	23	
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	30	26	22	20	
10	50	38	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	28	24	20	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17179	17179	17179
5°	17290	17154	17078
10°	17152	17014	16921
15°	16970	16782	16719
20°	16768	16510	16478
25°	16533	16233	16183
30°	16184	15940	15834
35°	15724	15503	15410
40°	15233	14997	14937
45°	14641	14449	14384
50°	14035	13917	13822
55°	13378	13378	13168
60°	12562	12804	12350
65°	11496	12070	11210
70°	10135	11109	9868
75°	8655	9942	8420
80°	6711	8368	6801
85°	4340	6426	5727



TEST NUMBER: P562180

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.3	2.7
10°-20°	495.0	7.5
20°-30°	734.3	11.1
30°-40°	859.2	13.0
40°-50°	855.3	13.0
50°-60°	738.6	11.2
60°-70°	531.7	8.1
70°-80°	278.8	4.2
80°-90°	69.1	1.0
90°-100°	135.9	2.1
100°-110°	386.8	5.9
110°-120°	370.6	5.6
120°-130°	293.3	4.5
130°-140°	235.4	3.6
140°-150°	184.3	2.8
150°-160°	134.8	2.0
160°-170°	83.5	1.3
170°-180°	28.3	0.4
0°-30°	1404.6	21.3
0°-40°	2263.8	34.4
0°-60°	3857.8	58.5
0°-90°	4737.4	71.9
90°-120°	893.2	13.6
90°-150°	1606.2	24.4
90°-180°	1853.0	28.1
0°-180°	6590.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1862	1862	1862	1862	1862	
5°	1867	1846	1852	1847	1844	177
15°	1777	1754	1757	1754	1750	501
25°	1624	1597	1595	1585	1590	747
35°	1396	1377	1376	1363	1368	873
45°	1122	1112	1107	1104	1102	866
55°	832	830	832	820	819	742
65°	527	543	553	531	514	522
75°	243	265	279	260	236	260
85°	41	54	61	57	54	54
90°	0	0	0	0	0	2
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	

TEST NUMBER: P562180

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1862.0	1862.0	1862.0	1862.0	1862.0
2.5°	1872.5	1857.1	1862.0	1857.9	1848.9
5°	1866.9	1846.1	1852.2	1847.2	1844.0
7.5°	1847.9	1828.6	1833.1	1827.8	1825.9
10°	1830.8	1811.6	1816.1	1809.4	1806.2
12.5°	1811.1	1790.6	1795.1	1788.5	1786.5
15°	1776.7	1754.2	1757.0	1753.7	1750.4
17.5°	1736.7	1713.9	1714.4	1709.1	1708.4
20°	1707.8	1683.7	1681.5	1675.1	1678.3
22.5°	1676.3	1650.9	1648.7	1639.6	1644.1
25°	1624.1	1596.9	1594.6	1584.9	1589.7
27.5°	1563.8	1536.8	1536.8	1523.2	1528.3
30°	1519.1	1493.5	1496.2	1479.9	1486.3
32.5°	1471.9	1448.8	1450.2	1434.0	1440.4
35°	1396.1	1376.8	1376.4	1363.4	1368.2
37.5°	1318.7	1301.7	1299.0	1291.5	1292.7
40°	1264.8	1250.4	1245.2	1240.2	1240.2
42.5°	1208.4	1195.3	1190.0	1186.4	1185.1
45°	1122.1	1112.5	1107.4	1104.0	1102.4
47.5°	1036.8	1027.8	1023.4	1021.0	1019.4
50°	977.8	971.3	969.6	964.6	963.0
52.5°	918.7	914.8	913.1	906.8	905.2
55°	831.7	830.1	831.7	820.2	818.6
57.5°	741.2	743.8	749.1	733.6	729.7
60°	680.8	687.2	693.9	675.8	669.3
62.5°	619.1	629.4	638.8	617.9	609.0
65°	526.6	542.6	552.9	531.1	513.5
67.5°	437.4	457.3	469.5	446.1	426.2
70°	375.7	398.1	411.8	388.3	365.8
72.5°	321.9	346.9	358.0	335.8	313.3
75°	242.8	265.3	278.9	260.3	236.2
77.5°	172.3	193.4	204.7	188.5	168.6
80°	126.3	148.8	157.5	144.0	128.0
82.5°	89.6	108.2	114.2	106.1	95.2
85°	41.0	53.8	60.7	57.3	54.1
87.5°	10.5	19.5	24.9	25.0	26.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7

TEST NUMBER: P562180

CATALOG NUMBER: SQ4-PW1-025U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)