

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562300

Luminaire Tested: **SQ4-PW1-0U-050D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562300  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-0U-050D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2022.9 lumens  
Efficiency: N/A  
Efficacy: 97.7 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562300

CATALOG NUMBER: SQ4-PW1-0U-050D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562300

CATALOG NUMBER: SQ4-PW1-0U-050D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85				
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71				
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60				
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52				
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45				
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40				
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35				
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31				
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28				
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7336	7336	7336
5°	7383	7325	7292
10°	7324	7265	7226
15°	7247	7167	7139
20°	7160	7050	7036
25°	7060	6932	6910
30°	6911	6807	6762
35°	6714	6619	6580
40°	6505	6404	6378
45°	6253	6169	6142
50°	5993	5942	5902
55°	5714	5714	5623
60°	5364	5467	5274
65°	4910	5154	4788
70°	4327	4742	4214
75°	3697	4246	3597
80°	2864	3570	2901
85°	1853	2742	2445



TEST NUMBER: P562300

CATALOG NUMBER: SQ4-PW1-0U-050D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.9	3.7
10°-20°	211.4	10.4
20°-30°	313.5	15.5
30°-40°	366.9	18.1
40°-50°	365.2	18.1
50°-60°	315.4	15.6
60°-70°	227.0	11.2
70°-80°	119.1	5.9
80°-90°	29.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.8	29.6
0°-40°	966.7	47.8
0°-60°	1647.3	81.4
0°-90°	2022.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2022.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	795	795	795	795	795	
5°	797	788	791	789	787	76
15°	759	749	750	749	747	214
25°	694	682	681	677	679	319
35°	596	588	588	582	584	373
45°	479	475	473	471	471	370
55°	355	354	355	350	350	317
65°	225	232	236	227	219	223
75°	104	113	119	111	101	111
85°	18	23	26	24	23	24
90°	0	0	0	0	0	



TEST NUMBER: P562300

CATALOG NUMBER: SQ4-PW1-0U-050D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	795.1	795.1	795.1	795.1	795.1
2.5°	799.6	793.0	795.1	793.3	789.5
5°	797.2	788.3	790.9	788.7	787.4
7.5°	789.1	780.8	782.8	780.5	779.7
10°	781.8	773.6	775.5	772.6	771.3
12.5°	773.4	764.6	766.5	763.7	762.9
15°	758.7	749.1	750.3	748.8	747.4
17.5°	741.6	731.8	732.0	729.8	729.5
20°	729.2	719.0	718.0	715.3	716.6
22.5°	715.8	705.0	704.0	700.1	702.1
25°	693.5	681.9	680.9	676.7	678.8
27.5°	667.7	656.2	656.2	650.4	652.6
30°	648.7	637.7	638.9	631.9	634.7
32.5°	628.5	618.6	619.3	612.3	615.1
35°	596.1	587.9	587.7	582.2	584.2
37.5°	563.1	555.8	554.7	551.5	552.0
40°	540.1	533.9	531.7	529.6	529.6
42.5°	516.0	510.4	508.2	506.6	506.1
45°	479.2	475.0	472.8	471.4	470.7
47.5°	442.7	438.9	437.0	436.0	435.3
50°	417.5	414.8	414.0	411.9	411.2
52.5°	392.3	390.6	389.9	387.2	386.5
55°	355.2	354.5	355.2	350.2	349.6
57.5°	316.5	317.6	319.9	313.2	311.6
60°	290.7	293.5	296.3	288.5	285.8
62.5°	264.4	268.8	272.8	263.9	260.0
65°	224.9	231.7	236.1	226.8	219.3
67.5°	186.8	195.3	200.5	190.5	182.0
70°	160.4	170.0	175.8	165.8	156.2
72.5°	137.4	148.1	152.9	143.4	133.8
75°	103.7	113.3	119.1	111.1	100.9
77.5°	73.6	82.6	87.4	80.5	72.0
80°	53.9	63.5	67.2	61.5	54.6
82.5°	38.2	46.2	48.8	45.3	40.6
85°	17.5	23.0	25.9	24.5	23.1
87.5°	4.5	8.3	10.6	10.7	11.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)