

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562323

Luminaire Tested: **SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562323  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3741.8 lumens  
Efficiency: N/A  
Efficacy: 88.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 42.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562323

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562323

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13569	13569	13569
5°	13657	13549	13488
10°	13548	13438	13365
15°	13404	13256	13206
20°	13244	13041	13015
25°	13059	12822	12782
30°	12783	12589	12507
35°	12420	12244	12172
40°	12032	11845	11798
45°	11564	11412	11362
50°	11085	10992	10917
55°	10568	10568	10401
60°	9922	10114	9756
65°	9080	9534	8855
70°	8004	8772	7796
75°	6837	7853	6652
80°	5303	6610	5372
85°	3430	5071	4531



TEST NUMBER: P562323

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.5	3.7
10°-20°	391.0	10.4
20°-30°	580.0	15.5
30°-40°	678.6	18.1
40°-50°	675.6	18.1
50°-60°	583.4	15.6
60°-70°	419.9	11.2
70°-80°	220.2	5.9
80°-90°	54.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.5	29.6
0°-40°	1788.1	47.8
0°-60°	3047.1	81.4
0°-90°	3741.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3741.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1471	1471	1471	1471	1471	
5°	1475	1458	1463	1459	1456	140
15°	1403	1386	1388	1385	1383	396
25°	1283	1261	1260	1252	1256	590
35°	1103	1088	1087	1077	1081	689
45°	886	879	875	872	871	684
55°	657	656	657	648	647	586
65°	416	429	437	420	406	412
75°	192	210	220	206	187	206
85°	32	42	48	45	43	44
90°	0	0	0	0	0	



TEST NUMBER: P562323

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1470.7	1470.7	1470.7	1470.7	1470.7
2.5°	1479.0	1466.8	1470.7	1467.4	1460.3
5°	1474.6	1458.1	1462.9	1459.0	1456.4
7.5°	1459.5	1444.3	1447.9	1443.7	1442.2
10°	1446.1	1430.9	1434.4	1429.2	1426.6
12.5°	1430.5	1414.3	1417.8	1412.6	1411.1
15°	1403.3	1385.6	1387.8	1385.1	1382.6
17.5°	1371.7	1353.7	1354.1	1349.9	1349.4
20°	1348.9	1329.9	1328.2	1323.0	1325.6
22.5°	1324.0	1304.0	1302.2	1295.1	1298.6
25°	1282.8	1261.3	1259.5	1251.8	1255.6
27.5°	1235.1	1213.8	1213.9	1203.1	1207.1
30°	1199.9	1179.6	1181.7	1168.9	1174.0
32.5°	1162.6	1144.3	1145.5	1132.6	1137.7
35°	1102.7	1087.5	1087.1	1076.9	1080.7
37.5°	1041.5	1028.1	1026.0	1020.0	1021.1
40°	999.0	987.6	983.5	979.6	979.6
42.5°	954.5	944.1	939.9	937.1	936.1
45°	886.3	878.7	874.6	872.0	870.8
47.5°	818.9	811.8	808.3	806.5	805.2
50°	772.3	767.2	765.8	761.9	760.6
52.5°	725.6	722.6	721.2	716.3	715.0
55°	657.0	655.7	657.0	647.9	646.6
57.5°	585.4	587.5	591.6	579.4	576.4
60°	537.7	542.8	548.1	533.7	528.7
62.5°	489.0	497.1	504.6	488.1	481.0
65°	415.9	428.6	436.7	419.5	405.6
67.5°	345.5	361.2	370.8	352.3	336.6
70°	296.7	314.5	325.2	306.7	289.0
72.5°	254.2	274.0	282.7	265.2	247.5
75°	191.8	209.5	220.3	205.6	186.6
77.5°	136.1	152.8	161.7	148.9	133.2
80°	99.8	117.5	124.4	113.7	101.1
82.5°	70.7	85.4	90.2	83.8	75.2
85°	32.4	42.5	47.9	45.3	42.8
87.5°	8.3	15.4	19.7	19.7	20.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)