

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562195

Luminaire Tested: **SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562195
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4169.3 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562195
CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562195

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	72	64	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	63	56	50	68	59	52	46	50	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	29	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7204	7204	7204
5°	7251	7193	7161
10°	7192	7134	7096
15°	7116	7038	7011
20°	7031	6923	6910
25°	6933	6807	6786
30°	6786	6684	6640
35°	6593	6501	6462
40°	6388	6288	6264
45°	6139	6059	6032
50°	5885	5836	5796
55°	5611	5611	5522
60°	5268	5370	5180
65°	4820	5060	4700
70°	4249	4659	4138
75°	3629	4167	3533
80°	2816	3507	2853
85°	1821	2699	2403



TEST NUMBER: P562195

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.5	1.8
10°-20°	207.6	5.0
20°-30°	307.9	7.4
30°-40°	360.3	8.6
40°-50°	358.7	8.6
50°-60°	309.7	7.4
60°-70°	223.0	5.3
70°-80°	116.9	2.8
80°-90°	29.0	0.7
90°-100°	160.1	3.8
100°-110°	455.6	10.9
110°-120°	436.5	10.5
120°-130°	345.5	8.3
130°-140°	277.3	6.7
140°-150°	217.1	5.2
150°-160°	158.8	3.8
160°-170°	98.4	2.4
170°-180°	33.4	0.8
0°-30°	589.0	14.1
0°-40°	949.3	22.8
0°-60°	1617.7	38.8
0°-90°	1986.6	47.6
90°-120°	1052.2	25.2
90°-150°	1892.1	45.4
90°-180°	2183.0	52.4
0°-180°	4169.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	781	781	781	781	781	
5°	783	774	777	775	773	74
15°	745	736	737	735	734	210
25°	681	670	669	665	667	313
35°	585	577	577	572	574	366
45°	470	466	464	463	462	363
55°	349	348	349	344	343	311
65°	221	228	232	223	215	219
75°	102	111	117	109	99	109
85°	17	23	26	24	23	23
90°	0	0	0	0	0	1
95°	17	69	310	107	66	20
105°	71	107	464	820	780	75
115°	132	159	352	746	876	130
125°	186	206	336	558	667	166
135°	227	246	332	471	532	175
145°	268	282	335	408	444	167
155°	306	313	343	368	384	141
165°	338	339	347	354	359	95
175°	354	352	351	349	346	34
180°	351	351	351	351	351	



TEST NUMBER: P562195

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	780.8	780.8	780.8	780.8	780.8
2.5°	785.2	778.7	780.8	779.1	775.3
5°	782.9	774.1	776.7	774.6	773.2
7.5°	774.9	766.8	768.7	766.5	765.7
10°	767.7	759.7	761.5	758.8	757.4
12.5°	759.5	750.9	752.7	750.0	749.2
15°	745.0	735.6	736.8	735.4	734.0
17.5°	728.2	718.7	718.9	716.7	716.4
20°	716.1	706.0	705.1	702.4	703.8
22.5°	702.9	692.3	691.4	687.6	689.4
25°	681.0	669.6	668.7	664.6	666.6
27.5°	655.7	644.4	644.5	638.7	640.9
30°	637.0	626.3	627.4	620.6	623.3
32.5°	617.2	607.5	608.1	601.3	604.0
35°	585.4	577.4	577.2	571.7	573.7
37.5°	553.0	545.8	544.7	541.5	542.1
40°	530.4	524.3	522.1	520.1	520.1
42.5°	506.7	501.2	499.0	497.5	497.0
45°	470.5	466.5	464.4	463.0	462.3
47.5°	434.8	431.0	429.1	428.2	427.5
50°	410.0	407.3	406.6	404.5	403.8
52.5°	385.2	383.6	382.9	380.3	379.6
55°	348.8	348.1	348.8	343.9	343.3
57.5°	310.8	311.9	314.1	307.6	306.0
60°	285.5	288.2	291.0	283.4	280.7
62.5°	259.6	263.9	267.9	259.1	255.4
65°	220.8	227.6	231.8	222.7	215.3
67.5°	183.4	191.7	196.9	187.1	178.7
70°	157.5	167.0	172.7	162.8	153.4
72.5°	135.0	145.5	150.1	140.8	131.4
75°	101.8	111.2	116.9	109.2	99.1
77.5°	72.2	81.1	85.9	79.1	70.7
80°	53.0	62.4	66.0	60.4	53.7
82.5°	37.6	45.4	47.9	44.5	39.9
85°	17.2	22.6	25.5	24.0	22.7
87.5°	4.4	8.2	10.5	10.5	11.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.3	28.3	65.7	19.1	14.4
95°	17.4	69.0	310.0	107.3	66.1
97.5°	31.9	80.8	477.4	341.6	234.1
100°	42.1	87.8	513.7	520.4	400.8
102.5°	53.3	95.4	505.7	666.1	561.7
105°	70.8	107.4	464.3	820.1	779.6
107.5°	88.6	121.4	415.9	863.5	899.6
110°	100.9	131.6	388.1	846.9	927.9



TEST NUMBER: P562195

CATALOG NUMBER: SQ4-PW1-050U-050D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	112.6	141.8	369.4	807.6	923.1
115°	131.6	159.0	352.1	745.8	875.8
117.5°	148.3	174.0	341.8	678.3	815.9
120°	161.7	183.2	340.7	639.6	771.6
122.5°	172.4	193.9	338.0	605.8	728.3
125°	185.7	206.0	336.0	557.6	666.7
127.5°	200.3	219.2	335.0	528.9	618.7
130°	207.8	226.7	333.4	508.8	587.2
132.5°	215.8	234.2	333.4	493.2	565.3
135°	227.1	246.1	332.0	471.0	532.4
137.5°	237.8	256.2	331.9	452.3	505.3
140°	245.8	264.8	331.3	436.7	487.7
142.5°	254.9	270.7	333.0	424.3	470.0
145°	267.9	281.6	334.7	407.7	444.2
147.5°	279.0	292.3	337.6	390.9	422.5
150°	288.6	297.7	338.7	385.3	407.5
152.5°	296.1	305.7	339.8	377.8	398.4
155°	306.0	313.1	342.7	368.4	383.5
157.5°	318.3	322.6	343.4	364.2	374.9
160°	324.7	327.9	346.0	361.0	370.1
162.5°	328.4	332.2	346.6	358.2	365.3
165°	338.0	339.3	346.7	354.2	359.4
167.5°	344.6	343.4	349.8	353.2	355.3
170°	346.7	346.1	348.7	349.4	352.1
172.5°	351.5	349.3	350.3	348.4	350.5
175°	354.1	352.1	350.7	348.7	346.0
177.5°	355.1	352.0	350.3	348.2	348.7
180°	351.4	351.4	351.4	351.4	351.4

(END OF REPORT)