

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562337

Luminaire Tested: **SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562337
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4835.6 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562337
CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562337

CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17535	17535	17535
5°	17649	17509	17432
10°	17508	17366	17273
15°	17322	17130	17066
20°	17115	16852	16819
25°	16876	16569	16518
30°	16519	16270	16162
35°	16050	15824	15730
40°	15550	15308	15246
45°	14945	14748	14683
50°	14325	14204	14108
55°	13656	13656	13441
60°	12823	13070	12607
65°	11734	12319	11442
70°	10345	11338	10073
75°	8833	10149	8595
80°	6849	8544	6939
85°	4435	6563	5854



TEST NUMBER: P562337

CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	3.7
10°-20°	505.3	10.4
20°-30°	749.5	15.5
30°-40°	877.0	18.1
40°-50°	873.1	18.1
50°-60°	753.9	15.6
60°-70°	542.7	11.2
70°-80°	284.6	5.9
80°-90°	70.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1433.8	29.6
0°-40°	2310.7	47.8
0°-60°	3937.8	81.4
0°-90°	4835.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4835.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1901	1901	1901	1901	1901	
5°	1906	1884	1890	1885	1882	180
15°	1814	1791	1793	1790	1787	511
25°	1658	1630	1628	1618	1623	762
35°	1425	1405	1405	1392	1397	891
45°	1145	1136	1130	1127	1125	884
55°	849	847	849	837	836	757
65°	538	554	564	542	524	533
75°	248	271	285	266	241	266
85°	42	55	62	58	55	57
90°	0	0	0	0	0	



TEST NUMBER: P562337

CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1900.6	1900.6	1900.6	1900.6	1900.6
2.5°	1911.3	1895.6	1900.6	1896.4	1887.2
5°	1905.6	1884.3	1890.5	1885.4	1882.2
7.5°	1886.2	1866.5	1871.1	1865.7	1863.7
10°	1868.8	1849.1	1853.7	1846.9	1843.7
12.5°	1848.7	1827.7	1832.3	1825.5	1823.6
15°	1813.5	1790.6	1793.4	1790.0	1786.7
17.5°	1772.7	1749.4	1749.9	1744.5	1743.9
20°	1743.2	1718.6	1716.4	1709.8	1713.0
22.5°	1711.0	1685.2	1682.9	1673.6	1678.2
25°	1657.8	1629.9	1627.6	1617.7	1622.6
27.5°	1596.2	1568.7	1568.7	1554.8	1560.0
30°	1550.6	1524.4	1527.2	1510.6	1517.1
32.5°	1502.4	1478.8	1480.3	1463.7	1470.2
35°	1425.0	1405.4	1404.9	1391.6	1396.6
37.5°	1346.0	1328.6	1325.9	1318.2	1319.5
40°	1291.1	1276.3	1271.0	1265.9	1265.9
42.5°	1233.5	1220.0	1214.7	1211.0	1209.7
45°	1145.4	1135.6	1130.3	1126.9	1125.3
47.5°	1058.3	1049.1	1044.6	1042.2	1040.6
50°	998.0	991.5	989.6	984.6	982.9
52.5°	937.7	933.8	932.0	925.6	924.0
55°	849.0	847.3	849.0	837.2	835.6
57.5°	756.6	759.2	764.6	748.8	744.8
60°	694.9	701.5	708.3	689.8	683.2
62.5°	632.0	642.4	652.1	630.8	621.6
65°	537.5	553.9	564.3	542.1	524.1
67.5°	446.4	466.7	479.2	455.3	435.0
70°	383.5	406.4	420.3	396.3	373.4
72.5°	328.5	354.1	365.4	342.8	319.8
75°	247.8	270.8	284.7	265.7	241.1
77.5°	175.8	197.4	209.0	192.4	172.1
80°	128.9	151.9	160.8	147.0	130.6
82.5°	91.4	110.4	116.5	108.3	97.1
85°	41.9	55.0	62.0	58.5	55.3
87.5°	10.7	19.9	25.5	25.5	26.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)