

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562342

Luminaire Tested: **SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562342  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5254.0 lumens  
Efficiency: N/A  
Efficacy: 94.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 55.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562342  
CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562342

CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19053	19053	19053
5°	19176	19024	18940
10°	19023	18869	18767
15°	18821	18612	18543
20°	18596	18310	18275
25°	18336	18003	17947
30°	17949	17677	17561
35°	17439	17193	17091
40°	16895	16631	16566
45°	16238	16024	15954
50°	15565	15434	15329
55°	14839	14839	14604
60°	13933	14201	13697
65°	12749	13385	12433
70°	11238	12320	10944
75°	9600	11026	9340
80°	7444	9282	7539
85°	4817	7124	6352



TEST NUMBER: P562342

CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	194.5	3.7
10°-20°	549.0	10.4
20°-30°	814.4	15.5
30°-40°	952.9	18.1
40°-50°	948.6	18.1
50°-60°	819.2	15.6
60°-70°	589.6	11.2
70°-80°	309.2	5.9
80°-90°	76.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1557.8	29.6
0°-40°	2510.7	47.8
0°-60°	4278.5	81.4
0°-90°	5254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5254.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2065	2065	2065	2065	2065	
5°	2070	2047	2054	2049	2045	196
15°	1970	1946	1949	1945	1941	555
25°	1801	1771	1768	1758	1763	828
35°	1548	1527	1526	1512	1517	968
45°	1244	1234	1228	1224	1223	960
55°	922	921	922	910	908	823
65°	584	602	613	589	570	579
75°	269	294	309	289	262	289
85°	46	60	67	64	60	62
90°	0	0	0	0	0	



TEST NUMBER: P562342

CATALOG NUMBER: SQ4-PW1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2065.1	2065.1	2065.1	2065.1	2065.1
2.5°	2076.7	2059.6	2065.1	2060.5	2050.5
5°	2070.5	2047.4	2054.1	2048.6	2045.0
7.5°	2049.4	2028.1	2033.0	2027.2	2025.0
10°	2030.5	2009.1	2014.1	2006.7	2003.2
12.5°	2008.6	1985.9	1990.8	1983.5	1981.4
15°	1970.4	1945.5	1948.6	1944.9	1941.3
17.5°	1926.0	1900.8	1901.3	1895.5	1894.8
20°	1894.0	1867.3	1864.9	1857.7	1861.3
22.5°	1859.1	1831.0	1828.5	1818.4	1823.4
25°	1801.2	1771.0	1768.5	1757.7	1763.0
27.5°	1734.3	1704.4	1704.4	1689.3	1695.0
30°	1684.8	1656.3	1659.3	1641.3	1648.4
32.5°	1632.4	1606.8	1608.4	1590.3	1597.5
35°	1548.3	1527.0	1526.5	1512.1	1517.4
37.5°	1462.5	1443.6	1440.6	1432.3	1433.7
40°	1402.8	1386.8	1380.9	1375.5	1375.5
42.5°	1340.2	1325.6	1319.8	1315.8	1314.4
45°	1244.5	1233.8	1228.1	1224.4	1222.7
47.5°	1149.9	1139.9	1135.0	1132.4	1130.6
50°	1084.4	1077.3	1075.3	1069.8	1068.0
52.5°	1018.9	1014.6	1012.7	1005.7	1004.0
55°	922.5	920.7	922.5	909.7	907.9
57.5°	822.0	824.9	830.8	813.6	809.3
60°	755.1	762.2	769.6	749.4	742.3
62.5°	686.7	698.0	708.5	685.3	675.4
65°	584.0	601.8	613.1	589.1	569.5
67.5°	485.1	507.1	520.7	494.7	472.7
70°	416.6	441.6	456.7	430.6	405.7
72.5°	357.0	384.7	397.0	372.4	347.5
75°	269.3	294.2	309.3	288.7	262.0
77.5°	191.0	214.5	227.1	209.1	187.0
80°	140.1	165.0	174.7	159.7	141.9
82.5°	99.3	120.0	126.6	117.6	105.5
85°	45.5	59.7	67.3	63.6	60.0
87.5°	11.6	21.6	27.7	27.7	29.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)