

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562356

Luminaire Tested: **SQ4-PW1-100U-050D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562356
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-050D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6811.4 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 52.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562356
CATALOG NUMBER: SQ4-PW1-100U-050D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562356

CATALOG NUMBER: SQ4-PW1-100U-050D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	34	34	33	26
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7716	7716	7716
5°	7766	7705	7670
10°	7704	7642	7601
15°	7622	7538	7510
20°	7532	7416	7401
25°	7426	7291	7269
30°	7269	7159	7112
35°	7063	6963	6921
40°	6842	6736	6710
45°	6576	6490	6461
50°	6304	6251	6208
55°	6010	6010	5915
60°	5643	5752	5547
65°	5163	5421	5034
70°	4551	4990	4432
75°	3889	4467	3782
80°	3013	3756	3055
85°	1948	2890	2572



TEST NUMBER: P562356

CATALOG NUMBER: SQ4-PW1-100U-050D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.8	1.2
10°-20°	222.3	3.3
20°-30°	329.8	4.8
30°-40°	385.9	5.7
40°-50°	384.2	5.6
50°-60°	331.8	4.9
60°-70°	238.8	3.5
70°-80°	125.2	1.8
80°-90°	31.1	0.5
90°-100°	343.6	5.0
100°-110°	977.6	14.4
110°-120°	936.6	13.8
120°-130°	741.3	10.9
130°-140°	595.0	8.7
140°-150°	465.8	6.8
150°-160°	340.8	5.0
160°-170°	211.1	3.1
170°-180°	71.6	1.1
0°-30°	630.9	9.3
0°-40°	1016.8	14.9
0°-60°	1732.8	25.4
0°-90°	2127.9	31.2
90°-120°	2257.8	33.1
90°-150°	4059.9	59.6
90°-180°	4684.0	68.8
0°-180°	6811.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	838	829	832	830	828	79
15°	798	788	789	788	786	225
25°	730	717	716	712	714	335
35°	627	618	618	612	614	392
45°	504	500	497	496	495	389
55°	374	373	374	368	368	333
65°	236	244	248	239	231	234
75°	109	119	125	117	106	117
85°	18	24	27	26	24	24
90°	0	0	0	0	0	2
95°	37	148	665	230	142	43
105°	152	230	996	1760	1673	161
115°	282	341	755	1600	1879	278
125°	398	442	721	1196	1431	357
135°	487	528	712	1011	1142	376
145°	575	604	718	875	953	359
155°	656	672	735	791	823	303
165°	725	728	744	760	771	204
175°	760	756	753	748	742	72
180°	754	754	754	754	754	

TEST NUMBER: P562356

CATALOG NUMBER: SQ4-PW1-100U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	836.3	836.3	836.3	836.3	836.3
2.5°	841.1	834.1	836.3	834.5	830.4
5°	838.5	829.2	831.9	829.7	828.2
7.5°	830.0	821.4	823.4	821.0	820.1
10°	822.3	813.7	815.7	812.7	811.3
12.5°	813.5	804.3	806.3	803.3	802.4
15°	798.0	787.9	789.2	787.7	786.2
17.5°	780.0	769.8	770.0	767.7	767.4
20°	767.1	756.3	755.3	752.4	753.8
22.5°	752.9	741.5	740.5	736.5	738.5
25°	729.5	717.2	716.2	711.9	714.0
27.5°	702.4	690.3	690.3	684.2	686.5
30°	682.3	670.8	672.0	664.7	667.6
32.5°	661.1	650.7	651.4	644.1	647.0
35°	627.1	618.4	618.2	612.4	614.5
37.5°	592.3	584.7	583.4	580.1	580.6
40°	568.1	561.6	559.3	557.1	557.1
42.5°	542.8	536.9	534.5	532.9	532.3
45°	504.0	499.7	497.4	495.9	495.2
47.5°	465.7	461.7	459.7	458.6	457.9
50°	439.2	436.3	435.5	433.3	432.5
52.5°	412.6	410.9	410.1	407.3	406.6
55°	373.6	372.9	373.6	368.4	367.7
57.5°	332.9	334.1	336.5	329.5	327.8
60°	305.8	308.7	311.7	303.5	300.6
62.5°	278.1	282.7	286.9	277.6	273.5
65°	236.5	243.7	248.3	238.6	230.6
67.5°	196.4	205.4	210.9	200.4	191.4
70°	168.7	178.8	185.0	174.4	164.3
72.5°	144.6	155.8	160.8	150.8	140.7
75°	109.1	119.1	125.3	116.9	106.1
77.5°	77.4	86.9	92.0	84.7	75.7
80°	56.7	66.8	70.7	64.7	57.5
82.5°	40.2	48.6	51.3	47.6	42.7
85°	18.4	24.2	27.3	25.8	24.3
87.5°	4.7	8.8	11.2	11.2	11.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.5	60.8	141.1	41.1	31.0
95°	37.3	148.0	665.1	230.2	141.9
97.5°	68.5	173.4	1024.3	733.0	502.3
100°	90.3	188.4	1102.3	1116.6	860.1
102.5°	114.4	204.7	1085.1	1429.2	1205.2
105°	151.9	230.4	996.2	1759.7	1672.8
107.5°	190.1	260.4	892.5	1852.9	1930.3
110°	216.4	282.3	832.8	1817.3	1991.1

TEST NUMBER: P562356

CATALOG NUMBER: SQ4-PW1-100U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	241.7	304.2	792.7	1732.9	1980.7
115°	282.4	341.3	755.4	1600.3	1879.2
117.5°	318.2	373.4	733.3	1455.4	1750.8
120°	346.9	393.1	731.1	1372.5	1655.6
122.5°	369.8	416.1	725.3	1299.8	1562.7
125°	398.5	441.9	721.0	1196.5	1430.6
127.5°	429.7	470.4	718.7	1134.8	1327.7
130°	445.8	486.4	715.3	1091.8	1260.0
132.5°	463.0	502.5	715.3	1058.2	1213.0
135°	487.4	528.0	712.4	1010.7	1142.5
137.5°	510.3	549.8	712.1	970.4	1084.3
140°	527.5	568.2	711.0	937.1	1046.4
142.5°	547.0	580.9	714.4	910.5	1008.6
145°	574.8	604.2	718.2	874.7	953.2
147.5°	598.6	627.2	724.5	838.7	906.5
150°	619.2	638.9	726.8	826.7	874.4
152.5°	635.3	656.0	729.0	810.6	854.9
155°	656.5	671.9	735.4	790.6	822.8
157.5°	682.9	692.1	736.8	781.5	804.4
160°	696.7	703.7	742.5	774.5	794.1
162.5°	704.7	712.8	743.7	768.7	783.8
165°	725.3	728.1	744.0	760.0	771.2
167.5°	739.4	736.8	750.6	757.8	762.3
170°	744.0	742.6	748.3	749.8	755.4
172.5°	754.3	749.5	751.7	747.5	752.0
175°	759.7	755.5	752.6	748.1	742.5
177.5°	762.0	755.3	751.7	747.1	748.3
180°	754.0	754.0	754.0	754.0	754.0

(END OF REPORT)