

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562265

Luminaire Tested: **SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562265  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (6500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6686.5 lumens  
Efficiency: N/A  
Efficacy: 121.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 55.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562265  
CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (6500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562265

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (6500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	72	64	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	63	56	50	68	59	52	46	50	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	29	24	30	25	21	26	21	18	21	18	16	14
10	47	35	28	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11556	11556	11556
5°	11631	11539	11488
10°	11538	11445	11383
15°	11415	11289	11247
20°	11279	11106	11084
25°	11122	10919	10885
30°	10887	10722	10651
35°	10577	10429	10367
40°	10247	10088	10048
45°	9848	9719	9676
50°	9440	9361	9298
55°	9000	9000	8858
60°	8451	8614	8307
65°	7733	8119	7540
70°	6817	7472	6639
75°	5821	6687	5664
80°	4516	5627	4575
85°	2922	4319	3853



TEST NUMBER: P562265

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (6500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.9	1.8
10°-20°	333.0	5.0
20°-30°	493.9	7.4
30°-40°	578.0	8.6
40°-50°	575.4	8.6
50°-60°	496.9	7.4
60°-70°	357.6	5.3
70°-80°	187.5	2.8
80°-90°	46.5	0.7
90°-100°	256.7	3.8
100°-110°	730.5	10.9
110°-120°	699.9	10.5
120°-130°	553.9	8.3
130°-140°	444.6	6.6
140°-150°	348.1	5.2
150°-160°	254.7	3.8
160°-170°	157.8	2.4
170°-180°	53.5	0.8
0°-30°	944.9	14.1
0°-40°	1522.8	22.8
0°-60°	2595.1	38.8
0°-90°	3186.8	47.7
90°-120°	1687.1	25.2
90°-150°	3033.8	45.4
90°-180°	3500.0	52.3
0°-180°	6686.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1256	1242	1246	1242	1240	119
15°	1195	1180	1182	1180	1178	337
25°	1092	1074	1073	1066	1069	502
35°	939	926	926	917	920	587
45°	755	748	745	743	742	582
55°	560	558	560	552	551	499
65°	354	365	372	357	345	351
75°	163	178	188	175	159	175
85°	28	36	41	39	36	36
90°	0	0	0	0	0	2
95°	28	111	497	172	106	32
105°	114	172	744	1315	1250	120
115°	211	255	564	1196	1404	208
125°	298	330	539	894	1069	267
135°	364	395	532	755	854	281
145°	430	452	537	654	712	268
155°	491	502	550	591	615	227
165°	542	544	556	568	576	152
175°	568	565	562	559	555	54
180°	563	563	563	563	563	

TEST NUMBER: P562265

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1252.5	1252.5	1252.5	1252.5	1252.5
2.5°	1259.6	1249.2	1252.5	1249.7	1243.7
5°	1255.8	1241.8	1245.9	1242.5	1240.4
7.5°	1243.0	1230.1	1233.1	1229.5	1228.2
10°	1231.6	1218.6	1221.6	1217.2	1215.0
12.5°	1218.3	1204.5	1207.5	1203.1	1201.8
15°	1195.1	1180.0	1181.9	1179.6	1177.5
17.5°	1168.2	1152.9	1153.2	1149.7	1149.2
20°	1148.8	1132.6	1131.1	1126.8	1128.9
22.5°	1127.6	1110.6	1109.1	1103.0	1106.0
25°	1092.5	1074.2	1072.6	1066.1	1069.3
27.5°	1051.9	1033.8	1033.8	1024.6	1028.1
30°	1021.9	1004.6	1006.4	995.5	999.8
32.5°	990.1	974.6	975.5	964.6	968.9
35°	939.1	926.2	925.9	917.1	920.4
37.5°	887.0	875.6	873.8	868.7	869.6
40°	850.8	841.1	837.6	834.3	834.3
42.5°	812.9	804.0	800.5	798.1	797.2
45°	754.8	748.4	744.9	742.7	741.6
47.5°	697.4	691.4	688.4	686.8	685.7
50°	657.7	653.4	652.2	648.9	647.8
52.5°	618.0	615.4	614.2	610.0	608.9
55°	559.5	558.4	559.5	551.7	550.7
57.5°	498.6	500.3	503.9	493.4	490.9
60°	458.0	462.3	466.8	454.6	450.2
62.5°	416.5	423.4	429.7	415.7	409.6
65°	354.2	365.0	371.9	357.3	345.4
67.5°	294.2	307.6	315.8	300.1	286.7
70°	252.7	267.8	277.0	261.2	246.1
72.5°	216.5	233.3	240.8	225.9	210.8
75°	163.3	178.4	187.6	175.1	158.9
77.5°	115.9	130.1	137.7	126.8	113.4
80°	85.0	100.1	105.9	96.9	86.1
82.5°	60.3	72.8	76.8	71.3	64.0
85°	27.6	36.2	40.8	38.6	36.4
87.5°	7.1	13.1	16.8	16.8	17.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.6	45.4	105.4	30.7	23.1
95°	27.8	110.6	497.0	172.0	106.0
97.5°	51.2	129.5	765.4	547.7	375.3
100°	67.5	140.8	823.7	834.3	642.7
102.5°	85.5	152.9	810.8	1068.0	900.6
105°	113.5	172.2	744.4	1314.9	1250.0
107.5°	142.0	194.6	666.9	1384.6	1442.4
110°	161.7	211.0	622.3	1357.9	1487.8



TEST NUMBER: P562265

CATALOG NUMBER: SQ4-PW1-075U-075D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	180.6	227.3	592.3	1294.9	1480.1
115°	211.0	255.0	564.5	1195.8	1404.3
117.5°	237.8	279.1	548.0	1087.5	1308.3
120°	259.2	293.8	546.3	1025.6	1237.2
122.5°	276.4	310.9	542.0	971.3	1167.7
125°	297.8	330.2	538.8	894.1	1069.0
127.5°	321.1	351.5	537.1	848.0	992.1
130°	333.1	363.5	534.5	815.8	941.5
132.5°	346.0	375.5	534.5	790.8	906.4
135°	364.2	394.6	532.4	755.2	853.7
137.5°	381.3	410.9	532.1	725.2	810.2
140°	394.2	424.5	531.3	700.2	781.9
142.5°	408.7	434.1	533.9	680.3	753.6
145°	429.5	451.5	536.6	653.7	712.3
147.5°	447.3	468.7	541.4	626.7	677.4
150°	462.7	477.4	543.1	617.8	653.4
152.5°	474.7	490.2	544.8	605.7	638.8
155°	490.6	502.1	549.5	590.7	614.8
157.5°	510.3	517.2	550.6	583.9	601.1
160°	520.6	525.8	554.8	578.7	593.4
162.5°	526.6	532.6	555.7	574.4	585.7
165°	542.0	544.1	555.9	567.9	576.3
167.5°	552.5	550.6	560.8	566.3	569.6
170°	555.9	554.9	559.1	560.3	564.5
172.5°	563.6	560.1	561.7	558.6	561.9
175°	567.7	564.6	562.3	559.0	554.8
177.5°	569.4	564.4	561.7	558.3	559.1
180°	563.4	563.4	563.4	563.4	563.4

(END OF REPORT)