

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562362

Luminaire Tested: **SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562362
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7029.8 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 64.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562362
CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562362

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	40
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10322	10322	10322
5°	10389	10306	10261
10°	10305	10223	10167
15°	10196	10084	10045
20°	10075	9919	9901
25°	9934	9753	9723
30°	9725	9577	9514
35°	9447	9315	9259
40°	9153	9010	8975
45°	8797	8681	8643
50°	8433	8361	8305
55°	8038	8038	7912
60°	7549	7693	7422
65°	6907	7252	6735
70°	6088	6674	5929
75°	5201	5974	5058
80°	4033	5026	4086
85°	2604	3864	3440



TEST NUMBER: P562362

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.3	1.5
10°-20°	297.4	4.2
20°-30°	441.2	6.3
30°-40°	516.2	7.3
40°-50°	513.9	7.3
50°-60°	443.8	6.3
60°-70°	319.4	4.5
70°-80°	167.5	2.4
80°-90°	41.5	0.6
90°-100°	306.9	4.4
100°-110°	873.2	12.4
110°-120°	836.6	11.9
120°-130°	662.1	9.4
130°-140°	531.5	7.6
140°-150°	416.1	5.9
150°-160°	304.4	4.3
160°-170°	188.6	2.7
170°-180°	64.0	0.9
0°-30°	844.0	12.0
0°-40°	1360.2	19.3
0°-60°	2317.9	33.0
0°-90°	2846.4	40.5
90°-120°	2016.7	28.7
90°-150°	3626.3	51.6
90°-180°	4183.0	59.5
0°-180°	7029.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1119	1119	1119	1119	1119	
5°	1122	1109	1113	1110	1108	106
15°	1068	1054	1056	1054	1052	301
25°	976	960	958	952	955	449
35°	839	827	827	819	822	524
45°	674	668	665	663	662	520
55°	500	499	500	493	492	446
65°	316	326	332	319	308	314
75°	146	159	168	156	142	156
85°	25	32	36	34	32	32
90°	0	0	0	0	0	2
95°	33	132	594	206	127	38
105°	136	206	890	1572	1494	144
115°	252	305	675	1429	1678	248
125°	356	395	644	1069	1278	319
135°	435	472	636	903	1020	336
145°	513	540	642	781	851	321
155°	586	600	657	706	735	271
165°	648	650	664	679	689	182
175°	679	675	672	668	663	64
180°	674	674	674	674	674	

TEST NUMBER: P562362

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1118.8	1118.8	1118.8	1118.8	1118.8
2.5°	1125.1	1115.8	1118.8	1116.3	1110.9
5°	1121.7	1109.2	1112.8	1109.8	1107.9
7.5°	1110.3	1098.7	1101.4	1098.2	1097.1
10°	1100.0	1088.5	1091.2	1087.2	1085.2
12.5°	1088.2	1075.9	1078.5	1074.6	1073.4
15°	1067.5	1054.0	1055.7	1053.7	1051.7
17.5°	1043.5	1029.8	1030.0	1026.9	1026.5
20°	1026.1	1011.6	1010.3	1006.4	1008.4
22.5°	1007.2	992.0	990.6	985.2	987.9
25°	975.8	959.5	958.1	952.2	955.1
27.5°	939.6	923.4	923.4	915.2	918.3
30°	912.8	897.3	899.0	889.2	893.0
32.5°	884.4	870.5	871.4	861.6	865.4
35°	838.8	827.3	827.0	819.2	822.1
37.5°	792.3	782.1	780.5	776.0	776.7
40°	760.0	751.3	748.1	745.2	745.2
42.5°	726.1	718.2	715.0	712.8	712.1
45°	674.2	668.4	665.3	663.3	662.4
47.5°	623.0	617.6	614.9	613.5	612.5
50°	587.5	583.6	582.5	579.6	578.6
52.5°	552.0	549.7	548.6	544.9	543.9
55°	499.7	498.8	499.7	492.8	491.9
57.5°	445.3	446.9	450.1	440.7	438.4
60°	409.1	412.9	416.9	406.0	402.2
62.5°	372.0	378.2	383.8	371.3	365.9
65°	316.4	326.0	332.2	319.1	308.5
67.5°	262.8	274.7	282.1	268.0	256.1
70°	225.7	239.2	247.4	233.3	219.8
72.5°	193.4	208.4	215.1	201.8	188.3
75°	145.9	159.4	167.6	156.4	141.9
77.5°	103.5	116.2	123.0	113.3	101.3
80°	75.9	89.4	94.6	86.5	76.9
82.5°	53.8	65.0	68.6	63.7	57.2
85°	24.6	32.4	36.5	34.5	32.5
87.5°	6.3	11.7	15.0	15.0	15.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.2	54.3	126.0	36.7	27.7
95°	33.3	132.2	594.1	205.6	126.8
97.5°	61.2	154.8	914.9	654.7	448.6
100°	80.7	168.3	984.6	997.3	768.2
102.5°	102.2	182.8	969.2	1276.6	1076.5
105°	135.7	205.8	889.8	1571.8	1494.2
107.5°	169.8	232.6	797.1	1655.0	1724.1
110°	193.3	252.2	743.9	1623.2	1778.4



TEST NUMBER: P562362

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.9	271.7	708.0	1547.9	1769.2
115°	252.2	304.8	674.7	1429.4	1678.5
117.5°	284.2	333.6	655.0	1299.9	1563.8
120°	309.8	351.2	653.0	1225.9	1478.8
122.5°	330.3	371.6	647.9	1161.0	1395.8
125°	355.9	394.7	644.0	1068.7	1277.8
127.5°	383.8	420.2	642.0	1013.6	1185.9
130°	398.2	434.5	638.9	975.2	1125.4
132.5°	413.6	448.9	638.9	945.2	1083.4
135°	435.3	471.6	636.3	902.8	1020.4
137.5°	455.8	491.1	636.1	866.8	968.5
140°	471.2	507.5	635.1	837.0	934.7
142.5°	488.6	518.9	638.1	813.2	900.9
145°	513.4	539.7	641.5	781.3	851.4
147.5°	534.7	560.2	647.1	749.1	809.7
150°	553.1	570.6	649.1	738.5	781.0
152.5°	567.5	586.0	651.2	724.0	763.6
155°	586.4	600.2	656.8	706.1	734.9
157.5°	610.0	618.2	658.1	698.0	718.5
160°	622.3	628.5	663.2	691.8	709.3
162.5°	629.4	636.7	664.2	686.6	700.1
165°	647.9	650.4	664.5	678.8	688.8
167.5°	660.4	658.2	670.4	676.9	680.9
170°	664.5	663.3	668.3	669.7	674.7
172.5°	673.7	669.5	671.4	667.7	671.7
175°	678.6	674.8	672.2	668.2	663.2
177.5°	680.6	674.6	671.4	667.3	668.3
180°	673.5	673.5	673.5	673.5	673.5

(END OF REPORT)