

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P562392

Luminaire Tested: **SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562392  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (4500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9647.9 lumens  
Efficiency: N/A  
Efficacy: 109.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 88.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562392  
CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562392

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	90	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38
3	82	73	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	55	42	34	29	50	39	32	28	34	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18580	18580	18580
5°	18700	18552	18470
10°	18551	18401	18300
15°	18354	18150	18082
20°	18134	17856	17821
25°	17881	17556	17501
30°	17504	17238	17126
35°	17006	16766	16666
40°	16475	16220	16155
45°	15835	15626	15557
50°	15179	15051	14949
55°	14469	14469	14240
60°	13587	13849	13358
65°	12433	13053	12123
70°	10960	12012	10674
75°	9361	10751	9108
80°	7258	9048	7353
85°	4700	6944	6203



TEST NUMBER: P562392

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.6	2.0
10°-20°	535.4	5.5
20°-30°	794.1	8.2
30°-40°	929.2	9.6
40°-50°	925.1	9.6
50°-60°	798.8	8.3
60°-70°	575.0	6.0
70°-80°	301.5	3.1
80°-90°	74.8	0.8
90°-100°	331.9	3.4
100°-110°	944.4	9.8
110°-120°	904.8	9.4
120°-130°	716.1	7.4
130°-140°	574.8	6.0
140°-150°	450.0	4.7
150°-160°	329.3	3.4
160°-170°	203.9	2.1
170°-180°	69.2	0.7
0°-30°	1519.1	15.7
0°-40°	2448.3	25.4
0°-60°	4172.2	43.2
0°-90°	5123.5	53.1
90°-120°	2181.1	22.6
90°-150°	3921.9	40.7
90°-180°	4524.0	46.9
0°-180°	9647.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2014	2014	2014	2014	2014	
5°	2019	1996	2003	1998	1994	191
15°	1922	1897	1900	1897	1893	542
25°	1756	1727	1725	1714	1719	808
35°	1510	1489	1489	1474	1480	944
45°	1214	1203	1198	1194	1192	936
55°	900	898	900	887	885	803
65°	570	587	598	574	555	564
75°	263	287	302	282	256	281
85°	44	58	66	62	59	59
90°	0	0	0	0	0	3
95°	36	143	642	222	137	41
105°	147	223	962	1700	1616	155
115°	273	330	730	1546	1815	269
125°	385	427	696	1156	1382	345
135°	471	510	688	976	1104	363
145°	555	584	694	845	921	347
155°	634	649	710	764	795	293
165°	701	703	719	734	745	197
175°	734	730	727	723	717	70
180°	728	728	728	728	728	

TEST NUMBER: P562392

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2013.8	2013.8	2013.8	2013.8	2013.8
2.5°	2025.1	2008.5	2013.8	2009.3	1999.6
5°	2019.1	1996.5	2003.1	1997.7	1994.3
7.5°	1998.5	1977.7	1982.5	1976.8	1974.7
10°	1980.1	1959.2	1964.1	1956.9	1953.4
12.5°	1958.8	1936.6	1941.4	1934.2	1932.2
15°	1921.5	1897.2	1900.2	1896.6	1893.1
17.5°	1878.2	1853.6	1854.1	1848.4	1847.7
20°	1847.0	1821.0	1818.6	1811.6	1815.1
22.5°	1812.9	1785.5	1783.1	1773.3	1778.1
25°	1756.5	1727.0	1724.6	1714.0	1719.2
27.5°	1691.2	1662.1	1662.1	1647.3	1652.9
30°	1643.0	1615.2	1618.1	1600.5	1607.5
32.5°	1591.9	1566.9	1568.4	1550.8	1557.8
35°	1509.9	1489.1	1488.6	1474.5	1479.7
37.5°	1426.1	1407.7	1404.8	1396.7	1398.1
40°	1367.9	1352.3	1346.7	1341.3	1341.3
42.5°	1306.9	1292.7	1287.0	1283.1	1281.7
45°	1213.6	1203.2	1197.6	1194.0	1192.3
47.5°	1121.3	1111.6	1106.8	1104.3	1102.5
50°	1057.5	1050.5	1048.6	1043.2	1041.5
52.5°	993.6	989.4	987.5	980.8	979.0
55°	899.5	897.8	899.5	887.1	885.3
57.5°	801.6	804.4	810.1	793.3	789.2
60°	736.3	743.3	750.5	730.8	723.9
62.5°	669.6	680.7	690.9	668.3	658.6
65°	569.5	586.9	597.9	574.4	555.3
67.5°	473.0	494.5	507.8	482.5	460.9
70°	406.3	430.6	445.3	419.9	395.7
72.5°	348.1	375.2	387.1	363.2	338.9
75°	262.6	286.9	301.6	281.5	255.5
77.5°	186.3	209.2	221.4	203.9	182.4
80°	136.6	160.9	170.3	155.7	138.4
82.5°	96.9	117.0	123.5	114.7	102.9
85°	44.4	58.2	65.6	62.0	58.6
87.5°	11.4	21.1	27.0	27.0	28.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.1	58.7	136.3	39.7	29.9
95°	36.0	143.0	642.5	222.4	137.1
97.5°	66.2	167.5	989.5	708.1	485.2
100°	87.2	182.0	1064.8	1078.6	830.8
102.5°	110.5	197.7	1048.2	1380.6	1164.3
105°	146.8	222.6	962.4	1699.9	1616.0
107.5°	183.6	251.6	862.1	1789.9	1864.7
110°	209.1	272.7	804.5	1755.5	1923.4



TEST NUMBER: P562392

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	233.5	293.8	765.7	1674.0	1913.4
115°	272.8	329.7	729.7	1545.9	1815.4
117.5°	307.4	360.8	708.4	1405.9	1691.3
120°	335.1	379.8	706.2	1325.8	1599.3
122.5°	357.3	401.9	700.7	1255.6	1509.6
125°	385.0	426.9	696.5	1155.8	1381.9
127.5°	415.1	454.4	694.3	1096.2	1282.5
130°	430.6	469.9	691.0	1054.7	1217.2
132.5°	447.3	485.4	691.0	1022.3	1171.7
135°	470.8	510.1	688.2	976.3	1103.6
137.5°	493.0	531.1	687.9	937.5	1047.4
140°	509.6	548.8	686.8	905.2	1010.8
142.5°	528.4	561.2	690.1	879.5	974.3
145°	555.3	583.7	693.7	845.0	920.8
147.5°	578.3	605.9	699.8	810.2	875.7
150°	598.2	617.2	702.0	798.6	844.7
152.5°	613.7	633.7	704.3	783.1	825.8
155°	634.2	649.1	710.4	763.7	794.8
157.5°	659.7	668.6	711.7	754.9	777.1
160°	673.0	679.7	717.3	748.2	767.1
162.5°	680.7	688.6	718.4	742.5	757.2
165°	700.7	703.4	718.7	734.1	745.0
167.5°	714.2	711.8	725.0	732.1	736.4
170°	718.7	717.3	722.8	724.3	729.7
172.5°	728.6	724.0	726.1	722.1	726.4
175°	733.9	729.8	727.0	722.7	717.3
177.5°	736.1	729.6	726.1	721.7	722.8
180°	728.4	728.4	728.4	728.4	728.4

(END OF REPORT)