

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562311

Luminaire Tested: **SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562311
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2905.4 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562311

CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562311

CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10535	10535	10535
5°	10604	10520	10474
10°	10519	10435	10378
15°	10407	10293	10254
20°	10284	10126	10106
25°	10140	9955	9924
30°	9926	9776	9711
35°	9643	9507	9451
40°	9342	9197	9161
45°	8980	8861	8822
50°	8606	8535	8477
55°	8205	8205	8076
60°	7704	7853	7575
65°	7051	7403	6875
70°	6215	6811	6053
75°	5308	6096	5165
80°	4118	5133	4171
85°	2668	3938	3515



TEST NUMBER: P562311

CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	3.7
10°-20°	303.6	10.4
20°-30°	450.3	15.5
30°-40°	526.9	18.1
40°-50°	524.6	18.1
50°-60°	453.0	15.6
60°-70°	326.1	11.2
70°-80°	171.0	5.9
80°-90°	42.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	861.5	29.7
0°-40°	1388.4	47.8
0°-60°	2365.9	81.4
0°-90°	2905.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2905.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1142	1142	1142	1142	1142	
5°	1145	1132	1136	1133	1131	108
15°	1090	1076	1078	1076	1074	307
25°	996	979	978	972	975	458
35°	856	844	844	836	839	535
45°	688	682	679	677	676	531
55°	510	509	510	503	502	455
65°	323	333	339	326	315	320
75°	149	163	171	160	145	160
85°	25	33	37	35	33	34
90°	0	0	0	0	0	



TEST NUMBER: P562311

CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1141.9	1141.9	1141.9	1141.9	1141.9
2.5°	1148.4	1138.9	1141.9	1139.4	1133.9
5°	1145.0	1132.2	1135.9	1132.8	1130.9
7.5°	1133.3	1121.5	1124.2	1121.0	1119.8
10°	1122.8	1111.0	1113.8	1109.7	1107.7
12.5°	1110.8	1098.2	1100.9	1096.8	1095.7
15°	1089.6	1075.9	1077.6	1075.5	1073.5
17.5°	1065.1	1051.1	1051.4	1048.2	1047.8
20°	1047.4	1032.6	1031.3	1027.3	1029.3
22.5°	1028.1	1012.5	1011.2	1005.6	1008.3
25°	996.1	979.3	977.9	972.0	974.9
27.5°	959.0	942.5	942.5	934.2	937.3
30°	931.7	915.9	917.6	907.6	911.5
32.5°	902.7	888.5	889.4	879.4	883.4
35°	856.2	844.4	844.1	836.2	839.1
37.5°	808.7	798.3	796.6	792.0	792.8
40°	775.7	766.9	763.6	760.6	760.6
42.5°	741.1	733.0	729.8	727.6	726.8
45°	688.2	682.3	679.1	677.1	676.1
47.5°	635.9	630.4	627.6	626.2	625.2
50°	599.6	595.7	594.6	591.6	590.6
52.5°	563.4	561.1	560.0	556.2	555.2
55°	510.1	509.1	510.1	503.0	502.1
57.5°	454.6	456.1	459.4	449.9	447.5
60°	417.5	421.5	425.6	414.4	410.5
62.5°	379.7	386.0	391.8	379.0	373.5
65°	323.0	332.8	339.1	325.7	314.9
67.5°	268.2	280.4	288.0	273.6	261.4
70°	230.4	244.2	252.5	238.1	224.4
72.5°	197.4	212.7	219.5	205.9	192.2
75°	148.9	162.7	171.0	159.6	144.9
77.5°	105.6	118.6	125.6	115.6	103.4
80°	77.5	91.2	96.6	88.3	78.5
82.5°	54.9	66.3	70.0	65.0	58.4
85°	25.2	33.0	37.2	35.2	33.2
87.5°	6.4	11.9	15.3	15.3	16.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)