

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562314

Luminaire Tested: **SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562314
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3078.4 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562314
CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562314

CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11163	11163	11163
5°	11235	11147	11097
10°	11146	11056	10996
15°	11027	10905	10865
20°	10895	10728	10708
25°	10744	10549	10516
30°	10516	10357	10289
35°	10218	10074	10014
40°	9899	9745	9706
45°	9514	9389	9347
50°	9120	9043	8982
55°	8694	8694	8557
60°	8163	8320	8025
65°	7471	7844	7285
70°	6585	7219	6412
75°	5625	6459	5472
80°	4362	5435	4421
85°	2826	4171	3726



TEST NUMBER: P562314

CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.9	3.7
10°-20°	321.7	10.4
20°-30°	477.2	15.5
30°-40°	558.3	18.1
40°-50°	555.8	18.1
50°-60°	480.0	15.6
60°-70°	345.5	11.2
70°-80°	181.2	5.9
80°-90°	44.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	912.8	29.7
0°-40°	1471.1	47.8
0°-60°	2506.9	81.4
0°-90°	3078.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3078.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1210	1210	1210	1210	1210	
5°	1213	1200	1204	1200	1198	115
15°	1154	1140	1142	1140	1138	325
25°	1055	1038	1036	1030	1033	485
35°	907	895	894	886	889	567
45°	729	723	720	717	716	563
55°	540	539	540	533	532	482
65°	342	353	359	345	334	339
75°	158	172	181	169	154	169
85°	27	35	39	37	35	36
90°	0	0	0	0	0	



TEST NUMBER: P562314

CATALOG NUMBER: SQ4-PW1-0U-075D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1209.9	1209.9	1209.9	1209.9	1209.9
2.5°	1216.8	1206.8	1209.9	1207.3	1201.4
5°	1213.1	1199.6	1203.6	1200.3	1198.2
7.5°	1200.8	1188.3	1191.2	1187.7	1186.5
10°	1189.7	1177.2	1180.1	1175.8	1173.7
12.5°	1176.9	1163.6	1166.5	1162.2	1160.9
15°	1154.5	1139.9	1141.7	1139.5	1137.5
17.5°	1128.5	1113.7	1114.0	1110.6	1110.2
20°	1109.7	1094.1	1092.7	1088.5	1090.6
22.5°	1089.3	1072.8	1071.4	1065.5	1068.4
25°	1055.4	1037.7	1036.2	1029.9	1033.0
27.5°	1016.1	998.6	998.7	989.8	993.1
30°	987.1	970.5	972.2	961.7	965.8
32.5°	956.4	941.4	942.4	931.8	936.0
35°	907.2	894.7	894.4	885.9	889.1
37.5°	856.9	845.8	844.1	839.2	840.0
40°	821.9	812.5	809.1	805.9	805.9
42.5°	785.2	776.7	773.3	770.9	770.1
45°	729.2	722.9	719.6	717.4	716.4
47.5°	673.7	667.9	665.0	663.5	662.4
50°	635.4	631.2	630.0	626.8	625.8
52.5°	597.0	594.5	593.4	589.3	588.2
55°	540.5	539.4	540.5	533.0	532.0
57.5°	481.6	483.3	486.8	476.7	474.2
60°	442.4	446.6	450.9	439.1	434.9
62.5°	402.3	409.0	415.1	401.5	395.7
65°	342.2	352.6	359.3	345.1	333.7
67.5°	284.2	297.1	305.1	289.9	277.0
70°	244.1	258.7	267.6	252.3	237.7
72.5°	209.2	225.4	232.6	218.2	203.6
75°	157.8	172.4	181.2	169.1	153.5
77.5°	111.9	125.7	133.0	122.5	109.6
80°	82.1	96.7	102.3	93.6	83.2
82.5°	58.2	70.3	74.2	68.9	61.8
85°	26.7	35.0	39.4	37.3	35.2
87.5°	6.8	12.7	16.2	16.2	17.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)