

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562393

Luminaire Tested: **SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562393
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9754.6 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 88
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562393
CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562393

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53		
1	99	94	90	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45		
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38		
3	82	73	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32		
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28		
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24		
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21		
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19		
8	55	42	34	29	50	39	32	28	34	29	25	30	25	22	25	22	19	17		
9	51	39	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15		
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18785	18785	18785
5°	18906	18757	18674
10°	18756	18604	18504
15°	18557	18351	18283
20°	18335	18053	18018
25°	18079	17750	17696
30°	17697	17429	17315
35°	17194	16952	16851
40°	16658	16399	16334
45°	16010	15800	15729
50°	15347	15217	15114
55°	14630	14630	14398
60°	13738	14002	13505
65°	12570	13197	12258
70°	11082	12147	10790
75°	9464	10872	9208
80°	7337	9149	7433
85°	4742	7029	6267



TEST NUMBER: P562393

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.7	2.0
10°-20°	541.3	5.5
20°-30°	802.9	8.2
30°-40°	939.5	9.6
40°-50°	935.3	9.6
50°-60°	807.7	8.3
60°-70°	581.4	6.0
70°-80°	304.9	3.1
80°-90°	75.6	0.8
90°-100°	335.6	3.4
100°-110°	954.8	9.8
110°-120°	914.8	9.4
120°-130°	724.0	7.4
130°-140°	581.1	6.0
140°-150°	455.0	4.7
150°-160°	332.9	3.4
160°-170°	206.2	2.1
170°-180°	70.0	0.7
0°-30°	1535.9	15.7
0°-40°	2475.4	25.4
0°-60°	4218.4	43.2
0°-90°	5180.3	53.1
90°-120°	2205.2	22.6
90°-150°	3965.3	40.7
90°-180°	4574.0	46.9
0°-180°	9754.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2036	2036	2036	2036	2036	
5°	2041	2019	2025	2020	2016	193
15°	1943	1918	1921	1918	1914	548
25°	1776	1746	1744	1733	1738	817
35°	1527	1506	1505	1491	1496	954
45°	1227	1216	1211	1207	1206	947
55°	910	908	910	897	895	811
65°	576	593	604	581	562	571
75°	266	290	305	285	258	285
85°	45	59	66	63	59	59
90°	0	0	0	0	0	3
95°	36	144	650	225	139	42
105°	148	225	973	1719	1634	157
115°	276	333	738	1563	1835	272
125°	389	432	704	1169	1397	348
135°	476	516	696	987	1116	367
145°	561	590	701	854	931	351
155°	641	656	718	772	804	296
165°	708	711	727	742	753	199
175°	742	738	735	731	725	70
180°	736	736	736	736	736	

TEST NUMBER: P562393

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2036.0	2036.0	2036.0	2036.0	2036.0
2.5°	2047.5	2030.7	2036.0	2031.5	2021.7
5°	2041.4	2018.6	2025.3	2019.8	2016.3
7.5°	2020.6	1999.6	2004.5	1998.7	1996.6
10°	2002.0	1980.9	1985.8	1978.6	1975.1
12.5°	1980.4	1958.0	1962.9	1955.6	1953.5
15°	1942.8	1918.2	1921.2	1917.6	1914.1
17.5°	1899.0	1874.1	1874.6	1868.8	1868.1
20°	1867.4	1841.1	1838.7	1831.6	1835.1
22.5°	1833.0	1805.3	1802.8	1792.9	1797.8
25°	1775.9	1746.1	1743.6	1733.0	1738.3
27.5°	1709.9	1680.5	1680.5	1665.6	1671.2
30°	1661.1	1633.1	1636.0	1618.2	1625.3
32.5°	1609.5	1584.2	1585.8	1568.0	1575.0
35°	1526.6	1505.5	1505.1	1490.8	1496.1
37.5°	1441.9	1423.3	1420.4	1412.2	1413.6
40°	1383.1	1367.3	1361.6	1356.2	1356.2
42.5°	1321.4	1307.0	1301.3	1297.3	1295.9
45°	1227.0	1216.5	1210.9	1207.2	1205.5
47.5°	1133.7	1123.9	1119.0	1116.5	1114.7
50°	1069.2	1062.1	1060.2	1054.8	1053.0
52.5°	1004.6	1000.4	998.5	991.6	989.9
55°	909.5	907.7	909.5	896.9	895.1
57.5°	810.5	813.3	819.1	802.1	797.9
60°	744.5	751.5	758.8	738.9	731.9
62.5°	677.0	688.2	698.5	675.7	665.9
65°	575.8	593.4	604.5	580.8	561.5
67.5°	478.2	500.0	513.4	487.8	466.0
70°	410.8	435.4	450.3	424.6	400.0
72.5°	352.0	379.3	391.4	367.2	342.6
75°	265.5	290.0	305.0	284.6	258.3
77.5°	188.4	211.5	223.9	206.2	184.4
80°	138.1	162.7	172.2	157.5	139.9
82.5°	97.9	118.3	124.9	116.0	104.0
85°	44.8	58.9	66.4	62.7	59.2
87.5°	11.5	21.3	27.3	27.3	28.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.2	59.4	137.8	40.1	30.2
95°	36.4	144.5	649.6	224.8	138.6
97.5°	66.9	169.3	1000.5	715.9	490.6
100°	88.2	184.0	1076.6	1090.5	840.0
102.5°	111.7	199.9	1059.8	1395.9	1177.1
105°	148.4	225.1	973.0	1718.7	1633.8
107.5°	185.6	254.4	871.7	1809.7	1885.3
110°	211.4	275.7	813.4	1774.9	1944.6

TEST NUMBER: P562393

CATALOG NUMBER: SQ4-PW1-100U-125D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	236.0	297.1	774.2	1692.5	1934.6
115°	275.8	333.3	737.8	1563.0	1835.4
117.5°	310.8	364.7	716.3	1421.4	1710.0
120°	338.8	384.0	714.0	1340.5	1617.0
122.5°	361.2	406.4	708.4	1269.5	1526.3
125°	389.2	431.6	704.2	1168.6	1397.2
127.5°	419.7	459.4	702.0	1108.3	1296.7
130°	435.4	475.1	698.6	1066.4	1230.6
132.5°	452.2	490.8	698.6	1033.6	1184.7
135°	476.0	515.7	695.8	987.1	1115.8
137.5°	498.4	537.0	695.5	947.8	1059.0
140°	515.2	554.9	694.4	915.2	1022.0
142.5°	534.3	567.4	697.8	889.2	985.1
145°	561.4	590.2	701.4	854.4	931.0
147.5°	584.7	612.6	707.6	819.1	885.4
150°	604.8	624.0	709.8	807.5	854.0
152.5°	620.5	640.8	712.1	791.7	835.0
155°	641.2	656.3	718.2	772.1	803.6
157.5°	667.0	676.0	719.6	763.2	785.7
160°	680.4	687.3	725.2	756.5	775.6
162.5°	688.3	696.2	726.3	750.8	765.5
165°	708.4	711.2	726.6	742.3	753.2
167.5°	722.1	719.7	733.1	740.2	744.5
170°	726.6	725.2	730.8	732.3	737.8
172.5°	736.7	732.0	734.2	730.1	734.5
175°	742.0	737.9	735.0	730.7	725.2
177.5°	744.3	737.7	734.2	729.7	730.8
180°	736.4	736.4	736.4	736.4	736.4

(END OF REPORT)