

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562403

Luminaire Tested: **SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562403
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7478.4 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 62.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562403
CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562403

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	45	44	43	31	30	29	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7204	7204	7204
5°	7251	7193	7161
10°	7192	7134	7096
15°	7116	7038	7011
20°	7031	6923	6910
25°	6933	6807	6786
30°	6786	6684	6640
35°	6593	6501	6462
40°	6388	6288	6264
45°	6139	6059	6032
50°	5885	5836	5796
55°	5611	5611	5522
60°	5268	5370	5180
65°	4820	5060	4700
70°	4249	4659	4138
75°	3629	4167	3533
80°	2816	3507	2853
85°	1821	2699	2403



TEST NUMBER: P562403

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.5	1.0
10°-20°	207.6	2.8
20°-30°	307.9	4.1
30°-40°	360.3	4.8
40°-50°	358.7	4.8
50°-60°	309.7	4.1
60°-70°	223.0	3.0
70°-80°	116.9	1.6
80°-90°	29.0	0.4
90°-100°	402.9	5.4
100°-110°	1146.3	15.3
110°-120°	1098.3	14.7
120°-130°	869.3	11.6
130°-140°	697.7	9.3
140°-150°	546.2	7.3
150°-160°	399.7	5.3
160°-170°	247.6	3.3
170°-180°	84.0	1.1
0°-30°	589.0	7.9
0°-40°	949.3	12.7
0°-60°	1617.7	21.6
0°-90°	1986.6	26.6
90°-120°	2647.5	35.4
90°-150°	4760.6	63.7
90°-180°	5492.0	73.4
0°-180°	7478.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	781	781	781	781	781	
5°	783	774	777	775	773	74
15°	745	736	737	735	734	210
25°	681	670	669	665	667	313
35°	585	577	577	572	574	366
45°	470	466	464	463	462	363
55°	349	348	349	344	343	311
65°	221	228	232	223	215	219
75°	102	111	117	109	99	109
85°	17	23	26	24	23	23
90°	0	0	0	0	0	2
95°	44	174	780	270	166	50
105°	178	270	1168	2063	1962	188
115°	331	400	886	1876	2204	326
125°	467	518	846	1403	1678	418
135°	572	619	835	1185	1340	441
145°	674	708	842	1026	1118	421
155°	770	788	862	927	965	356
165°	850	854	872	891	904	239
175°	891	886	882	877	871	84
180°	884	884	884	884	884	

TEST NUMBER: P562403

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	780.8	780.8	780.8	780.8	780.8
2.5°	785.2	778.7	780.8	779.1	775.3
5°	782.9	774.1	776.7	774.6	773.2
7.5°	774.9	766.8	768.7	766.5	765.7
10°	767.7	759.7	761.5	758.8	757.4
12.5°	759.5	750.9	752.7	750.0	749.2
15°	745.0	735.6	736.8	735.4	734.0
17.5°	728.2	718.7	718.9	716.7	716.4
20°	716.1	706.0	705.1	702.4	703.8
22.5°	702.9	692.3	691.4	687.6	689.4
25°	681.0	669.6	668.7	664.6	666.6
27.5°	655.7	644.4	644.5	638.7	640.9
30°	637.0	626.3	627.4	620.6	623.3
32.5°	617.2	607.5	608.1	601.3	604.0
35°	585.4	577.4	577.2	571.7	573.7
37.5°	553.0	545.8	544.7	541.5	542.1
40°	530.4	524.3	522.1	520.1	520.1
42.5°	506.7	501.2	499.0	497.5	497.0
45°	470.5	466.5	464.4	463.0	462.3
47.5°	434.8	431.0	429.1	428.2	427.5
50°	410.0	407.3	406.6	404.5	403.8
52.5°	385.2	383.6	382.9	380.3	379.6
55°	348.8	348.1	348.8	343.9	343.3
57.5°	310.8	311.9	314.1	307.6	306.0
60°	285.5	288.2	291.0	283.4	280.7
62.5°	259.6	263.9	267.9	259.1	255.4
65°	220.8	227.6	231.8	222.7	215.3
67.5°	183.4	191.7	196.9	187.1	178.7
70°	157.5	167.0	172.7	162.8	153.4
72.5°	135.0	145.5	150.1	140.8	131.4
75°	101.8	111.2	116.9	109.2	99.1
77.5°	72.2	81.1	85.9	79.1	70.7
80°	53.0	62.4	66.0	60.4	53.7
82.5°	37.6	45.4	47.9	44.5	39.9
85°	17.2	22.6	25.5	24.0	22.7
87.5°	4.4	8.2	10.5	10.5	11.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.4	71.3	165.4	48.1	36.3
95°	43.7	173.5	779.9	269.9	166.4
97.5°	80.3	203.3	1201.1	859.5	589.0
100°	105.9	220.9	1292.6	1309.2	1008.5
102.5°	134.1	240.0	1272.4	1675.9	1413.2
105°	178.2	270.2	1168.2	2063.4	1961.5
107.5°	222.9	305.4	1046.5	2172.7	2263.4
110°	253.8	331.0	976.6	2130.9	2334.7

TEST NUMBER: P562403

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.4	356.7	929.5	2032.0	2322.6
115°	331.1	400.1	885.8	1876.5	2203.6
117.5°	373.1	437.9	859.9	1706.5	2053.0
120°	406.8	461.0	857.2	1609.4	1941.3
122.5°	433.7	487.9	850.5	1524.1	1832.4
125°	467.3	518.2	845.5	1403.0	1677.5
127.5°	503.9	551.6	842.8	1330.6	1556.8
130°	522.7	570.4	838.7	1280.2	1477.4
132.5°	542.9	589.3	838.7	1240.9	1422.3
135°	571.5	619.1	835.4	1185.1	1339.6
137.5°	598.4	644.7	835.0	1137.9	1271.4
140°	618.5	666.2	833.7	1098.8	1227.0
142.5°	641.4	681.2	837.7	1067.6	1182.6
145°	674.0	708.5	842.1	1025.7	1117.7
147.5°	701.9	735.4	849.5	983.4	1063.0
150°	726.1	749.1	852.2	969.4	1025.3
152.5°	744.9	769.3	854.9	950.5	1002.4
155°	769.8	787.9	862.3	927.0	964.8
157.5°	800.7	811.6	863.9	916.3	943.3
160°	816.9	825.1	870.7	908.2	931.2
162.5°	826.3	835.8	872.0	901.3	919.1
165°	850.5	853.8	872.3	891.1	904.3
167.5°	867.0	864.0	880.1	888.6	893.9
170°	872.3	870.7	877.4	879.2	885.8
172.5°	884.4	878.9	881.4	876.5	881.8
175°	890.8	885.9	882.4	877.2	870.7
177.5°	893.5	885.6	881.4	876.1	877.4
180°	884.1	884.1	884.1	884.1	884.1

(END OF REPORT)