

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562405

Luminaire Tested: **SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562405  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (4500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7738.0 lumens  
Efficiency: N/A  
Efficacy: 124.6 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 62.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562405  
CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562405

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	45	44	43	31	30	29	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7454	7454	7454
5°	7502	7442	7410
10°	7442	7382	7342
15°	7363	7282	7254
20°	7275	7163	7150
25°	7174	7044	7021
30°	7022	6916	6870
35°	6823	6726	6687
40°	6610	6507	6481
45°	6353	6269	6241
50°	6089	6038	5997
55°	5805	5805	5714
60°	5451	5556	5359
65°	4988	5237	4864
70°	4397	4821	4281
75°	3754	4313	3654
80°	2912	3629	2949
85°	1884	2784	2488



TEST NUMBER: P562405

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.1	1.0
10°-20°	214.8	2.8
20°-30°	318.6	4.1
30°-40°	372.8	4.8
40°-50°	371.1	4.8
50°-60°	320.5	4.1
60°-70°	230.7	3.0
70°-80°	121.0	1.6
80°-90°	30.0	0.4
90°-100°	416.8	5.4
100°-110°	1186.1	15.3
110°-120°	1136.4	14.7
120°-130°	899.4	11.6
130°-140°	721.9	9.3
140°-150°	565.2	7.3
150°-160°	413.5	5.3
160°-170°	256.2	3.3
170°-180°	86.9	1.1
0°-30°	609.5	7.9
0°-40°	982.3	12.7
0°-60°	1673.9	21.6
0°-90°	2055.5	26.6
90°-120°	2739.4	35.4
90°-150°	4925.9	63.7
90°-180°	5682.0	73.4
0°-180°	7738.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	808	808	808	808	808	
5°	810	801	804	802	800	77
15°	771	761	762	761	760	217
25°	705	693	692	688	690	324
35°	606	597	597	592	594	379
45°	487	483	480	479	478	376
55°	361	360	361	356	355	322
65°	228	236	240	230	223	226
75°	105	115	121	113	102	113
85°	18	23	26	25	24	23
90°	0	0	0	0	0	3
95°	45	180	807	279	172	52
105°	184	280	1209	2135	2030	195
115°	343	414	916	1942	2280	337
125°	484	536	875	1452	1736	433
135°	591	641	864	1226	1386	456
145°	697	733	871	1061	1157	436
155°	796	815	892	959	998	368
165°	880	883	903	922	936	247
175°	922	917	913	908	901	87
180°	915	915	915	915	915	

TEST NUMBER: P562405

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	807.9	807.9	807.9	807.9	807.9
2.5°	812.5	805.8	807.9	806.1	802.2
5°	810.0	801.0	803.6	801.5	800.1
7.5°	801.8	793.4	795.4	793.1	792.2
10°	794.4	786.0	788.0	785.1	783.7
12.5°	785.8	776.9	778.9	776.0	775.2
15°	770.9	761.2	762.4	760.9	759.5
17.5°	753.5	743.6	743.8	741.6	741.3
20°	741.0	730.6	729.6	726.8	728.2
22.5°	727.3	716.3	715.4	711.4	713.4
25°	704.7	692.9	691.9	687.7	689.7
27.5°	678.5	666.8	666.8	660.9	663.1
30°	659.1	648.0	649.2	642.1	644.9
32.5°	638.6	628.6	629.2	622.2	625.0
35°	605.8	597.4	597.2	591.6	593.7
37.5°	572.2	564.8	563.6	560.4	560.9
40°	548.8	542.5	540.3	538.1	538.1
42.5°	524.3	518.6	516.3	514.8	514.2
45°	486.9	482.7	480.5	479.0	478.3
47.5°	449.9	446.0	444.0	443.0	442.3
50°	424.2	421.5	420.7	418.5	417.8
52.5°	398.6	396.9	396.2	393.5	392.8
55°	360.9	360.2	360.9	355.9	355.2
57.5°	321.6	322.7	325.0	318.3	316.6
60°	295.4	298.2	301.1	293.2	290.4
62.5°	268.6	273.1	277.2	268.1	264.2
65°	228.5	235.5	239.9	230.5	222.8
67.5°	189.8	198.4	203.7	193.6	184.9
70°	163.0	172.7	178.7	168.5	158.7
72.5°	139.7	150.5	155.3	145.7	136.0
75°	105.3	115.1	121.0	112.9	102.5
77.5°	74.7	83.9	88.8	81.8	73.2
80°	54.8	64.6	68.3	62.5	55.5
82.5°	38.9	46.9	49.5	46.0	41.3
85°	17.8	23.4	26.3	24.9	23.5
87.5°	4.6	8.5	10.8	10.8	11.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.9	73.8	171.1	49.8	37.6
95°	45.2	179.6	807.0	279.3	172.2
97.5°	83.1	210.3	1242.8	889.3	609.4
100°	109.6	228.6	1337.4	1354.7	1043.5
102.5°	138.8	248.3	1316.6	1734.0	1462.3
105°	184.4	279.6	1208.7	2135.1	2029.6
107.5°	230.6	316.0	1082.8	2248.1	2342.0
110°	262.6	342.5	1010.5	2204.9	2415.7

TEST NUMBER: P562405

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	369.1	961.8	2102.5	2403.2
115°	342.6	414.0	916.5	1941.7	2280.1
117.5°	386.1	453.1	889.8	1765.8	2124.2
120°	420.9	477.0	887.0	1665.2	2008.8
122.5°	448.7	504.8	880.0	1577.0	1896.1
125°	483.5	536.2	874.8	1451.7	1735.7
127.5°	521.4	570.7	872.0	1376.8	1610.8
130°	540.9	590.2	867.9	1324.7	1528.7
132.5°	561.8	609.7	867.9	1284.0	1471.7
135°	591.3	640.6	864.4	1226.3	1386.1
137.5°	619.1	667.1	864.0	1177.4	1315.5
140°	640.0	689.3	862.6	1137.0	1269.6
142.5°	663.7	704.8	866.8	1104.6	1223.7
145°	697.4	733.1	871.3	1061.3	1156.6
147.5°	726.3	761.0	879.0	1017.6	1099.9
150°	751.3	775.1	881.8	1003.1	1060.9
152.5°	770.8	796.0	884.5	983.5	1037.2
155°	796.5	815.2	892.2	959.2	998.3
157.5°	828.5	839.8	893.9	948.1	976.0
160°	845.2	853.7	900.9	939.7	963.5
162.5°	855.0	864.8	902.3	932.6	951.0
165°	880.0	883.4	902.6	922.1	935.7
167.5°	897.1	894.0	910.6	919.5	924.9
170°	902.6	900.9	907.9	909.7	916.5
172.5°	915.2	909.4	912.0	906.9	912.4
175°	921.8	916.7	913.1	907.7	900.9
177.5°	924.5	916.4	912.0	906.5	907.9
180°	914.8	914.8	914.8	914.8	914.8

(END OF REPORT)