

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562329

Luminaire Tested: **SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562329
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4149.9 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562329

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562329

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92		94	92	89		91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77		83	79	75		80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38		49	42	37		48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31		42	35	30		41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28		39	32	28		38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15049	15049	15049
5°	15146	15026	14960
10°	15025	14903	14823
15°	14865	14701	14646
20°	14688	14462	14434
25°	14483	14219	14176
30°	14177	13962	13871
35°	13774	13580	13499
40°	13345	13136	13085
45°	12826	12656	12600
50°	12294	12190	12109
55°	11720	11720	11535
60°	11005	11217	10819
65°	10071	10573	9820
70°	8878	9730	8646
75°	7582	8709	7375
80°	5882	7332	5956
85°	3800	5632	5018



TEST NUMBER: P562329

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.6	3.7
10°-20°	433.6	10.4
20°-30°	643.2	15.5
30°-40°	752.6	18.1
40°-50°	749.3	18.1
50°-60°	647.0	15.6
60°-70°	465.7	11.2
70°-80°	244.2	5.9
80°-90°	60.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1230.4	29.6
0°-40°	1983.1	47.8
0°-60°	3379.3	81.4
0°-90°	4149.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4149.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1635	1617	1622	1618	1615	155
15°	1556	1537	1539	1536	1533	439
25°	1423	1399	1397	1388	1392	654
35°	1223	1206	1206	1194	1198	764
45°	983	974	970	967	966	758
55°	729	727	729	718	717	650
65°	461	475	484	465	450	457
75°	213	232	244	228	207	228
85°	36	47	53	50	47	49
90°	0	0	0	0	0	



TEST NUMBER: P562329

CATALOG NUMBER: SQ4-PW1-0U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.1	1631.1	1631.1	1631.1	1631.1
2.5°	1640.3	1626.8	1631.1	1627.4	1619.6
5°	1635.4	1617.1	1622.4	1618.1	1615.3
7.5°	1618.7	1601.8	1605.8	1601.1	1599.5
10°	1603.8	1586.9	1590.8	1585.0	1582.2
12.5°	1586.5	1568.5	1572.4	1566.7	1565.0
15°	1556.3	1536.7	1539.1	1536.2	1533.3
17.5°	1521.3	1501.3	1501.7	1497.1	1496.6
20°	1496.0	1474.9	1473.0	1467.3	1470.1
22.5°	1468.4	1446.2	1444.3	1436.3	1440.2
25°	1422.7	1398.8	1396.8	1388.3	1392.5
27.5°	1369.8	1346.2	1346.2	1334.3	1338.8
30°	1330.7	1308.2	1310.6	1296.4	1302.0
32.5°	1289.3	1269.1	1270.4	1256.1	1261.7
35°	1222.9	1206.1	1205.7	1194.3	1198.5
37.5°	1155.1	1140.2	1137.9	1131.3	1132.4
40°	1108.0	1095.3	1090.7	1086.4	1086.4
42.5°	1058.5	1047.0	1042.4	1039.3	1038.1
45°	983.0	974.5	970.0	967.1	965.7
47.5°	908.2	900.4	896.4	894.4	893.0
50°	856.5	850.9	849.3	845.0	843.6
52.5°	804.8	801.4	799.9	794.4	793.0
55°	728.6	727.2	728.6	718.5	717.1
57.5°	649.3	651.5	656.2	642.6	639.2
60°	596.4	602.0	607.9	591.9	586.3
62.5°	542.3	551.3	559.6	541.3	533.4
65°	461.3	475.3	484.3	465.3	449.8
67.5°	383.1	400.5	411.3	390.8	373.3
70°	329.1	348.8	360.7	340.1	320.5
72.5°	282.0	303.9	313.6	294.2	274.5
75°	212.7	232.4	244.3	228.0	206.9
77.5°	150.9	169.4	179.3	165.2	147.7
80°	110.7	130.3	138.0	126.1	112.1
82.5°	78.5	94.8	100.0	92.9	83.3
85°	35.9	47.2	53.2	50.2	47.4
87.5°	9.2	17.1	21.8	21.9	23.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)