

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562406

Luminaire Tested: **SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562406
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7823.7 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562406
CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562406

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	45	44	43	31	30	29	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7536	7536	7536
5°	7585	7525	7492
10°	7525	7464	7424
15°	7445	7362	7335
20°	7356	7243	7228
25°	7253	7121	7100
30°	7099	6993	6946
35°	6899	6801	6760
40°	6683	6578	6553
45°	6423	6339	6310
50°	6156	6105	6064
55°	5870	5870	5776
60°	5512	5617	5418
65°	5043	5294	4919
70°	4446	4872	4330
75°	3796	4360	3693
80°	2943	3671	2981
85°	1905	2816	2509



TEST NUMBER: P562406

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	1.0
10°-20°	217.2	2.8
20°-30°	322.1	4.1
30°-40°	376.9	4.8
40°-50°	375.2	4.8
50°-60°	324.0	4.1
60°-70°	233.2	3.0
70°-80°	122.3	1.6
80°-90°	30.3	0.4
90°-100°	421.5	5.4
100°-110°	1199.2	15.3
110°-120°	1149.0	14.7
120°-130°	909.4	11.6
130°-140°	729.9	9.3
140°-150°	571.4	7.3
150°-160°	418.1	5.3
160°-170°	259.0	3.3
170°-180°	87.9	1.1
0°-30°	616.2	7.9
0°-40°	993.1	12.7
0°-60°	1692.4	21.6
0°-90°	2078.3	26.6
90°-120°	2769.7	35.4
90°-150°	4980.4	63.7
90°-180°	5745.0	73.4
0°-180°	7823.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	819	810	812	810	809	78
15°	779	770	771	769	768	220
25°	712	700	700	695	697	328
35°	612	604	604	598	600	383
45°	492	488	486	484	484	380
55°	365	364	365	360	359	326
65°	231	238	242	233	225	229
75°	106	116	122	114	104	114
85°	18	24	27	25	24	24
90°	0	0	0	0	0	3
95°	46	182	816	282	174	52
105°	186	283	1222	2159	2052	197
115°	346	419	927	1963	2305	341
125°	489	542	884	1468	1755	438
135°	598	648	874	1240	1402	461
145°	705	741	881	1073	1169	440
155°	805	824	902	970	1009	372
165°	890	893	913	932	946	250
175°	932	927	923	918	911	88
180°	925	925	925	925	925	

TEST NUMBER: P562406

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	816.8	816.8	816.8	816.8	816.8
2.5°	821.5	814.7	816.8	815.0	811.1
5°	819.0	809.9	812.5	810.3	808.9
7.5°	810.7	802.2	804.2	801.9	801.0
10°	803.2	794.7	796.7	793.8	792.4
12.5°	794.5	785.5	787.5	784.6	783.7
15°	779.4	769.6	770.8	769.3	767.9
17.5°	761.9	751.9	752.1	749.8	749.5
20°	749.2	738.6	737.7	734.8	736.2
22.5°	735.4	724.3	723.3	719.3	721.3
25°	712.5	700.5	699.5	695.3	697.4
27.5°	686.0	674.2	674.2	668.2	670.5
30°	666.4	655.2	656.4	649.2	652.0
32.5°	645.7	635.6	636.2	629.1	631.9
35°	612.5	604.0	603.8	598.1	600.2
37.5°	578.5	571.0	569.9	566.6	567.1
40°	554.9	548.5	546.2	544.1	544.1
42.5°	530.1	524.4	522.1	520.5	519.9
45°	492.3	488.0	485.8	484.3	483.6
47.5°	454.8	450.9	448.9	447.9	447.2
50°	428.9	426.1	425.3	423.2	422.5
52.5°	403.0	401.3	400.6	397.8	397.1
55°	364.9	364.2	364.9	359.8	359.1
57.5°	325.2	326.3	328.6	321.8	320.1
60°	298.7	301.5	304.4	296.4	293.6
62.5°	271.6	276.1	280.2	271.1	267.1
65°	231.0	238.1	242.5	233.0	225.3
67.5°	191.9	200.6	206.0	195.7	187.0
70°	164.8	174.7	180.6	170.3	160.5
72.5°	141.2	152.2	157.0	147.3	137.5
75°	106.5	116.4	122.3	114.2	103.6
77.5°	75.6	84.9	89.8	82.7	74.0
80°	55.4	65.3	69.1	63.2	56.1
82.5°	39.3	47.5	50.1	46.5	41.7
85°	18.0	23.6	26.6	25.2	23.7
87.5°	4.6	8.5	10.9	11.0	11.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.1	74.6	173.0	50.4	38.0
95°	45.7	181.5	815.9	282.4	174.1
97.5°	84.1	212.7	1256.6	899.2	616.2
100°	110.8	231.1	1352.2	1369.7	1055.1
102.5°	140.3	251.0	1331.1	1753.2	1478.5
105°	186.4	282.7	1222.1	2158.7	2052.1
107.5°	233.2	319.5	1094.8	2273.0	2367.9
110°	265.5	346.3	1021.6	2229.2	2442.4



TEST NUMBER: P562406

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	296.5	373.2	972.4	2125.8	2429.8
115°	346.4	418.6	926.7	1963.1	2305.3
117.5°	390.4	458.1	899.6	1785.3	2147.7
120°	425.5	482.3	896.8	1683.7	2031.0
122.5°	453.7	510.4	889.8	1594.5	1917.0
125°	488.8	542.1	884.5	1467.8	1754.9
127.5°	527.2	577.0	881.7	1392.1	1628.7
130°	546.9	596.7	877.5	1339.3	1545.7
132.5°	568.0	616.5	877.5	1298.2	1488.0
135°	597.9	647.7	873.9	1239.8	1401.5
137.5°	626.0	674.5	873.6	1190.5	1330.1
140°	647.1	697.0	872.2	1149.5	1283.6
142.5°	671.0	712.6	876.4	1116.9	1237.2
145°	705.1	741.2	881.0	1073.1	1169.4
147.5°	734.3	769.4	888.7	1028.8	1112.0
150°	759.6	783.7	891.5	1014.2	1072.6
152.5°	779.3	804.8	894.3	994.4	1048.7
155°	805.4	824.3	902.1	969.8	1009.3
157.5°	837.7	849.1	903.8	958.6	986.8
160°	854.6	863.2	910.9	950.1	974.2
162.5°	864.4	874.4	912.3	942.9	961.5
165°	889.8	893.2	912.6	932.3	946.0
167.5°	907.0	903.9	920.7	929.6	935.1
170°	912.6	910.9	917.9	919.8	926.7
172.5°	925.3	919.4	922.1	917.0	922.5
175°	932.0	926.8	923.2	917.7	910.9
177.5°	934.8	926.5	922.1	916.5	917.9
180°	924.9	924.9	924.9	924.9	924.9

(END OF REPORT)