

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562407

Luminaire Tested: **SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562407  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7935.1 lumens  
Efficiency: N/A  
Efficacy: 128.0 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 62  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562407  
CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562407

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	45	44	43	31	30	29	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7644	7644	7644
5°	7693	7632	7599
10°	7632	7570	7529
15°	7551	7467	7439
20°	7461	7346	7331
25°	7356	7223	7200
30°	7201	7092	7045
35°	6997	6898	6857
40°	6778	6672	6646
45°	6515	6429	6400
50°	6244	6192	6150
55°	5953	5953	5858
60°	5589	5698	5495
65°	5115	5370	4988
70°	4510	4942	4392
75°	3850	4424	3747
80°	2986	3725	3023
85°	1927	2858	2551



TEST NUMBER: P562407

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	1.0
10°-20°	220.3	2.8
20°-30°	326.7	4.1
30°-40°	382.3	4.8
40°-50°	380.6	4.8
50°-60°	328.7	4.1
60°-70°	236.6	3.0
70°-80°	124.1	1.6
80°-90°	30.8	0.4
90°-100°	427.5	5.4
100°-110°	1216.3	15.3
110°-120°	1165.4	14.7
120°-130°	922.3	11.6
130°-140°	740.3	9.3
140°-150°	579.6	7.3
150°-160°	424.1	5.3
160°-170°	262.7	3.3
170°-180°	89.1	1.1
0°-30°	625.0	7.9
0°-40°	1007.3	12.7
0°-60°	1716.5	21.6
0°-90°	2107.9	26.6
90°-120°	2809.1	35.4
90°-150°	5051.4	63.7
90°-180°	5827.0	73.4
0°-180°	7935.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	828	828	828	828	828	
5°	831	821	824	822	820	79
15°	790	780	782	780	779	223
25°	723	710	710	705	707	332
35°	621	613	612	607	609	388
45°	499	495	493	491	490	385
55°	370	369	370	365	364	330
65°	234	241	246	236	228	232
75°	108	118	124	116	105	116
85°	18	24	27	26	24	24
90°	0	0	0	0	0	3
95°	46	184	828	286	177	53
105°	189	287	1240	2189	2081	200
115°	351	425	940	1991	2338	346
125°	496	550	897	1489	1780	444
135°	606	657	886	1258	1421	468
145°	715	752	894	1088	1186	447
155°	817	836	915	984	1024	378
165°	902	906	926	946	960	254
175°	945	940	936	931	924	90
180°	938	938	938	938	938	



TEST NUMBER: P562407

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	828.5	828.5	828.5	828.5	828.5
2.5°	833.2	826.3	828.5	826.6	822.6
5°	830.7	821.4	824.1	821.9	820.5
7.5°	822.2	813.6	815.6	813.3	812.4
10°	814.6	806.0	808.0	805.1	803.7
12.5°	805.9	796.7	798.7	795.8	794.9
15°	790.5	780.5	781.8	780.3	778.8
17.5°	772.7	762.6	762.8	760.4	760.2
20°	759.9	749.2	748.2	745.3	746.7
22.5°	745.9	734.6	733.6	729.5	731.5
25°	722.6	710.5	709.5	705.2	707.3
27.5°	695.8	683.8	683.8	677.7	680.0
30°	675.9	664.5	665.7	658.5	661.3
32.5°	654.9	644.6	645.3	638.0	640.9
35°	621.2	612.6	612.4	606.6	608.8
37.5°	586.7	579.2	578.0	574.6	575.2
40°	562.8	556.4	554.0	551.8	551.8
42.5°	537.7	531.8	529.5	527.9	527.3
45°	499.3	495.0	492.7	491.2	490.5
47.5°	461.3	457.3	455.3	454.3	453.6
50°	435.0	432.2	431.4	429.2	428.5
52.5°	408.8	407.1	406.3	403.5	402.8
55°	370.1	369.4	370.1	365.0	364.2
57.5°	329.8	330.9	333.3	326.4	324.7
60°	302.9	305.8	308.8	300.7	297.8
62.5°	275.5	280.0	284.2	275.0	271.0
65°	234.3	241.4	246.0	236.3	228.5
67.5°	194.6	203.5	208.9	198.5	189.6
70°	167.2	177.1	183.2	172.8	162.8
72.5°	143.2	154.3	159.3	149.4	139.4
75°	108.0	118.0	124.1	115.8	105.1
77.5°	76.6	86.1	91.1	83.9	75.0
80°	56.2	66.2	70.1	64.1	56.9
82.5°	39.9	48.1	50.8	47.2	42.3
85°	18.2	24.0	27.0	25.5	24.1
87.5°	4.7	8.7	11.1	11.1	11.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.3	75.7	175.5	51.1	38.5
95°	46.4	184.1	827.5	286.4	176.6
97.5°	85.2	215.7	1274.5	912.0	624.9
100°	112.4	234.4	1371.5	1389.2	1070.1
102.5°	142.3	254.6	1350.1	1778.2	1499.5
105°	189.0	286.7	1239.5	2189.4	2081.3
107.5°	236.5	324.0	1110.4	2305.4	2401.6
110°	269.3	351.3	1036.2	2261.0	2477.2

TEST NUMBER: P562407

CATALOG NUMBER: SQ4-PW1-125U-050D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	378.5	986.3	2156.1	2464.4
115°	351.3	424.6	939.9	1991.1	2338.1
117.5°	395.9	464.6	912.4	1810.7	2178.3
120°	431.6	489.1	909.6	1707.7	2059.9
122.5°	460.1	517.7	902.4	1617.2	1944.3
125°	495.8	549.9	897.1	1488.7	1779.9
127.5°	534.7	585.3	894.2	1411.9	1651.8
130°	554.7	605.2	890.0	1358.4	1567.7
132.5°	576.1	625.2	890.0	1316.7	1509.2
135°	606.4	657.0	886.4	1257.5	1421.4
137.5°	634.9	684.1	886.0	1207.4	1349.0
140°	656.3	706.9	884.6	1165.9	1301.9
142.5°	680.6	722.8	888.9	1132.8	1254.8
145°	715.2	751.8	893.5	1088.4	1186.0
147.5°	744.8	780.4	901.4	1043.5	1127.9
150°	770.5	794.9	904.2	1028.6	1087.9
152.5°	790.4	816.2	907.1	1008.6	1063.7
155°	816.8	836.0	914.9	983.6	1023.7
157.5°	849.6	861.2	916.7	972.3	1000.9
160°	866.8	875.5	923.8	963.6	988.0
162.5°	876.8	886.9	925.3	956.4	975.2
165°	902.4	905.9	925.6	945.6	959.5
167.5°	919.9	916.8	933.8	942.9	948.4
170°	925.6	923.9	931.0	932.9	939.9
172.5°	938.5	932.5	935.3	930.0	935.6
175°	945.2	940.0	936.3	930.8	923.8
177.5°	948.1	939.7	935.3	929.6	931.0
180°	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)