

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562363

Luminaire Tested: **SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562363
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7175.4 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 64.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562363
CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562363

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	40
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10535	10535	10535
5°	10604	10520	10474
10°	10519	10435	10378
15°	10407	10293	10254
20°	10284	10126	10106
25°	10140	9955	9924
30°	9926	9776	9711
35°	9643	9507	9451
40°	9342	9197	9161
45°	8980	8861	8822
50°	8606	8535	8477
55°	8205	8205	8076
60°	7704	7853	7575
65°	7051	7403	6875
70°	6215	6811	6053
75°	5308	6096	5165
80°	4118	5133	4171
85°	2668	3938	3515



TEST NUMBER: P562363

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	1.5
10°-20°	303.6	4.2
20°-30°	450.3	6.3
30°-40°	526.9	7.3
40°-50°	524.6	7.3
50°-60°	453.0	6.3
60°-70°	326.1	4.5
70°-80°	171.0	2.4
80°-90°	42.4	0.6
90°-100°	313.2	4.4
100°-110°	891.3	12.4
110°-120°	853.9	11.9
120°-130°	675.9	9.4
130°-140°	542.5	7.6
140°-150°	424.7	5.9
150°-160°	310.7	4.3
160°-170°	192.5	2.7
170°-180°	65.3	0.9
0°-30°	861.5	12.0
0°-40°	1388.4	19.3
0°-60°	2365.9	33.0
0°-90°	2905.4	40.5
90°-120°	2058.5	28.7
90°-150°	3701.5	51.6
90°-180°	4270.0	59.5
0°-180°	7175.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1142	1142	1142	1142	1142	
5°	1145	1132	1136	1133	1131	108
15°	1090	1076	1078	1076	1074	307
25°	996	979	978	972	975	458
35°	856	844	844	836	839	535
45°	688	682	679	677	676	531
55°	510	509	510	503	502	455
65°	323	333	339	326	315	320
75°	149	163	171	160	145	160
85°	25	33	37	35	33	33
90°	0	0	0	0	0	2
95°	34	135	606	210	129	39
105°	138	210	908	1604	1525	147
115°	258	311	689	1459	1713	253
125°	363	403	657	1091	1304	325
135°	444	481	650	922	1042	343
145°	524	551	655	798	869	327
155°	599	613	670	721	750	277
165°	661	664	678	693	703	186
175°	693	689	686	682	677	66
180°	687	687	687	687	687	



TEST NUMBER: P562363

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1141.9	1141.9	1141.9	1141.9	1141.9
2.5°	1148.4	1138.9	1141.9	1139.4	1133.9
5°	1145.0	1132.2	1135.9	1132.8	1130.9
7.5°	1133.3	1121.5	1124.2	1121.0	1119.8
10°	1122.8	1111.0	1113.8	1109.7	1107.7
12.5°	1110.8	1098.2	1100.9	1096.8	1095.7
15°	1089.6	1075.9	1077.6	1075.5	1073.5
17.5°	1065.1	1051.1	1051.4	1048.2	1047.8
20°	1047.4	1032.6	1031.3	1027.3	1029.3
22.5°	1028.1	1012.5	1011.2	1005.6	1008.3
25°	996.1	979.3	977.9	972.0	974.9
27.5°	959.0	942.5	942.5	934.2	937.3
30°	931.7	915.9	917.6	907.6	911.5
32.5°	902.7	888.5	889.4	879.4	883.4
35°	856.2	844.4	844.1	836.2	839.1
37.5°	808.7	798.3	796.6	792.0	792.8
40°	775.7	766.9	763.6	760.6	760.6
42.5°	741.1	733.0	729.8	727.6	726.8
45°	688.2	682.3	679.1	677.1	676.1
47.5°	635.9	630.4	627.6	626.2	625.2
50°	599.6	595.7	594.6	591.6	590.6
52.5°	563.4	561.1	560.0	556.2	555.2
55°	510.1	509.1	510.1	503.0	502.1
57.5°	454.6	456.1	459.4	449.9	447.5
60°	417.5	421.5	425.6	414.4	410.5
62.5°	379.7	386.0	391.8	379.0	373.5
65°	323.0	332.8	339.1	325.7	314.9
67.5°	268.2	280.4	288.0	273.6	261.4
70°	230.4	244.2	252.5	238.1	224.4
72.5°	197.4	212.7	219.5	205.9	192.2
75°	148.9	162.7	171.0	159.6	144.9
77.5°	105.6	118.6	125.6	115.6	103.4
80°	77.5	91.2	96.6	88.3	78.5
82.5°	54.9	66.3	70.0	65.0	58.4
85°	25.2	33.0	37.2	35.2	33.2
87.5°	6.4	11.9	15.3	15.3	16.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.5	55.4	128.6	37.4	28.2
95°	34.0	134.9	606.4	209.9	129.4
97.5°	62.5	158.1	933.9	668.3	457.9
100°	82.3	171.8	1005.0	1018.0	784.1
102.5°	104.3	186.6	989.3	1303.0	1098.8
105°	138.5	210.1	908.3	1604.4	1525.1
107.5°	173.3	237.4	813.7	1689.3	1759.9
110°	197.3	257.4	759.3	1656.8	1815.3

TEST NUMBER: P562363

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.3	277.3	722.7	1579.9	1805.9
115°	257.5	311.1	688.7	1459.0	1713.3
117.5°	290.1	340.5	668.6	1326.9	1596.2
120°	316.3	358.4	666.5	1251.3	1509.5
122.5°	337.2	379.3	661.3	1185.0	1424.8
125°	363.3	402.9	657.4	1090.9	1304.3
127.5°	391.8	428.9	655.3	1034.6	1210.4
130°	406.4	443.5	652.1	995.4	1148.8
132.5°	422.1	458.2	652.1	964.8	1105.9
135°	444.3	481.4	649.5	921.5	1041.6
137.5°	465.3	501.3	649.3	884.8	988.5
140°	480.9	518.0	648.2	854.4	954.0
142.5°	498.7	529.6	651.4	830.1	919.5
145°	524.1	550.9	654.8	797.5	869.1
147.5°	545.8	571.8	660.5	764.6	826.5
150°	564.6	582.5	662.6	753.8	797.2
152.5°	579.2	598.1	664.7	739.0	779.4
155°	598.6	612.6	670.4	720.8	750.2
157.5°	622.6	631.0	671.7	712.5	733.4
160°	635.1	641.5	677.0	706.1	724.0
162.5°	642.5	649.9	678.0	700.8	714.6
165°	661.3	663.8	678.3	692.9	703.1
167.5°	674.1	671.8	684.3	690.9	695.0
170°	678.3	677.0	682.2	683.6	688.7
172.5°	687.7	683.3	685.3	681.5	685.6
175°	692.7	688.8	686.1	682.1	677.0
177.5°	694.7	688.6	685.3	681.2	682.2
180°	687.4	687.4	687.4	687.4	687.4

(END OF REPORT)