

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562365

Luminaire Tested: **SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562365
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7482.1 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 64.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562365
CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562365

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	40
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10986	10986	10986
5°	11057	10969	10921
10°	10969	10881	10822
15°	10853	10732	10692
20°	10723	10558	10537
25°	10573	10381	10349
30°	10350	10193	10126
35°	10056	9914	9855
40°	9742	9591	9552
45°	9363	9240	9199
50°	8975	8899	8839
55°	8556	8556	8421
60°	8034	8189	7898
65°	7353	7719	7169
70°	6480	7103	6312
75°	5536	6356	5386
80°	4293	5350	4346
85°	2774	4107	3663



TEST NUMBER: P562365

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.1	1.5
10°-20°	316.6	4.2
20°-30°	469.6	6.3
30°-40°	549.4	7.3
40°-50°	547.0	7.3
50°-60°	472.3	6.3
60°-70°	340.0	4.5
70°-80°	178.3	2.4
80°-90°	44.2	0.6
90°-100°	326.6	4.4
100°-110°	929.4	12.4
110°-120°	890.4	11.9
120°-130°	704.7	9.4
130°-140°	565.7	7.6
140°-150°	442.8	5.9
150°-160°	324.0	4.3
160°-170°	200.7	2.7
170°-180°	68.1	0.9
0°-30°	898.3	12.0
0°-40°	1447.7	19.3
0°-60°	2467.0	33.0
0°-90°	3029.5	40.5
90°-120°	2146.4	28.7
90°-150°	3859.7	51.6
90°-180°	4453.0	59.5
0°-180°	7482.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1191	1191	1191	1191	1191	
5°	1194	1181	1184	1181	1179	113
15°	1136	1122	1124	1122	1119	320
25°	1039	1021	1020	1014	1017	478
35°	893	880	880	872	875	558
45°	718	711	708	706	705	554
55°	532	531	532	524	524	475
65°	337	347	354	340	328	334
75°	155	170	178	166	151	166
85°	26	34	39	37	35	35
90°	0	0	0	0	0	2
95°	35	141	632	219	135	40
105°	144	219	947	1673	1590	153
115°	268	324	718	1521	1786	264
125°	379	420	686	1138	1360	339
135°	463	502	677	961	1086	358
145°	546	574	683	832	906	341
155°	624	639	699	752	782	289
165°	690	692	707	722	733	194
175°	722	718	715	711	706	68
180°	717	717	717	717	717	

TEST NUMBER: P562365

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1190.7	1190.7	1190.7	1190.7	1190.7
2.5°	1197.5	1187.6	1190.7	1188.1	1182.3
5°	1193.9	1180.6	1184.4	1181.3	1179.2
7.5°	1181.7	1169.4	1172.3	1168.9	1167.7
10°	1170.8	1158.5	1161.4	1157.1	1155.1
12.5°	1158.2	1145.1	1147.9	1143.7	1142.5
15°	1136.2	1121.8	1123.6	1121.5	1119.4
17.5°	1110.6	1096.0	1096.3	1093.0	1092.5
20°	1092.1	1076.7	1075.3	1071.2	1073.2
22.5°	1072.0	1055.8	1054.4	1048.5	1051.4
25°	1038.6	1021.2	1019.7	1013.5	1016.6
27.5°	1000.0	982.8	982.8	974.1	977.4
30°	971.5	955.1	956.8	946.4	950.5
32.5°	941.3	926.5	927.4	917.0	921.1
35°	892.8	880.5	880.2	871.9	875.0
37.5°	843.3	832.4	830.7	825.9	826.7
40°	808.9	799.6	796.3	793.1	793.1
42.5°	772.8	764.4	761.0	758.7	757.9
45°	717.6	711.4	708.2	706.0	705.0
47.5°	663.0	657.3	654.4	652.9	651.9
50°	625.3	621.2	620.0	616.9	615.8
52.5°	587.5	585.0	583.9	579.9	578.9
55°	531.9	530.9	531.9	524.5	523.5
57.5°	474.0	475.6	479.0	469.1	466.6
60°	435.4	439.5	443.8	432.1	428.0
62.5°	395.9	402.5	408.5	395.2	389.4
65°	336.8	347.0	353.6	339.7	328.4
67.5°	279.7	292.4	300.3	285.3	272.6
70°	240.2	254.6	263.3	248.3	234.0
72.5°	205.8	221.8	228.9	214.7	200.4
75°	155.3	169.6	178.3	166.5	151.1
77.5°	110.2	123.7	130.9	120.6	107.8
80°	80.8	95.1	100.7	92.1	81.8
82.5°	57.3	69.2	73.0	67.8	60.8
85°	26.2	34.4	38.8	36.7	34.6
87.5°	6.7	12.5	15.9	16.0	16.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.9	57.8	134.1	39.0	29.4
95°	35.4	140.7	632.3	218.9	134.9
97.5°	65.1	164.8	973.8	696.8	477.5
100°	85.9	179.1	1047.9	1061.5	817.6
102.5°	108.7	194.6	1031.6	1358.7	1145.8
105°	144.4	219.1	947.1	1672.9	1590.3
107.5°	180.7	247.6	848.4	1761.5	1835.1
110°	205.8	268.4	791.7	1727.6	1892.8

TEST NUMBER: P562365

CATALOG NUMBER: SQ4-PW1-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	229.8	289.2	753.6	1647.4	1883.0
115°	268.5	324.4	718.2	1521.4	1786.5
117.5°	302.5	355.0	697.2	1383.6	1664.4
120°	329.8	373.8	695.0	1304.8	1574.0
122.5°	351.6	395.6	689.5	1235.7	1485.7
125°	378.8	420.1	685.5	1137.5	1360.0
127.5°	408.5	447.2	683.3	1078.8	1262.2
130°	423.8	462.5	680.0	1037.9	1197.8
132.5°	440.2	477.7	680.0	1006.0	1153.1
135°	463.3	502.0	677.3	960.8	1086.1
137.5°	485.1	522.7	677.0	922.6	1030.8
140°	501.5	540.1	675.9	890.9	994.8
142.5°	520.0	552.3	679.2	865.5	958.8
145°	546.5	574.4	682.7	831.6	906.2
147.5°	569.1	596.3	688.7	797.3	861.8
150°	588.7	607.4	690.9	786.0	831.3
152.5°	604.0	623.7	693.1	770.6	812.7
155°	624.1	638.8	699.1	751.6	782.2
157.5°	649.2	658.0	700.4	742.9	764.8
160°	662.3	668.9	705.9	736.3	755.0
162.5°	669.9	677.6	707.0	730.8	745.1
165°	689.5	692.2	707.3	722.5	733.1
167.5°	702.9	700.5	713.5	720.4	724.7
170°	707.3	705.9	711.3	712.8	718.2
172.5°	717.1	712.5	714.6	710.6	714.9
175°	722.2	718.3	715.4	711.2	705.9
177.5°	724.4	718.0	714.6	710.3	711.3
180°	716.8	716.8	716.8	716.8	716.8

(END OF REPORT)