

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562416

Luminaire Tested: **SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562416  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8467.0 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 73.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562416

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562416

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	28	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	32	28	25	24	21	19	16
6	61	49	41	35	55	44	38	33	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10788	10788	10788
5°	10858	10773	10725
10°	10772	10685	10627
15°	10658	10539	10500
20°	10530	10368	10349
25°	10384	10194	10163
30°	10163	10010	9944
35°	9875	9736	9677
40°	9567	9418	9381
45°	9195	9073	9033
50°	8813	8740	8681
55°	8401	8401	8270
60°	7890	8042	7756
65°	7220	7580	7041
70°	6364	6976	6196
75°	5436	6242	5290
80°	4213	5255	4272
85°	2731	4033	3599



TEST NUMBER: P562416

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	1.3
10°-20°	310.9	3.7
20°-30°	461.1	5.4
30°-40°	539.6	6.4
40°-50°	537.2	6.3
50°-60°	463.9	5.5
60°-70°	333.9	3.9
70°-80°	175.1	2.1
80°-90°	43.4	0.5
90°-100°	402.9	4.8
100°-110°	1146.3	13.5
110°-120°	1098.3	13.0
120°-130°	869.3	10.3
130°-140°	697.7	8.2
140°-150°	546.2	6.5
150°-160°	399.7	4.7
160°-170°	247.6	2.9
170°-180°	84.0	1.0
0°-30°	882.1	10.4
0°-40°	1421.7	16.8
0°-60°	2422.7	28.6
0°-90°	2975.1	35.1
90°-120°	2647.5	31.3
90°-150°	4760.6	56.2
90°-180°	5492.0	64.9
0°-180°	8467.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1172	1159	1163	1160	1158	111
15°	1116	1102	1103	1101	1099	314
25°	1020	1003	1001	995	998	469
35°	877	865	864	856	859	548
45°	705	699	695	693	692	544
55°	522	521	522	515	514	466
65°	331	341	347	334	322	328
75°	152	167	175	164	148	163
85°	26	34	38	36	34	34
90°	0	0	0	0	0	3
95°	44	174	780	270	166	50
105°	178	270	1168	2063	1962	188
115°	331	400	886	1876	2204	326
125°	467	518	846	1403	1678	418
135°	572	619	835	1185	1340	441
145°	674	708	842	1026	1118	421
155°	770	788	862	927	965	356
165°	850	854	872	891	904	239
175°	891	886	882	877	871	84
180°	884	884	884	884	884	

TEST NUMBER: P562416

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1169.3	1169.3	1169.3	1169.3	1169.3
2.5°	1175.9	1166.3	1169.3	1166.7	1161.1
5°	1172.4	1159.3	1163.2	1160.0	1158.0
7.5°	1160.5	1148.4	1151.2	1147.9	1146.7
10°	1149.8	1137.7	1140.5	1136.3	1134.3
12.5°	1137.4	1124.5	1127.3	1123.2	1122.0
15°	1115.8	1101.7	1103.4	1101.3	1099.3
17.5°	1090.6	1076.3	1076.6	1073.3	1072.9
20°	1072.5	1057.4	1056.0	1051.9	1054.0
22.5°	1052.7	1036.8	1035.4	1029.7	1032.5
25°	1020.0	1002.8	1001.4	995.3	998.3
27.5°	982.0	965.1	965.2	956.6	959.8
30°	954.0	937.9	939.6	929.4	933.4
32.5°	924.4	909.8	910.8	900.5	904.6
35°	876.8	864.7	864.4	856.2	859.2
37.5°	828.1	817.4	815.8	811.0	811.8
40°	794.3	785.3	782.0	778.9	778.9
42.5°	758.9	750.6	747.4	745.1	744.3
45°	704.7	698.7	695.4	693.3	692.3
47.5°	651.1	645.5	642.7	641.2	640.2
50°	614.0	610.0	608.9	605.8	604.8
52.5°	576.9	574.5	573.4	569.5	568.5
55°	522.3	521.3	522.3	515.1	514.1
57.5°	465.5	467.1	470.4	460.7	458.3
60°	427.6	431.6	435.8	424.4	420.3
62.5°	388.8	395.3	401.2	388.1	382.4
65°	330.7	340.8	347.2	333.6	322.5
67.5°	274.7	287.2	294.9	280.2	267.7
70°	235.9	250.0	258.6	243.9	229.7
72.5°	202.1	217.9	224.8	210.9	196.8
75°	152.5	166.6	175.1	163.5	148.4
77.5°	108.2	121.5	128.6	118.4	105.9
80°	79.3	93.4	98.9	90.4	80.4
82.5°	56.3	67.9	71.7	66.6	59.8
85°	25.8	33.8	38.1	36.0	34.0
87.5°	6.6	12.2	15.7	15.7	16.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.4	71.3	165.4	48.1	36.3
95°	43.7	173.5	779.9	269.9	166.4
97.5°	80.3	203.3	1201.1	859.5	589.0
100°	105.9	220.9	1292.6	1309.2	1008.5
102.5°	134.1	240.0	1272.4	1675.9	1413.2
105°	178.2	270.2	1168.2	2063.4	1961.5
107.5°	222.9	305.4	1046.5	2172.7	2263.4
110°	253.8	331.0	976.6	2130.9	2334.7

TEST NUMBER: P562416

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	283.4	356.7	929.5	2032.0	2322.6
115°	331.1	400.1	885.8	1876.5	2203.6
117.5°	373.1	437.9	859.9	1706.5	2053.0
120°	406.8	461.0	857.2	1609.4	1941.3
122.5°	433.7	487.9	850.5	1524.1	1832.4
125°	467.3	518.2	845.5	1403.0	1677.5
127.5°	503.9	551.6	842.8	1330.6	1556.8
130°	522.7	570.4	838.7	1280.2	1477.4
132.5°	542.9	589.3	838.7	1240.9	1422.3
135°	571.5	619.1	835.4	1185.1	1339.6
137.5°	598.4	644.7	835.0	1137.9	1271.4
140°	618.5	666.2	833.7	1098.8	1227.0
142.5°	641.4	681.2	837.7	1067.6	1182.6
145°	674.0	708.5	842.1	1025.7	1117.7
147.5°	701.9	735.4	849.5	983.4	1063.0
150°	726.1	749.1	852.2	969.4	1025.3
152.5°	744.9	769.3	854.9	950.5	1002.4
155°	769.8	787.9	862.3	927.0	964.8
157.5°	800.7	811.6	863.9	916.3	943.3
160°	816.9	825.1	870.7	908.2	931.2
162.5°	826.3	835.8	872.0	901.3	919.1
165°	850.5	853.8	872.3	891.1	904.3
167.5°	867.0	864.0	880.1	888.6	893.9
170°	872.3	870.7	877.4	879.2	885.8
172.5°	884.4	878.9	881.4	876.5	881.8
175°	890.8	885.9	882.4	877.2	870.7
177.5°	893.5	885.6	881.4	876.1	877.4
180°	884.1	884.1	884.1	884.1	884.1

(END OF REPORT)