

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562454

Luminaire Tested: **SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562454  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (3000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8403.4 lumens  
Efficiency: N/A  
Efficacy: 116.9 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 71.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562454  
CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (3000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562454

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (3000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23				
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20				
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16				
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19	14				
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12				
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14	10				
6	59	47	39	34	52	42	36	31	33	28	25	24	21	18	16	14	13	9				
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	7				
10	43	32	25	20	38	29	23	18	22	18	15	17	14	11	11	9	8	6				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7035	7035	7035
5°	7080	7025	6993
10°	7024	6967	6930
15°	6950	6872	6847
20°	6867	6761	6748
25°	6771	6648	6627
30°	6628	6527	6485
35°	6439	6348	6311
40°	6239	6141	6117
45°	5995	5917	5891
50°	5747	5698	5661
55°	5479	5479	5392
60°	5145	5244	5058
65°	4709	4943	4591
70°	4149	4548	4041
75°	3543	4071	3447
80°	2747	3427	2784
85°	1778	2636	2350



TEST NUMBER: P562454

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (3000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.8	0.9
10°-20°	202.7	2.4
20°-30°	300.7	3.6
30°-40°	351.8	4.2
40°-50°	350.3	4.2
50°-60°	302.5	3.6
60°-70°	217.7	2.6
70°-80°	114.2	1.4
80°-90°	28.3	0.3
90°-100°	474.1	5.6
100°-110°	1349.1	16.1
110°-120°	1292.6	15.4
120°-130°	1023.0	12.2
130°-140°	821.1	9.8
140°-150°	642.8	7.6
150°-160°	470.4	5.6
160°-170°	291.4	3.5
170°-180°	98.9	1.2
0°-30°	575.2	6.8
0°-40°	927.0	11.0
0°-60°	1579.8	18.8
0°-90°	1940.0	23.1
90°-120°	3115.8	37.1
90°-150°	5602.8	66.7
90°-180°	6463.0	76.9
0°-180°	8403.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	762	762	762	762	762	
5°	764	756	758	756	755	72
15°	728	718	720	718	717	205
25°	665	654	653	649	651	306
35°	572	564	564	558	560	357
45°	460	456	454	452	452	355
55°	341	340	341	336	335	304
65°	216	222	226	218	210	214
75°	99	109	114	107	97	107
85°	17	22	25	24	22	22
90°	0	0	0	0	0	3
95°	51	204	918	318	196	59
105°	210	318	1375	2428	2308	222
115°	390	471	1042	2208	2593	384
125°	550	610	995	1651	1974	492
135°	673	729	983	1395	1577	519
145°	793	834	991	1207	1316	496
155°	906	927	1015	1091	1136	419
165°	1001	1005	1027	1049	1064	281
175°	1048	1043	1038	1032	1025	99
180°	1040	1040	1040	1040	1040	

TEST NUMBER: P562454

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	762.5	762.5	762.5	762.5	762.5
2.5°	766.8	760.5	762.5	760.8	757.1
5°	764.5	756.0	758.5	756.4	755.1
7.5°	756.7	748.8	750.7	748.5	747.7
10°	749.7	741.9	743.7	741.0	739.7
12.5°	741.7	733.3	735.1	732.4	731.6
15°	727.6	718.4	719.5	718.1	716.8
17.5°	711.2	701.8	702.0	699.9	699.6
20°	699.4	689.5	688.6	685.9	687.3
22.5°	686.5	676.1	675.2	671.4	673.3
25°	665.1	653.9	653.0	649.0	651.0
27.5°	640.4	629.3	629.3	623.8	625.9
30°	622.1	611.6	612.7	606.0	608.7
32.5°	602.7	593.3	593.9	587.2	589.8
35°	571.7	563.8	563.6	558.3	560.3
37.5°	540.0	533.0	531.9	528.9	529.4
40°	518.0	512.1	509.9	507.9	507.9
42.5°	494.9	489.5	487.3	485.8	485.3
45°	459.5	455.6	453.5	452.1	451.5
47.5°	424.6	420.9	419.1	418.1	417.5
50°	400.4	397.8	397.0	395.0	394.4
52.5°	376.2	374.6	373.9	371.4	370.7
55°	340.6	339.9	340.6	335.9	335.2
57.5°	303.5	304.6	306.7	300.4	298.8
60°	278.8	281.4	284.2	276.7	274.1
62.5°	253.5	257.7	261.6	253.1	249.4
65°	215.7	222.2	226.4	217.5	210.3
67.5°	179.1	187.2	192.3	182.7	174.5
70°	153.8	163.0	168.6	159.0	149.8
72.5°	131.8	142.1	146.6	137.5	128.3
75°	99.4	108.6	114.2	106.6	96.7
77.5°	70.5	79.2	83.8	77.2	69.1
80°	51.7	60.9	64.5	59.0	52.4
82.5°	36.7	44.3	46.8	43.4	39.0
85°	16.8	22.1	24.9	23.5	22.2
87.5°	4.3	8.0	10.2	10.2	10.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.8	83.9	194.7	56.7	42.7
95°	51.4	204.2	917.9	317.7	195.8
97.5°	94.6	239.2	1413.6	1011.5	693.2
100°	124.6	260.0	1521.2	1540.9	1186.9
102.5°	157.9	282.4	1497.5	1972.3	1663.2
105°	209.7	318.0	1374.8	2428.4	2308.5
107.5°	262.3	359.4	1231.6	2557.0	2663.8
110°	298.7	389.6	1149.3	2507.8	2747.7



TEST NUMBER: P562454

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	333.5	419.8	1093.9	2391.5	2733.4
115°	389.7	470.9	1042.5	2208.5	2593.4
117.5°	439.2	515.4	1012.0	2008.4	2416.1
120°	478.7	542.5	1008.9	1894.1	2284.8
122.5°	510.4	574.2	1001.0	1793.7	2156.6
125°	549.9	609.9	995.0	1651.2	1974.2
127.5°	593.1	649.1	991.9	1566.0	1832.2
130°	615.2	671.3	987.1	1506.7	1738.8
132.5°	638.9	693.5	987.1	1460.4	1673.9
135°	672.6	728.7	983.2	1394.8	1576.6
137.5°	704.2	758.8	982.8	1339.2	1496.3
140°	728.0	784.1	981.2	1293.2	1444.1
142.5°	754.9	801.7	985.9	1256.4	1391.8
145°	793.2	833.9	991.1	1207.2	1315.5
147.5°	826.1	865.5	999.8	1157.4	1251.0
150°	854.6	881.6	1002.9	1140.9	1206.7
152.5°	876.7	905.4	1006.1	1118.7	1179.8
155°	906.0	927.3	1014.8	1091.0	1135.5
157.5°	942.4	955.2	1016.8	1078.4	1110.1
160°	961.4	971.1	1024.7	1068.8	1095.9
162.5°	972.5	983.7	1026.3	1060.8	1081.7
165°	1001.0	1004.8	1026.7	1048.8	1064.3
167.5°	1020.3	1016.9	1035.8	1045.8	1052.0
170°	1026.7	1024.7	1032.6	1034.8	1042.5
172.5°	1040.9	1034.3	1037.4	1031.6	1037.7
175°	1048.4	1042.6	1038.5	1032.4	1024.7
177.5°	1051.6	1042.3	1037.4	1031.1	1032.6
180°	1040.5	1040.5	1040.5	1040.5	1040.5

(END OF REPORT)