

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562420

Luminaire Tested: **SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562420
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8984.1 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562420

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562420

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	28	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	32	28	25	24	21	19	16
6	61	49	41	35	55	44	38	33	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11448	11448	11448
5°	11521	11430	11380
10°	11430	11338	11276
15°	11308	11183	11141
20°	11173	11001	10980
25°	11018	10817	10784
30°	10785	10622	10551
35°	10478	10331	10269
40°	10151	9993	9953
45°	9756	9628	9585
50°	9351	9274	9211
55°	8915	8915	8775
60°	8372	8532	8230
65°	7661	8043	7471
70°	6752	7402	6577
75°	5768	6623	5611
80°	4474	5574	4532
85°	2890	4277	3822



TEST NUMBER: P562420

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	1.3
10°-20°	329.9	3.7
20°-30°	489.3	5.4
30°-40°	572.5	6.4
40°-50°	570.0	6.3
50°-60°	492.2	5.5
60°-70°	354.3	3.9
70°-80°	185.8	2.1
80°-90°	46.1	0.5
90°-100°	427.5	4.8
100°-110°	1216.3	13.5
110°-120°	1165.4	13.0
120°-130°	922.3	10.3
130°-140°	740.3	8.2
140°-150°	579.6	6.5
150°-160°	424.1	4.7
160°-170°	262.7	2.9
170°-180°	89.1	1.0
0°-30°	936.0	10.4
0°-40°	1508.5	16.8
0°-60°	2570.7	28.6
0°-90°	3156.8	35.1
90°-120°	2809.1	31.3
90°-150°	5051.4	56.2
90°-180°	5827.0	64.9
0°-180°	8984.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1241	1241	1241	1241	1241	
5°	1244	1230	1234	1231	1229	118
15°	1184	1169	1171	1169	1166	334
25°	1082	1064	1063	1056	1059	498
35°	930	918	917	908	912	582
45°	748	741	738	736	735	577
55°	554	553	554	547	546	495
65°	351	362	368	354	342	348
75°	162	177	186	174	157	173
85°	27	36	40	38	36	36
90°	0	0	0	0	0	3
95°	46	184	828	286	177	53
105°	189	287	1240	2189	2081	200
115°	351	425	940	1991	2338	346
125°	496	550	897	1489	1780	444
135°	606	657	886	1258	1421	468
145°	715	752	894	1088	1186	447
155°	817	836	915	984	1024	378
165°	902	906	926	946	960	254
175°	945	940	936	931	924	90
180°	938	938	938	938	938	

TEST NUMBER: P562420

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1247.8	1237.5	1240.8	1238.0	1232.0
5°	1244.0	1230.1	1234.2	1230.9	1228.7
7.5°	1231.4	1218.5	1221.5	1218.0	1216.7
10°	1220.0	1207.2	1210.2	1205.7	1203.6
12.5°	1206.9	1193.2	1196.2	1191.8	1190.5
15°	1183.9	1169.0	1170.8	1168.6	1166.4
17.5°	1157.2	1142.1	1142.4	1138.9	1138.4
20°	1138.0	1122.0	1120.5	1116.2	1118.3
22.5°	1117.0	1100.1	1098.6	1092.6	1095.6
25°	1082.3	1064.1	1062.6	1056.1	1059.3
27.5°	1042.0	1024.1	1024.1	1015.0	1018.4
30°	1012.3	995.2	997.0	986.1	990.4
32.5°	980.8	965.4	966.4	955.5	959.8
35°	930.3	917.5	917.2	908.5	911.7
37.5°	878.7	867.4	865.6	860.6	861.4
40°	842.8	833.2	829.7	826.4	826.4
42.5°	805.2	796.5	793.0	790.6	789.7
45°	747.7	741.3	737.9	735.7	734.6
47.5°	690.9	684.9	681.9	680.4	679.3
50°	651.5	647.3	646.1	642.8	641.7
52.5°	612.2	609.6	608.5	604.3	603.2
55°	554.2	553.2	554.2	546.6	545.5
57.5°	493.9	495.6	499.1	488.8	486.2
60°	453.7	457.9	462.4	450.3	446.0
62.5°	412.6	419.4	425.7	411.8	405.8
65°	350.9	361.6	368.4	353.9	342.2
67.5°	291.4	304.7	312.9	297.3	284.0
70°	250.3	265.3	274.4	258.7	243.8
72.5°	214.5	231.2	238.5	223.8	208.8
75°	161.8	176.8	185.8	173.5	157.4
77.5°	114.8	128.9	136.4	125.6	112.4
80°	84.2	99.1	104.9	96.0	85.3
82.5°	59.7	72.1	76.1	70.7	63.4
85°	27.3	35.9	40.4	38.2	36.1
87.5°	7.0	13.0	16.6	16.6	17.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.3	75.7	175.5	51.1	38.5
95°	46.4	184.1	827.5	286.4	176.6
97.5°	85.2	215.7	1274.5	912.0	624.9
100°	112.4	234.4	1371.5	1389.2	1070.1
102.5°	142.3	254.6	1350.1	1778.2	1499.5
105°	189.0	286.7	1239.5	2189.4	2081.3
107.5°	236.5	324.0	1110.4	2305.4	2401.6
110°	269.3	351.3	1036.2	2261.0	2477.2

TEST NUMBER: P562420

CATALOG NUMBER: SQ4-PW1-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	378.5	986.3	2156.1	2464.4
115°	351.3	424.6	939.9	1991.1	2338.1
117.5°	395.9	464.6	912.4	1810.7	2178.3
120°	431.6	489.1	909.6	1707.7	2059.9
122.5°	460.1	517.7	902.4	1617.2	1944.3
125°	495.8	549.9	897.1	1488.7	1779.9
127.5°	534.7	585.3	894.2	1411.9	1651.8
130°	554.7	605.2	890.0	1358.4	1567.7
132.5°	576.1	625.2	890.0	1316.7	1509.2
135°	606.4	657.0	886.4	1257.5	1421.4
137.5°	634.9	684.1	886.0	1207.4	1349.0
140°	656.3	706.9	884.6	1165.9	1301.9
142.5°	680.6	722.8	888.9	1132.8	1254.8
145°	715.2	751.8	893.5	1088.4	1186.0
147.5°	744.8	780.4	901.4	1043.5	1127.9
150°	770.5	794.9	904.2	1028.6	1087.9
152.5°	790.4	816.2	907.1	1008.6	1063.7
155°	816.8	836.0	914.9	983.6	1023.7
157.5°	849.6	861.2	916.7	972.3	1000.9
160°	866.8	875.5	923.8	963.6	988.0
162.5°	876.8	886.9	925.3	956.4	975.2
165°	902.4	905.9	925.6	945.6	959.5
167.5°	919.9	916.8	933.8	942.9	948.4
170°	925.6	923.9	931.0	932.9	939.9
172.5°	938.5	932.5	935.3	930.0	935.6
175°	945.2	940.0	936.3	930.8	923.8
177.5°	948.1	939.7	935.3	929.6	931.0
180°	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)