

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562430

Luminaire Tested: **SQ4-PW1-125U-100D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562430  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-125U-100D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9574.9 lumens  
Efficiency: N/A  
Efficacy: 114.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 83.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562430  
CATALOG NUMBER: SQ4-PW1-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562430

CATALOG NUMBER: SQ4-PW1-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	55	49	66	57	50	45	47	42	38	38	35	32	30	28	25	22
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	16
7	57	45	37	32	52	41	34	29	35	29	25	28	24	21	22	20	17	15
8	53	41	33	28	48	38	31	26	31	26	22	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14442	14442	14442
5°	14536	14420	14356
10°	14419	14303	14225
15°	14266	14108	14055
20°	14096	13879	13853
25°	13899	13646	13605
30°	13606	13400	13312
35°	13218	13033	12955
40°	12806	12608	12557
45°	12308	12146	12093
50°	11799	11699	11621
55°	11247	11247	11070
60°	10560	10765	10383
65°	9665	10147	9424
70°	8519	9339	8295
75°	7276	8359	7080
80°	5643	7035	5717
85°	3652	5399	4817



TEST NUMBER: P562430

CATALOG NUMBER: SQ4-PW1-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.4	1.5
10°-20°	416.1	4.3
20°-30°	617.3	6.4
30°-40°	722.3	7.5
40°-50°	719.1	7.5
50°-60°	620.9	6.5
60°-70°	447.0	4.7
70°-80°	234.4	2.4
80°-90°	58.1	0.6
90°-100°	410.2	4.3
100°-110°	1167.3	12.2
110°-120°	1118.4	11.7
120°-130°	885.2	9.2
130°-140°	710.5	7.4
140°-150°	556.2	5.8
150°-160°	407.0	4.3
160°-170°	252.1	2.6
170°-180°	85.5	0.9
0°-30°	1180.8	12.3
0°-40°	1903.1	19.9
0°-60°	3243.1	33.9
0°-90°	3982.6	41.6
90°-120°	2695.9	28.2
90°-150°	4847.7	50.6
90°-180°	5592.0	58.4
0°-180°	9574.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1570	1552	1557	1553	1550	149
15°	1494	1475	1477	1474	1472	421
25°	1365	1342	1340	1332	1336	628
35°	1174	1158	1157	1146	1150	734
45°	943	935	931	928	927	728
55°	699	698	699	690	688	624
65°	443	456	465	446	432	439
75°	204	223	234	219	199	219
85°	34	45	51	48	46	45
90°	0	0	0	0	0	3
95°	44	177	794	275	169	51
105°	181	275	1190	2101	1997	192
115°	337	408	902	1911	2244	332
125°	476	528	861	1429	1708	426
135°	582	630	851	1207	1364	449
145°	686	722	858	1044	1138	429
155°	784	802	878	944	982	362
165°	866	869	888	907	921	244
175°	907	902	899	893	887	86
180°	900	900	900	900	900	



TEST NUMBER: P562430

CATALOG NUMBER: SQ4-PW1-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1565.3	1565.3	1565.3	1565.3	1565.3
2.5°	1574.1	1561.2	1565.3	1561.8	1554.3
5°	1569.5	1551.9	1557.0	1552.8	1550.1
7.5°	1553.5	1537.3	1541.0	1536.6	1535.0
10°	1539.1	1522.9	1526.7	1521.1	1518.4
12.5°	1522.6	1505.3	1509.0	1503.5	1501.9
15°	1493.6	1474.7	1477.0	1474.2	1471.5
17.5°	1459.9	1440.8	1441.2	1436.8	1436.2
20°	1435.7	1415.4	1413.6	1408.2	1410.9
22.5°	1409.2	1387.9	1386.0	1378.4	1382.2
25°	1365.3	1342.4	1340.5	1332.3	1336.4
27.5°	1314.6	1291.9	1292.0	1280.5	1284.8
30°	1277.1	1255.5	1257.8	1244.1	1249.5
32.5°	1237.4	1217.9	1219.2	1205.5	1210.9
35°	1173.6	1157.5	1157.1	1146.2	1150.2
37.5°	1108.5	1094.3	1092.0	1085.7	1086.8
40°	1063.3	1051.2	1046.8	1042.6	1042.6
42.5°	1015.9	1004.8	1000.4	997.4	996.3
45°	943.3	935.2	930.9	928.1	926.8
47.5°	871.6	864.1	860.3	858.3	857.0
50°	822.0	816.6	815.1	810.9	809.6
52.5°	772.3	769.1	767.6	762.4	761.0
55°	699.2	697.9	699.2	689.5	688.2
57.5°	623.1	625.2	629.7	616.7	613.4
60°	572.3	577.7	583.4	568.1	562.7
62.5°	520.5	529.1	537.0	519.5	511.9
65°	442.7	456.2	464.8	446.5	431.7
67.5°	367.7	384.4	394.7	375.0	358.3
70°	315.8	334.7	346.2	326.4	307.5
72.5°	270.6	291.6	300.9	282.3	263.4
75°	204.1	223.0	234.5	218.8	198.6
77.5°	144.8	162.6	172.1	158.5	141.8
80°	106.2	125.1	132.4	121.1	107.6
82.5°	75.3	90.9	96.0	89.2	80.0
85°	34.5	45.3	51.0	48.2	45.5
87.5°	8.8	16.4	21.0	21.0	22.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.7	72.6	168.4	49.0	37.0
95°	44.5	176.7	794.2	274.9	169.4
97.5°	81.8	207.0	1223.1	875.2	599.7
100°	107.8	225.0	1316.2	1333.2	1026.9
102.5°	136.6	244.4	1295.7	1706.5	1439.1
105°	181.4	275.1	1189.5	2101.2	1997.4
107.5°	227.0	311.0	1065.6	2212.4	2304.8
110°	258.4	337.1	994.4	2169.9	2377.4



TEST NUMBER: P562430

CATALOG NUMBER: SQ4-PW1-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	363.2	946.5	2069.2	2365.0
115°	337.2	407.5	902.0	1910.8	2243.9
117.5°	380.0	445.9	875.6	1737.7	2090.5
120°	414.2	469.4	872.9	1638.8	1976.9
122.5°	441.6	496.8	866.1	1552.0	1866.0
125°	475.8	527.7	860.9	1428.7	1708.1
127.5°	513.1	561.7	858.2	1355.0	1585.3
130°	532.3	580.8	854.1	1303.6	1504.5
132.5°	552.8	600.0	854.1	1263.6	1448.3
135°	581.9	630.5	850.7	1206.8	1364.1
137.5°	609.3	656.5	850.3	1158.7	1294.6
140°	629.9	678.4	848.9	1118.9	1249.4
142.5°	653.1	693.6	853.0	1087.1	1204.3
145°	686.3	721.5	857.5	1044.5	1138.2
147.5°	714.8	748.9	865.0	1001.4	1082.4
150°	739.4	762.8	867.8	987.2	1044.1
152.5°	758.6	783.3	870.5	967.9	1020.8
155°	783.9	802.3	878.0	943.9	982.4
157.5°	815.4	826.4	879.7	933.1	960.5
160°	831.8	840.2	886.6	924.8	948.2
162.5°	841.4	851.1	888.0	917.8	935.9
165°	866.1	869.4	888.3	907.4	920.8
167.5°	882.8	879.8	896.2	904.9	910.2
170°	888.3	886.6	893.4	895.3	902.0
172.5°	900.6	894.9	897.5	892.5	897.9
175°	907.1	902.1	898.6	893.3	886.6
177.5°	909.9	901.8	897.5	892.1	893.4
180°	900.3	900.3	900.3	900.3	900.3

(END OF REPORT)