

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562459

Luminaire Tested: **SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562459
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9130.6 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562459
CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562459

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14
6	59	47	39	34	52	42	36	31	33	28	25	24	21	18	16	14	13
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	29	23	18	22	18	15	17	14	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7644	7644	7644
5°	7693	7632	7599
10°	7632	7570	7529
15°	7551	7467	7439
20°	7461	7346	7331
25°	7356	7223	7200
30°	7201	7092	7045
35°	6997	6898	6857
40°	6778	6672	6646
45°	6515	6429	6400
50°	6244	6192	6150
55°	5953	5953	5858
60°	5589	5698	5495
65°	5115	5370	4988
70°	4510	4942	4392
75°	3850	4424	3747
80°	2986	3725	3023
85°	1927	2858	2551



TEST NUMBER: P562459

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	0.9
10°-20°	220.3	2.4
20°-30°	326.7	3.6
30°-40°	382.3	4.2
40°-50°	380.6	4.2
50°-60°	328.7	3.6
60°-70°	236.6	2.6
70°-80°	124.1	1.4
80°-90°	30.8	0.3
90°-100°	515.2	5.6
100°-110°	1465.8	16.1
110°-120°	1404.4	15.4
120°-130°	1111.5	12.2
130°-140°	892.2	9.8
140°-150°	698.5	7.6
150°-160°	511.1	5.6
160°-170°	316.6	3.5
170°-180°	107.4	1.2
0°-30°	625.0	6.8
0°-40°	1007.3	11.0
0°-60°	1716.5	18.8
0°-90°	2107.9	23.1
90°-120°	3385.4	37.1
90°-150°	6087.6	66.7
90°-180°	7023.0	76.9
0°-180°	9130.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	828	828	828	828	828	
5°	831	821	824	822	820	79
15°	790	780	782	780	779	223
25°	723	710	710	705	707	332
35°	621	613	612	607	609	388
45°	499	495	493	491	490	385
55°	370	369	370	365	364	330
65°	234	241	246	236	228	232
75°	108	118	124	116	105	116
85°	18	24	27	26	24	24
90°	0	0	0	0	0	3
95°	56	222	997	345	213	64
105°	228	346	1494	2639	2508	241
115°	423	512	1133	2400	2818	417
125°	598	663	1081	1794	2145	535
135°	731	792	1068	1516	1713	564
145°	862	906	1077	1312	1429	538
155°	984	1008	1103	1185	1234	455
165°	1088	1092	1116	1140	1156	306
175°	1139	1133	1128	1122	1113	108
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P562459

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	828.5	828.5	828.5	828.5	828.5
2.5°	833.2	826.3	828.5	826.6	822.6
5°	830.7	821.4	824.1	821.9	820.5
7.5°	822.2	813.6	815.6	813.3	812.4
10°	814.6	806.0	808.0	805.1	803.7
12.5°	805.9	796.7	798.7	795.8	794.9
15°	790.5	780.5	781.8	780.3	778.8
17.5°	772.7	762.6	762.8	760.4	760.2
20°	759.9	749.2	748.2	745.3	746.7
22.5°	745.9	734.6	733.6	729.5	731.5
25°	722.6	710.5	709.5	705.2	707.3
27.5°	695.8	683.8	683.8	677.7	680.0
30°	675.9	664.5	665.7	658.5	661.3
32.5°	654.9	644.6	645.3	638.0	640.9
35°	621.2	612.6	612.4	606.6	608.8
37.5°	586.7	579.2	578.0	574.6	575.2
40°	562.8	556.4	554.0	551.8	551.8
42.5°	537.7	531.8	529.5	527.9	527.3
45°	499.3	495.0	492.7	491.2	490.5
47.5°	461.3	457.3	455.3	454.3	453.6
50°	435.0	432.2	431.4	429.2	428.5
52.5°	408.8	407.1	406.3	403.5	402.8
55°	370.1	369.4	370.1	365.0	364.2
57.5°	329.8	330.9	333.3	326.4	324.7
60°	302.9	305.8	308.8	300.7	297.8
62.5°	275.5	280.0	284.2	275.0	271.0
65°	234.3	241.4	246.0	236.3	228.5
67.5°	194.6	203.5	208.9	198.5	189.6
70°	167.2	177.1	183.2	172.8	162.8
72.5°	143.2	154.3	159.3	149.4	139.4
75°	108.0	118.0	124.1	115.8	105.1
77.5°	76.6	86.1	91.1	83.9	75.0
80°	56.2	66.2	70.1	64.1	56.9
82.5°	39.9	48.1	50.8	47.2	42.3
85°	18.2	24.0	27.0	25.5	24.1
87.5°	4.7	8.7	11.1	11.1	11.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.2	91.2	211.5	61.6	46.4
95°	55.9	221.9	997.3	345.2	212.8
97.5°	102.7	259.9	1535.9	1099.1	753.1
100°	135.4	282.5	1652.8	1674.2	1289.6
102.5°	171.5	306.9	1627.1	2143.0	1807.2
105°	227.8	345.5	1493.8	2638.6	2508.3
107.5°	285.0	390.5	1338.2	2778.3	2894.3
110°	324.6	423.3	1248.8	2724.8	2985.4

TEST NUMBER: P562459

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	362.4	456.1	1188.6	2598.4	2970.0
115°	423.4	511.7	1132.7	2399.6	2817.8
117.5°	477.2	560.0	1099.6	2182.2	2625.2
120°	520.1	589.5	1096.2	2058.0	2482.5
122.5°	554.5	623.9	1087.6	1949.0	2343.2
125°	597.5	662.7	1081.1	1794.1	2145.0
127.5°	644.4	705.3	1077.7	1701.5	1990.7
130°	668.4	729.4	1072.5	1637.1	1889.3
132.5°	694.2	753.5	1072.5	1586.8	1818.8
135°	730.8	791.7	1068.2	1515.5	1713.0
137.5°	765.2	824.4	1067.8	1455.1	1625.8
140°	791.0	851.9	1066.1	1405.1	1569.0
142.5°	820.2	871.0	1071.2	1365.2	1512.3
145°	861.9	906.0	1076.8	1311.6	1429.3
147.5°	897.6	940.4	1086.3	1257.5	1359.2
150°	928.5	957.9	1089.7	1239.6	1311.1
152.5°	952.6	983.7	1093.2	1215.5	1281.9
155°	984.4	1007.5	1102.6	1185.4	1233.7
157.5°	1023.9	1037.8	1104.8	1171.7	1206.2
160°	1044.6	1055.1	1113.4	1161.3	1190.7
162.5°	1056.6	1068.8	1115.1	1152.6	1175.3
165°	1087.6	1091.8	1115.5	1139.5	1156.3
167.5°	1108.6	1104.8	1125.4	1136.3	1143.0
170°	1115.5	1113.4	1122.0	1124.3	1132.7
172.5°	1131.0	1123.8	1127.1	1120.8	1127.5
175°	1139.2	1132.8	1128.4	1121.8	1113.4
177.5°	1142.6	1132.5	1127.1	1120.3	1122.0
180°	1130.6	1130.6	1130.6	1130.6	1130.6

(END OF REPORT)