

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562460

Luminaire Tested: **SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562460  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (6500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9217.1 lumens  
Efficiency: N/A  
Efficacy: 129.3 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 71.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562460  
CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562460

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14	10
6	59	47	39	34	52	42	36	31	33	28	25	24	21	18	16	14	13	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	18	22	18	15	17	14	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7716	7716	7716
5°	7766	7705	7670
10°	7704	7642	7601
15°	7622	7538	7510
20°	7532	7416	7401
25°	7426	7291	7269
30°	7269	7159	7112
35°	7063	6963	6921
40°	6842	6736	6710
45°	6576	6490	6461
50°	6304	6251	6208
55°	6010	6010	5915
60°	5643	5752	5547
65°	5163	5421	5034
70°	4551	4990	4432
75°	3889	4467	3782
80°	3013	3756	3055
85°	1948	2890	2572



TEST NUMBER: P562460

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.8	0.9
10°-20°	222.3	2.4
20°-30°	329.8	3.6
30°-40°	385.9	4.2
40°-50°	384.2	4.2
50°-60°	331.8	3.6
60°-70°	238.8	2.6
70°-80°	125.2	1.4
80°-90°	31.1	0.3
90°-100°	520.1	5.6
100°-110°	1479.7	16.1
110°-120°	1417.7	15.4
120°-130°	1122.1	12.2
130°-140°	900.6	9.8
140°-150°	705.1	7.6
150°-160°	515.9	5.6
160°-170°	319.6	3.5
170°-180°	108.4	1.2
0°-30°	630.9	6.8
0°-40°	1016.8	11.0
0°-60°	1732.8	18.8
0°-90°	2127.9	23.1
90°-120°	3417.5	37.1
90°-150°	6145.3	66.7
90°-180°	7089.0	76.9
0°-180°	9217.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	838	829	832	830	828	79
15°	798	788	789	788	786	225
25°	730	717	716	712	714	335
35°	627	618	618	612	614	392
45°	504	500	497	496	495	389
55°	374	373	374	368	368	333
65°	236	244	248	239	231	234
75°	109	119	125	117	106	117
85°	18	24	27	26	24	24
90°	0	0	0	0	0	3
95°	56	224	1007	348	215	64
105°	230	349	1508	2664	2532	243
115°	427	516	1143	2422	2844	421
125°	603	669	1091	1811	2165	540
135°	738	799	1078	1530	1729	569
145°	870	915	1087	1324	1443	544
155°	994	1017	1113	1197	1245	459
165°	1098	1102	1126	1150	1167	309
175°	1150	1144	1139	1132	1124	109
180°	1141	1141	1141	1141	1141	

TEST NUMBER: P562460

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	836.3	836.3	836.3	836.3	836.3
2.5°	841.1	834.1	836.3	834.5	830.4
5°	838.5	829.2	831.9	829.7	828.2
7.5°	830.0	821.4	823.4	821.0	820.1
10°	822.3	813.7	815.7	812.7	811.3
12.5°	813.5	804.3	806.3	803.3	802.4
15°	798.0	787.9	789.2	787.7	786.2
17.5°	780.0	769.8	770.0	767.7	767.4
20°	767.1	756.3	755.3	752.4	753.8
22.5°	752.9	741.5	740.5	736.5	738.5
25°	729.5	717.2	716.2	711.9	714.0
27.5°	702.4	690.3	690.3	684.2	686.5
30°	682.3	670.8	672.0	664.7	667.6
32.5°	661.1	650.7	651.4	644.1	647.0
35°	627.1	618.4	618.2	612.4	614.5
37.5°	592.3	584.7	583.4	580.1	580.6
40°	568.1	561.6	559.3	557.1	557.1
42.5°	542.8	536.9	534.5	532.9	532.3
45°	504.0	499.7	497.4	495.9	495.2
47.5°	465.7	461.7	459.7	458.6	457.9
50°	439.2	436.3	435.5	433.3	432.5
52.5°	412.6	410.9	410.1	407.3	406.6
55°	373.6	372.9	373.6	368.4	367.7
57.5°	332.9	334.1	336.5	329.5	327.8
60°	305.8	308.7	311.7	303.5	300.6
62.5°	278.1	282.7	286.9	277.6	273.5
65°	236.5	243.7	248.3	238.6	230.6
67.5°	196.4	205.4	210.9	200.4	191.4
70°	168.7	178.8	185.0	174.4	164.3
72.5°	144.6	155.8	160.8	150.8	140.7
75°	109.1	119.1	125.3	116.9	106.1
77.5°	77.4	86.9	92.0	84.7	75.7
80°	56.7	66.8	70.7	64.7	57.5
82.5°	40.2	48.6	51.3	47.6	42.7
85°	18.4	24.2	27.3	25.8	24.3
87.5°	4.7	8.8	11.2	11.2	11.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.4	92.0	213.5	62.1	46.9
95°	56.4	224.0	1006.8	348.5	214.8
97.5°	103.7	262.4	1550.5	1109.5	760.3
100°	136.7	285.2	1668.5	1690.1	1301.8
102.5°	173.1	309.8	1642.5	2163.3	1824.3
105°	230.0	348.8	1508.0	2663.6	2532.1
107.5°	287.7	394.2	1350.9	2804.6	2921.8
110°	327.6	427.3	1260.6	2750.7	3013.7

TEST NUMBER: P562460

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	365.8	460.4	1199.9	2623.0	2998.1
115°	427.4	516.5	1143.4	2422.3	2844.5
117.5°	481.7	565.3	1110.0	2202.9	2650.1
120°	525.1	595.1	1106.6	2077.5	2506.0
122.5°	559.8	629.8	1097.9	1967.4	2365.4
125°	603.2	669.0	1091.4	1811.1	2165.4
127.5°	650.5	712.0	1087.9	1717.7	2009.6
130°	674.8	736.3	1082.7	1652.6	1907.2
132.5°	700.8	760.6	1082.7	1601.8	1836.0
135°	737.7	799.2	1078.4	1529.8	1729.3
137.5°	772.4	832.2	1077.9	1468.9	1641.2
140°	798.5	860.0	1076.2	1418.4	1583.9
142.5°	828.0	879.3	1081.4	1378.1	1526.6
145°	870.1	914.6	1087.0	1324.1	1442.9
147.5°	906.1	949.4	1096.6	1269.5	1372.1
150°	937.3	967.0	1100.1	1251.4	1323.5
152.5°	961.6	993.0	1103.5	1227.0	1294.0
155°	993.7	1017.1	1113.1	1196.6	1245.4
157.5°	1033.7	1047.7	1115.2	1182.9	1217.7
160°	1054.5	1065.1	1123.9	1172.3	1202.0
162.5°	1066.6	1078.9	1125.7	1163.5	1186.4
165°	1097.9	1102.1	1126.1	1150.3	1167.3
167.5°	1119.1	1115.3	1136.1	1147.1	1153.9
170°	1126.1	1124.0	1132.6	1135.0	1143.4
172.5°	1141.7	1134.5	1137.8	1131.4	1138.2
175°	1150.0	1143.6	1139.1	1132.4	1123.9
177.5°	1153.4	1143.2	1137.8	1130.9	1132.6
180°	1141.3	1141.3	1141.3	1141.3	1141.3

(END OF REPORT)